

Parker E-Can Field Power Supply

Military grade field power for sustained global operations.

Product Features:

- Provides on the go power for critical equipment
- Water resistant and vented case for use in wet and hot environments
- External port for charging while in transit
- Specifications:
 - 135 Ah LiFePO4 energy storage
 - 12VDC 135A continuous output
 - 1000A Jump start pulse capability
 - Charge at up to 135A continuous
 - 24V 30A Anderson connector output
 - 2- 110V outlets: 1500W with 3600W Peak
 - 2 each USB-A and USB-C outlets
 - 2500+ Battery cycles
 - -20F to 150F Temperature range
 - Battery monitor with percent charge and discharge rate readout capability
- Dimensions:
 - 18.5"x13.6"x7.5" – Similar size to standard Jerry Can.
 - Weight: 54lbs



Contact Information

Parker Hannifin Corporation
Defense Business Unit
Andrew McClelland
Defense Market Manager

phone 440 477 3993
amcclelland@parker.com



ENGINEERING YOUR SUCCESS.