

Ø	L = 6 m (16.5 mm: L = 4.5 m)			L = 3 m		
16.5 mm	1004A17 04		1004A17 02	1003A17 04 00	1003A17 06 00	6697 17 00
25 mm	1006A25 04 00	1006A25 06 00	1006A25 02 00	1003A25 04 00	1003A25 06 00	6697 25 00
40 mm	1006A40 04 00	1006A40 06 00	1006A40 02 00	1003A40 04 00	1003A40 06 00	6697 40 00
50 mm	1006A50 04	1006A50 06	1006A50 02	1003A50 04	1003A50 06	6697 50 00
63 mm	1006A63 04	1006A63 06	1006A63 02	1003A63 04	1003A63 06	6697 63 00
76 mm	TA06 L1 04	TA06 L1 06		TA03 L1 04		ER01 L1 00
100 mm	TA06 L3 04	TA06 L3 06		TA03 L3 04		ER01 L3 00
168 mm	TA06 L8 04	TA06 L8 06		TA03 L8 04		ER01 L8 00

Ø									
16.5 mm	6606 17 00	6602 17 00		6604 17 00	6625 17 00				4092 17 00
25 mm	6606 25 00	6602 25 00	6612 25 00	6604 25 00	6625 25 00				4092 25 00
40 mm	6606 40 00	6602 40 00	6612 40 00	6604 40 00	6625 40 00	RA07 40 00			4092 40 00
50 mm	6606 50 00	6602 50 00	6612 50 00	6604 50 00	6625 50 00	RA07 50 00			4092 50 00
63 mm	6606 63 00	6602 63 00	6612 63 00	6604 63 00	6625 63 00	RA07 63 00	RA26 63 00		4092 63 00

Ø									
76 mm	RR01 L1 00	RX02 L1 00	RX12 L1 00	RX04 L1 00	RA25 L1 04	RA07 L1 00	RA26 L1 00	VR01 L1 00	VR02 L1 00
100 mm	RR01 L3 00	RX02 L3 00	RX12 L3 00	RX04 L3 00	RA25 L3 04	RA07 L3 00	RA26 L3 00	VR01 L3 00	VR02 L3 00
168 mm	RR01 L8 00	RA02 L8 00	RA12 L8 00	RA04 L8 00	RA25 L8 04	RA07 L8 00	RA26 L8 00	VR01 L8 00	VR02 L8 00

Ø1	Ø2				
25 mm	16.5 mm			6666 17 25	
40 mm	25 mm			6666 25 40	
50 mm	25 mm	6604 50 25	6666 25 50		
	40 mm	6604 50 40	6666 40 50		
63 mm	40 mm	6604 63 40	6666 40 63		
	50 mm	6604 63 50	6666 50 63		
	76 mm			RA04 63 L1	
76 mm	40 mm	RX24 L1 40			RA26 L1 40
	50 mm	RX24 L1 50	RX64 L1 50		RA26 L1 50
	63 mm	RX24 L1 63	RX64 L1 63		RA26 L1 63
	100 mm			RA04 L1 L3	
100 mm	40 mm	RX24 L3 40			
	50 mm	RX24 L3 50	RX64 L3 50		
	63 mm	RX24 L3 63	RX64 L3 63		RA26 L3 63
	76 mm	RX04 L3 L1	RX66 L3 L1		RA26 L3 L1
	168 mm			RA04 L3 L8	
168 mm	63 mm	RA04 L8 63			
	76 mm	RA04 L8 L1	RA66 L8 L1		
	100 mm	RA04 L8 L3	RA66 L8 L3		RA26 L8 L3

Ø	BSPT				
16.5 mm	1/4"	6605 17 13	6609 17 13		
	1/2"	6605 17 21	6609 17 21		
25 mm	1/2"	6605 25 21	6609 25 21	6619 25 21	6615 25 21
	3/4"	6605 25 27	6609 25 27	6619 25 27	6615 25 27
	1"	6605 25 34	6609 25 34	6619 25 34	6615 25 34
40 mm	1"	6605 40 34	6609 40 34	6619 40 34	
	1 1/4"	6605 40 42	6609 40 42	6619 40 42	6615 40 42
	1 1/2"	6605 40 49	6609 40 49	6619 40 49	6615 40 49
	2"		6609 40 48	6619 40 48	
50 mm	1 1/2"	6605 50 49	6609 50 49	6619 50 49	6615 50 49
	2"	6605 50 48	6609 50 48	6619 50 48	6615 50 48
63 mm	2"	6605 63 48	6609 63 48	6619 63 48	
	2 1/2"	6605 63 47	6609 63 47	6619 63 47	

Ø	EN 1092-1 ISO 7005	
63 mm	DN65/2" 1/2	RA30 63 00
76 mm	DN80/3"	RA30 L1 00
100 mm	DN100/4"	RA30 L3 00
168 mm	DN150/6"	RA31 L8 00
	DN200/8"	RA30 L8 K2

BSPT	EN 1092-1 ISO 7005	
R3"	DN80	RA33 L1 24
R3"	DN100	RA33 L3 24

Ø1	Ø2		
25 mm	16.5 mm	6662 25 17	RA69 25 17
	25 mm	6662 25 00	
40 mm	16.5 mm	6662 40 17	
	25 mm	6662 40 25	RA69 40 25
50 mm	25 mm	6662 50 25	RA69 50 25
63 mm	25 mm	6662 63 25	RA69 63 25

Ø	BSPP			
25 mm	1/2"	6669 25 21	6661 25 21	RA65 25 04
40 mm	1/2"	6669 40 21	6661 40 21	RA65 40 04
	3/4"	6669 40 27	6661 40 27	
50 mm	1/2"	6669 50 21	6661 50 21	RA65 50 04
	3/4"	6669 50 27	6661 50 27	
	1"			RA65 50 08
63 mm	1/2"	6669 63 21	6661 63 21	RA65 63 04
	3/4"	6669 63 27	6661 63 27	
	1"			RA65 63 08
76 mm	1"			RR61 L1 08
	2"			RR61 L1 16
100 mm	1"			RR61 L3 08
	2"			RR61 L3 16
168 mm	1 1/2"			RR63 L8 12
	2"			RR63 L8 16
	2 1/2"			RR63 L8 20
	3"			RR63 L8 24

Ø	BSPP			
16.5 mm	1/2"		6693 17 21	6678 17 21
25 mm	1/2"	6637 25 21	6693 25 21	6678 25 21

Ø	BSPP				
16.5 mm	1/2"		6682 17 21	6681 17 21	6639 17 21
25 mm	1/2"	6695 25 21	6682 25 21	6681 25 21	6639 25 21

BSPP	BSPP				
1/2"	1/2"		6690 21 21	6686 21 21	6641 21 21
3/4"	1/2"	6635 27 21			