

Aluminium Range

| 6606/6676 | Z (mm) |
|-----------|--------|
| Ø16.5 | 35 |
| Ø25 | 48 |
| Ø40 | 57 |
| Ø50 | 25 |
| Ø63 | 25 |

| 6602 | Z (mm) |
|-------|--------|
| Ø16.5 | 31 |
| Ø25 | 40 |
| Ø40 | 62 |
| Ø50 | 56 |
| Ø63 | 61 |

| RX02/RA02 | Z (mm) |
|-----------|--------|
| Ø76 | 189 |
| Ø100 | 227 |
| Ø168 | 185 |

| 6612 | Z (mm) |
|------|--------|
| Ø25 | 32 |
| Ø40 | 45 |
| Ø50 | 38 |
| Ø63 | 37 |

| RX12/RA12 | Z (mm) |
|-----------|--------|
| Ø76 | 122 |
| Ø100 | 138 |
| Ø168 | 147 |

| 6604 | Z1 (mm) | Z2 (mm) |
|-----------|---------|---------|
| Ø16.5 | 34 | 31 |
| Ø25 | 48 | 40 |
| Ø40 | 57 | 57 |
| Ø50 | 56 | 56 |
| Ø50 → Ø25 | 56 | 111 |
| Ø50 → Ø40 | 56 | 107 |
| Ø63 | 61 | 61 |
| Ø63 → Ø40 | 61 | 116 |
| Ø63 → Ø50 | 61 | 117 |

| RX04/RA04 | Z1 (mm) | Z2 (mm) |
|-------------|---------|---------|
| Ø76 | 146 | 146 |
| Ø100 | 156 | 136 |
| Ø168 | 180 | 185 |
| Ø100 → Ø76 | 156 | 136 |
| Ø168 → Ø76 | 180 | 185 |
| Ø168 → Ø100 | 180 | 185 |

| RX24-RA04 + 6606 | Z1 (mm) | Z2 (mm) |
|------------------|---------|---------|
| Ø76 → Ø40 | 146 | 219 |
| Ø76 → Ø50 | 146 | 210 |
| Ø76 → Ø63 | 146 | 213 |
| Ø100 → Ø40 | 156 | 232 |
| Ø100 → Ø50 | 156 | 223 |
| Ø100 → Ø63 | 156 | 226 |
| Ø168 → Ø63 | 180 | 220 |

| RA04 | Z1 (mm) | Z2 (mm) |
|-------------|---------|---------|
| Ø76 → Ø100 | 161 | 149 |
| Ø100 → Ø168 | 194 | 161 |

| RA04 + 6606 | Z1 (mm) | Z2 (mm) |
|-------------|---------|---------|
| Ø63 → Ø76 | 224 | 142 |

| RA26 | Z1 (mm) | Z2 (mm) | Z3 (mm) |
|-------------|---------|---------|---------|
| Ø76 | 260 | 106 | 260 |
| Ø100 | 280 | 116 | 280 |
| Ø100 → Ø76 | 280 | 116 | 280 |
| Ø168 | 350 | 126 | 350 |
| Ø168 → Ø100 | 330 | 86 | 306 |

| RA26 + 6606 | Z1 (mm) | Z2 (mm) |
|-------------|---------|---------|
| Ø63 | 280 | 252 |

| RA26 + 6606 | Z1 (mm) | Z2 (mm) | Z3 (mm) |
|-------------|---------|---------|---------|
| Ø76 → Ø40 | 344 | 106 | 260 |
| Ø76 → Ø50 | 330 | 106 | 260 |
| Ø76 → Ø63 | 330 | 106 | 260 |
| Ø100 → Ø63 | 330 | 116 | 280 |
| Ø100 → Ø76 | 350 | 126 | 350 |
| Ø168 → Ø100 | 350 | 126 | 306 |

| RA07 + 6606 | Z (mm) |
|-------------|--------|
| Ø40 | 240 |
| Ø50 | 228 |
| Ø63 | 232 |

| RA07 | Z (mm) |
|------|--------|
| Ø76 | 149 |
| Ø100 | 161 |
| Ø168 | 191 |

| RA07 ... 45 | Z1 (mm) | Z2 (mm) |
|--------------|---------|---------|
| Ø76 → DN80 | 207 | 149 |
| Ø100 → DN100 | 219 | 161 |
| Ø168 → DN150 | 258 | 191 |

| RA44 ... 45 | Z1 (mm) | Z2 (mm) |
|--------------|---------|---------|
| Ø76 → DN80 | 207 | 149 |
| Ø100 → DN100 | 219 | 161 |
| Ø168 → DN150 | 258 | 191 |

| 6666 | Z (mm) |
|-------------|--------|
| Ø25 → Ø16.5 | 51 |
| Ø40 → Ø25 | 71 |
| Ø50 → Ø25 | 70 |
| Ø50 → Ø40 | 66 |
| Ø63 → Ø40 | 75 |
| Ø63 → Ø50 | 65 |

| RX64/RA66 | Z (mm) |
|-------------|--------|
| Ø76 → Ø50 | 270 |
| Ø76 → Ø63 | 280 |
| Ø100 → Ø50 | 393 |
| Ø100 → Ø63 | 300 |
| Ø100 → Ø76 | 193 |
| Ø168 → Ø76 | 210 |
| Ø168 → Ø100 | 210 |

| 6609 | Z1 (mm) | Z2 (mm) |
|--------------|---------|---------|
| Ø16.5 → 1/4" | 31 | 41 |
| Ø16.5 → 1/2" | 31 | 46 |
| Ø25 → 1/2" | 40 | 53 |
| Ø25 → 3/4" | 40 | 53 |
| Ø25 → 1" | 40 | 55 |
| Ø40 → 1" | 62 | 75 |
| Ø40 → 1 1/4" | 62 | 81 |
| Ø40 → 1 1/2" | 62 | 81 |
| Ø40 → 2" | 62 | 81 |
| Ø50 → 1 1/2" | 56 | 97 |
| Ø50 → 2" | 56 | 99 |
| Ø63 → 2" | 63 | 104 |
| Ø63 → 2 1/2" | 63 | 106 |

| 6619 | Z1 (mm) | Z2 (mm) |
|--------------|---------|---------|
| Ø16.5 → 1/4" | 32 | 42 |
| Ø16.5 → 1/2" | 32 | 42 |
| Ø25 → 1/2" | 32 | 44 |
| Ø25 → 3/4" | 45 | 58 |
| Ø25 → 1" | 45 | 64 |
| Ø40 → 1" | 45 | 64 |
| Ø40 → 1 1/4" | 45 | 64 |
| Ø40 → 1 1/2" | 38 | 80 |
| Ø40 → 2" | 38 | 82 |
| Ø50 → 1 1/2" | 38 | 80 |
| Ø50 → 2" | 38 | 82 |
| Ø63 → 2" | 38 | 82 |
| Ø63 → 2 1/2" | 38 | 82 |

| 6651 | Z (mm) |
|------|--------|
| Ø25 | 107 |
| Ø40 | 61 |

| 6652 | Z (mm) |
|------|--------|
| Ø25 | 204 |
| Ø40 | 217 |

| 4092 | Z1 (mm) | Z2 (mm) |
|-------|---------|---------|
| Ø16.5 | 29 | 43 |
| Ø25 | 41 | 57 |
| Ø40 | 57 | 58 |
| Ø50 | 43 | 60 |
| Ø63 | 66 | 77 |

| VR02 | Z (mm) |
|------|--------|
| Ø76 | 100 |
| Ø100 | 103 |
| Ø168 | 128 |

| RA69 | Z (mm) |
|-------------|--------|
| Ø25 → Ø16.5 | 47 |
| Ø40 → Ø25 | 63 |
| Ø50 → Ø25 | 66 |
| Ø63 → Ø25 | 72 |

| 6662 | Z (mm) |
|-------------|--------|
| Ø25 → Ø16.5 | 82 |
| Ø25 → Ø25 | 74 |
| Ø40 → Ø16.5 | 89 |
| Ø40 → Ø25 | 82 |
| Ø50 → Ø25 | 58 |
| Ø63 → Ø25 | 65 |

Stainless Steel Range

| RR06 | Z (mm) |
|------|--------|
| Ø22 | 1.2 |
| Ø28 | 1.2 |

| RR06/RP06 | Z (mm) |
|-----------|--------|
| Ø42 | 2.6 |
| Ø60 | 2.6 |

| RR05 | Z (mm) |
|------------|--------|
| Ø22 → 1/2" | 21 |
| Ø22 → 3/4" | 22 |
| Ø28 → 1" | 24 |

| RR02 | Z (mm) |
|------|--------|
| Ø22 | 13 |
| Ø28 | 15 |

| RP02 | Z (mm) |
|------|--------|
| Ø42 | 55 |
| Ø60 | 64 |

| RX02 | Z (mm) |
|------|--------|
| Ø76 | 189 |
| Ø100 | 227 |

| RX12 | Z (mm) |
|------|--------|
| Ø42 | 160 |
| Ø60 | 175 |
| Ø76 | 122 |
| Ø100 | 138 |

| RR04 | Z1 (mm) | Z2 (mm) |
|-----------|---------|---------|
| Ø22 | 11.7 | 11 |
| Ø28 | 15 | 15 |
| Ø28 → Ø22 | 12 | 16 |

| RP04 | Z1 (mm) | Z2 (mm) |
|------|---------|---------|
| Ø42 | 55 | 55 |
| Ø60 | 64 | 64 |

| RX04 | Z1 (mm) | Z2 (mm) |
|------------|---------|---------|
| Ø76 | 146 | 146 |
| Ø76 → Ø42 | 146 | 182 |
| Ø76 → Ø60 | 146 | 183 |
| Ø100 | 156 | 136 |
| Ø100 → Ø42 | 156 | 196 |
| Ø100 → Ø60 | 156 | 196 |
| Ø100 → Ø76 | 156 | 136 |

| RR23/RX23 | Z1 (mm) | Z2 (mm) |
|-----------|---------|---------|
| Ø22 | 12 | 14 |
| Ø76 | 146 | 63 |
| Ø100 | 156 | 76 |

Contact: