

CoolTherm® UR-2000 Thermally Conductive Urethane Gap Filler

Technical Data Sheet

CoolTherm® UR-2000 gap filler is a two-component thermally conductive urethane system designed to provide thermal conductivity for electronic applications. CoolTherm UR-2000 gap filler cures at room temperature to produce a flame retardant adhesive.

Features and Benefits:

Thixotropic Viscosity – maintains low viscosity during dispensing, with minimal flow after dispensing; excellent sag and slump resistance.

UL Rated – provides excellent flame retardancy; meets requirements of UL 94 V-0 standards.

Room Temperature Cure – suitable for curing at room temperature; may be heat cured (120°C) to expedite cure.

Durable – provides excellent adhesion to powder-coated and e-coated aluminum surfaces; excellent resistance to peel from PET film and aluminum-coated PET substrates.

Application:

Mixing – Mix CoolTherm UR-2000 resin with CoolTherm UR-2000 hardener at a 1:1 ratio, by volume (100:125, by weight). Handheld cartridges or automatic meter/mix/dispense equipment should be used to avoid any air entrapment in the material. Manual mixing is not recommended.

Applying – Apply material using handheld cartridges or automatic meter/mix/dispense equipment.

- Handheld Cartridges
 1. Load the cartridge into the applicator gun and remove the end caps.
 2. Level the plungers by expelling a small amount of material to ensure both sides are level.
 3. Attach mixing tip and expel a mixer's length of material.
 4. Apply material to substrate and mate the parts within the working time of the gap filler. Clamp in position until material reaches handling strength.
- Meter/Mix/Dispense Equipment
 1. Ensure the correct style/type of MMD system is used with this material.
 2. Warming the dispense lines will lower viscosity, increase dispensing speed, and maintain consistency in the dispensing environment.
 3. Contact your Parker LORD representative if assistance is needed with selecting and using equipment.
 4. Refer to Meter/Mix/Dispensing of LORD Urethane Gap Filler Materials technical tip for additional information.

Curing – CoolTherm UR-2000 gap filler will reach full cure in 24 hours at room temperature. Cure can be expedited at 120°C for 2 hours. This time-at-temperature profile refers to the time the material should be allowed to cure once it reaches the target temperature. Allowance should be made for oven ramp rates, parts with large thermal mass and other circumstances that may delay material reaching the target temperature.

Typical Properties*

	UR-2000 Resin	UR-2000 Hardener	Mixed
Appearance	Red to Pink Paste	White Paste	Pink Paste
Viscosity, cP @ 25°C			
0.5/sec Shear Rate	1,200,000	1,250,000	500,000
1/sec Shear Rate	745,000	780,000	400,000
5/sec Shear Rate	305,000	270,000	220,000
Specific Gravity	2.3	2.8	–
Working Time, minutes @ 25°C	–	–	85

*Data is typical and not to be used for specification purposes.



ENGINEERING YOUR SUCCESS.

Typical Cured Properties*

Thermal Conductivity, W/m·K Hot Disc Transient Method	2
Glass Transition Temperature (T _g), °C by DMA	20
Hardness Shore D, ASTM D 2240	55
Lap Shear Strength, MPa (psi) ASTM D 1002	
Powder-coated Aluminum	6 (870)
E-coated Steel	9 (1305)
180° Peel Strength, gf/cm ASTM D 903	
Bare PET, 0.25 mm	2000
Aluminum-coated PET	600
Volume Resistivity, ohm-cm ASTM D 257	1 x 10 ¹³
Dielectric Strength, kV/mm (V/mil) 1 MHz, ASTM D 149	15 (381)

*Data is typical and not to be used for specification purposes.

Shelf Life/Storage:

Shelf life of each component is six months when stored in clean, dry environment at 18-30°C in original, unopened container.

After opening, protect each component from exposure to moisture by using dry nitrogen as an inert cover each time material is removed. Do not return dispensed material to its original container.

Cautionary Information:

Before using this or any Parker LORD product, refer to the Safety Data Sheet (SDS) and label for safe use and handling instructions.

For industrial/commercial use only. Must be applied by trained personnel only. Not to be used in household applications. Not for consumer use.

Values stated in this technical data sheet represent typical values as not all tests are run on each lot of material produced. For formalized product specifications for specific product end uses, contact the Customer Support Center.

Information provided herein is based upon tests believed to be reliable. In as much as Parker LORD has no control over the manner in which others may use this information, it does not guarantee the results to be obtained. In addition, Parker LORD does not guarantee the performance of the product or the results obtained from the use of the product or this information where the product has been repackaged by any third party, including but not limited to any product end-user. Nor does the company make any express or implied warranty of merchantability or fitness for a particular purpose concerning the effects or results of such use.

WARNING — USER RESPONSIBILITY. FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker-Hannifin Corporation, its subsidiaries and authorized distributors provide product or system options for further investigation by users having technical expertise.

The user, through its own analysis and testing, is solely responsible for making the final selection of the system and components and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application, follow applicable industry standards, and follow the information concerning the product in the current product catalog and in any other materials provided from Parker or its subsidiaries or authorized distributors.

To the extent that Parker or its subsidiaries or authorized distributors provide component or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the components or systems.

©2020 Parker Hannifin - All Rights Reserved

Information and specifications subject to change without notice and without liability therefor. Trademarks used herein are the property of their respective owners.

OD DS4449 06/20 Rev.0



Parker LORD
Engineered Materials Group

111 LORD Drive
Cary, NC 27511-7923
USA

phone +1 877 ASK LORD (275 5673)

www.lord.com