

SAFETY DATA SHEET

TBN REAGENT (C)

Page: 1

Compilation date: 03/12/2014

Revision date: 19/12/17

Revision No: 7

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: TBN REAGENT (C)

Product code: AS-K13378-KW

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Oil test reagent.

1.3. Details of the supplier of the safety data sheet

Company name: Parker Hannifin Ltd ,
3 - 6 Thorgate Road
Lineside Industrial Estate
Littlehampton , West Sussex
BN17 7LU , UNITED KINGDOM
UNITED KINGDOM

Tel: +44 (0) 1903 731470

Fax: +44 (0) 1903 731480

Email: sds@kittiwake.com

1.4. Emergency telephone number

Emergency tel: +32 3 575 11 30 (SGS 24/7 Emergency Hotline)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Chronic 3: H412; Eye Dam. 1: H318

Most important adverse effects: Causes serious eye damage. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H318: Causes serious eye damage.

H412: Harmful to aquatic life with long lasting effects.

Signal words: Danger

Hazard pictograms: GHS05: Corrosion



Precautionary statements: P273: Avoid release to the environment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

SAFETY DATA SHEET

TBN REAGENT (C)

Page: 2

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P310: Immediately call a POISON CENTER/doctor/hospital.

P501: Dispose of contents/container to hazardous waste.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDRODESULPHURIZED HEAVY

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-185-4	64742-82-1	-	Asp. Tox. 1: H304; Flam. Liq. 3: H226; Aquatic Chronic 2: H411	10-30%

C10 ALCOHOL ETHOXYLATE

-	160875-66-1	-	Acute Tox. 4: H302; Eye Dam. 1: H318	10-30%
---	-------------	---	--------------------------------------	--------

ORTHOPHOSPHORIC ACID

231-633-2	7664-38-2	-	Skin Corr. 1B: H314	1-10%
-----------	-----------	---	---------------------	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin.

Drench the affected skin with running water for 10 minutes or longer if substance is still on skin.

Eye contact: Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.

Ingestion: Do not induce vomiting. If conscious, give half a litre of water to drink immediately. If unconscious and breathing is OK, place in the recovery position. Transfer to hospital as soon as possible.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. If unconscious, check for breathing and apply artificial respiration if necessary. If unconscious and breathing is OK, place in the recovery position. If conscious, ensure the casualty sits or lies down. If breathing becomes bubbly, have the casualty sit and provide oxygen if available. Transfer to hospital as soon as possible.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. Corneal burns may occur.

[cont...]

SAFETY DATA SHEET

TBN REAGENT (C)

Page: 3

Ingestion: There may be shortness of breath due to congestion of the lungs. Nausea and stomach pain may occur. There may be vomiting.

Inhalation: Exposure may cause coughing or wheezing. There may be congestion of the lungs causing severe shortness of breath.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Carbon dioxide. Alcohol or polymer foam. Dry chemical powder.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 13 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Avoid direct contact with the substance. Smoking is forbidden.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition.

[cont...]

SAFETY DATA SHEET

TBN REAGENT (C)

Page: 4

7.3. Specific end use(s)

Specific end use(s): Oil test reagent.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ORTHOPHOSPHORIC ACID...100%

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1 mg/m ³	2 mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Ensure eye bath is to hand. Safety glasses with side-shields.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Straw

Odour: Perceptible odour

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Viscosity: Viscous

Flash point°C: >64

Relative density: 0.96 @ 20°C

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

[cont...]

SAFETY DATA SHEET

TBN REAGENT (C)

Page: 5

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Flames.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

ORTHOPHOSPHORIC ACID...100%

ORL	RAT	LD50	1530	mg/kg
-----	-----	------	------	-------

Relevant hazards for substance:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. Corneal burns may occur.

Ingestion: There may be shortness of breath due to congestion of the lungs. Nausea and stomach pain may occur. There may be vomiting.

Inhalation: Exposure may cause coughing or wheezing. There may be congestion of the lungs causing severe shortness of breath.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: No data available.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: Insoluble in water.

[cont...]

SAFETY DATA SHEET

TBN REAGENT (C)

Page: 6

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Harmful to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Dissolve or mix the material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber. Observe all federal, state and local regulations.

Disposal of packaging: Dispose of as normal industrial waste.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H226: Flammable liquid and vapour.

H302: Harmful if swallowed.

H304: May be fatal if swallowed and enters airways.

H314: Causes severe skin burns and eye damage.

H318: Causes serious eye damage.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.