

# P5625/P5675

## Markets



Designed for high pressure pumping applications up to 8000 PSI.

- P5625 has a super tough cover for long lasting abrasion resistance
- P5625 No-Skive design eliminates the need to remove the hose cover before crimping
- P5675 has an extremely thick super tough cover designed for ultra-abrasion resistance
- P5675 requires skiving of the external cover before crimping
- Approved with S6 Series fittings

## P5625/P5675



# Part Number	Hose I.D.		Hose O.D.		Working Pressure		Minimum Bend Radius		Weight		Parkrimp S6 Series
	inch	mm	inch	mm	psi	MPa	inch	mm	lbs/ft	kg/m	
P5625-32	2	51	2.82	71,6	8000	56,0	25	630	5.00	7,43	●
P5675-32	2	51	2.95	75,0	8000	56,0	25	630	5.29	7,89	●

**Application:** Cement slurry, mud service

**Inner Tube:** Synthetic rubber

**Reinforcement:** Four or six spiral steel wire

**Cover:** Synthetic abrasion resistant rubber

**Temperature Range:** -4°F to +158°F (-20°C to +70°C)

**Safety Factor:** 2.5:1

**Fittings:** S6 Series