#### **Technical Information**

## **General Description**

Series BVHH valves are used for shut-off applications and are rated at 690 Bar (10,000 PSI). These valves represent the strongest ball valve in the industry. Series BVHH valves come in ports 1/2" to 2" and SAE, NPT and BSPP ports.


## **Operation**


Parker's 2-way ball valves operate to either off or full flow by rotating the handle 90°. Ball valves are not designed to be a metering or flow control device.

## **Specifications**

Maximum Pressure	690 Bar (10,000 PSI)			
<b>Body Material</b>	Carbon Steel, Black Oxide			
Ball Material	Steel, Chrome Plated Stainless Steel			
Stem Material	Steel, Zinc Plated Stainless Steel			
Standard Handle	Steel Offset, Nickel Plated			
Standard Ball Seals	Delrin + MoS <sub>2</sub>			
Standard Shaft Seals	O-Ring & Backup, Nitrile			
Temperature Range with Standard Seals	-30°C to +100°C (-22°F to +212°F)			









#### **Features**

- Encased Delrin moly ball seals increase the reliability compared to ring reinforcement designs.
- The BVHH is fully ported resulting in very low pressure drop.
- Nitrile seals are standard with fluorocarbon and EPR as options.
- The BVHH is available with options found in the 404 Bar (6000 PSI) models.

#### **Performance Curves**






WARNING: This product can expose you to chemicals including Lead, Nickel (Metallic), or 1,3-Butadiene which are known to the State of California to cause cancer, and Lead or 1,3-Butadiene which is known to the State of California to cause birth defects and other reproductive harm. For more information go to www.P65Warnings.ca.gov.

Cat3300\_02.indd, ddp, 04/19



# Ball Valves Series BVHH


## **Ordering Information**




### **Seal Kit Accessories**

Ball Valve Seal Kits restore a ball valve to factory specifications, providing no erosion or metal-to-metal wear has taken place.

The Seal Kit includes all the o-rings, ball seals and thrust bearings that were originally installed at the factory. A sketch of these parts is provided at the right.



# **Ordering Information**




#### Replacement Handles Standard Steel Offset

Series	Part Number
BVHH04	BVH-HS1
BVHH06	BVH-HS1
BVHH08	BVH-HS1
BVHH12	BVH-HS2
BVHH16	BVH-HS2
BVHH20	BVH-HS3
BVHH24	BVH-HS3
BVHH32	BVH-HS3

Cat3300\_02.indd, ddp, 04/19



#### \_\_\_\_




	Port Thread	Working	Dimensions mm (in)						
Code	Size Pressure	Α	В	С	D	E	F	G	
BVHH – N	BVHH – NPT, SAE, and BSPP								
08	1/2"	690 Bar (10,000 PSI)	107.2 (4.22)	44.5 (1.75)	9.7 (0.38)	22.1 (0.87)	62.5 (2.46)	114.3 (4.50)	83.1 (3.27)
12	3/4"	690 Bar (10,000 PSI)	119.9 (4.72)	63.5 (2.50)	14.2 (0.56)	19.1 (0.75)	82.3 (3.24)	177.8 (7.00)	122.9 (4.84)
16	1"	690 Bar (10,000 PSI)	135.1 (5.32)	69.9 (2.75)	19.1 (0.75)	25.7 (1.01)	83.8 (3.30)	177.8 (7.00)	129.3 (5.09)
20	1 1/4"	690 Bar (10,000 PSI)	157.5 (6.20)	88.9 (3.50)	22.9 (0.90)	28.1 (1.11)	100.9 (3.97)	250.4 (9.86)	165.1 (6.50)
24	1 1/2"	690 Bar (10,000 PSI)	157.7 (6.21)	101.6 (4.00)	28.7 (1.13)	27.2 (1.07)	102.9 (4.05)	250.4 (9.83)	175.5 (6.91)
32	2"	690 Bar (10,000 PSI)	186.7 (7.35)	114.3 (4.50)	38.1 (1.50)	26.2 (1.03)	133.9 (5.27)	250.4 (9.86)	192.8 (7.59)



# **Locking Handle Kit Accessories**

**BVHPLK:** Standard Series 'BVHPLK-\*' kit replaces the stopwasher with a stationary and moving plate, as illustrated below. As the handle is actuated, the moving plate aligns with one of the two locking positions in the stationary plate, enabling the valve to be locked in either **fully closed** or **fully open** position.



## **Ordering Information**

вунн		Standard Locking		
Code	Size	(Part Number)		
08	1/2"	BVHPLK-1		
12	3/4"	BVHPLK-2		
16	1"	BVHPLK-2		
20	1 1/4"	BVHPLK-3		
24	1 1/2"	BVHPLK-3		
32	2"	BVHPLK-3		

