



FOCUSED ON PURIFICATION

Parker Oil Water Separators | ES2000 Series



ENGINEERING YOUR SUCCESS.

Discharging oil contaminated condensate from compressed air systems is not only harmful to the environment, it is probably illegal.

FOCUSED ON CONTAMINANT REMOVAL

Oil can seriously affect the efficient operation of sewage purification, as well as harm the environment. For this reason, very low oil in water discharge limits are permitted and rigid legislation exists in most countries to protect the environment against this type of contamination.

International standards such as ISO 14001 also require the compressed air user to comply with local environmental legislation and show use of protective systems and procedures.

After the oily condensate has been efficiently removed from the compressed air system it cannot be discharged directly to the sanitary sewer without first having the oil content reduced to within legal disposal limits.

Parker Oil/Water Separators are a simple, economical and environmental solution. These oil/water separators are installed as part of the compressed air system and simply reduce the oil concentration in the collected condensate to a level permitted for discharge. This allows the larger volume of clean water, up to 99.9% of the total condensate, to be discharged safely into the sanitary sewer and the relatively small amount of concentrated oil to be disposed of legitimately and economically.

Parker ES2000

Benefits

- Help to protect and maintain the environment
- Efficiently separate oil and water on-site
- Returns up to 99.9% of the condensate to sanitary sewers
- Meet trade effluent discharge regulations
- Rapid payback over conventional disposal methods
- Simple to install, operate and maintain
- Will assist you in achieving ISO 14001 certification

Features

- **High specification carbon** for improved service intervals
- **Sealed external oil container** for easy oil disposal
- **Additional oil containers** for simple maintenance
- Robust, corrosion resistant, **polyethylene construction**, includes ribbing for extra strength
- **Flow splitter** provides equal distribution of condensate on multiple oil/water separator installations
- **Single piece units** - reduces overall footprint
- Large **centrifugal inlet chamber** provides effective venting of compressed air energy, while multiple inlet ports and four inlet chamber positions simplify installation
- Large, easily cleaned **primary settlement chamber** for the accumulation and removal of dirt particles
- Large **internal galleries** reduce risk of an internal blockage and simplify maintenance
- **Oil absorbing pre-filter(s)** protect carbon stage from bulk contamination
- Large **carbon stage** for increased contact time, improving water quality and extending carbon life
- **Adjustable oil outlet funnel** for the efficient removal of separated oil
- **Sample tap** removes need to disconnect outlet piping when obtaining a test sample

Accessories

- Additional oil containers for simple maintenance
- Flow splitter provides equal distribution of condensate on multiple oil/water separator installations
- Condensate manifold - multi ported device for connection to drain ports






-
- > Oil spillages from industry do not have to be big to be serious.
 - > One liter of oil can cover 3500m² of water surface.
 - > One gallon of oil can cover 4 acres of water surface.

Technical Data

Model	ES2100	ES2150	ES2200	ES2300	ES2400	ES2500	ES2600
Inlet Connections	1 x 1/2" 1 x 1/4"	1 x 1/2" 1 x 1/4"	1 x 1/2" 1 x 1/4"	1 x 1/2" 3 x 1/4"	1 x 1/2" 3 x 1/4"	1 x 1/2" 3 x 1/4"	1 x 1/2" 3 x 1/4"
Outlet Hose Connections	3/4" (19 mm)	1" (25 mm)	3/4" (19 mm)	1" (25 mm)	1" (25 mm)	1" (25 mm)	1" (25 mm)
Settlement Tank Capacity	N/A	16 US G	20 US G	33 US G	49 US G	94 US G	128 US G
	N/A	60l	75l	125l	185l	355l	485l
Max. Pressure	16 bar g (232 psi g)						
Min/Max Temperature	°F	41 to 95	41 to 95	41 to 95	41 to 95	41 to 95	41 to 95
	°C	5 to 35	5 to 35	5 to 35	5 to 35	5 to 35	5 to 35
Material (Re-cyclable)	Polyethylene						

Weights and Dimensions

Model	Height (H)		Width (W)		Depth (D)		Weight			
	ins	mm	ins	mm	ins	mm	Empty		Full	
							lbs	kg	lbs	kg
ES2100	33.1	842	9.8	270	12.4	316	13	6	154	24.5
ES2150	31.9	810	13.8	433	16.9	350	22	10	173	78.5
ES2200	31.7	803	13.8	450	17.7	350	26	12	206	93.5
ES2300	47.0	1195	19.7	500	31.5	795	59	27	350	159
ES2400	47.0	1195	26.6	650	31.5	795	79	36	477	217
ES2500	60.4	1535	27.6	700	38.8	980	154	70	880	400
ES2600	60.4	1535	39.4	1000	39.8	1005	214	97	1210	550



Product Selection

There are many factors which play a part in the selection of a static oil/water separator, with ambient conditions of the installation and oil type being the most important.

Capacities shown in this literature assume installation in two of the worlds major climatic conditions. Should the oil/water separator be installed in conditions other than those shown, please contact your local Parker representative or approved distributor/agent for correct sizing.

No Refrigerated Dryer Installed in System		Oil Type											
		Band A Turbine, Additive Free				Band B Mineral, PAO, TMP, PE				Band C Diesters, Triesters, PAG			
Compressor	Model	cfm	m ³ /min	m ³ /hr	L/s	cfm	m ³ /min	m ³ /hr	L/s	cfm	m ³ /min	m ³ /hr	L/s
Rotary Screw, Vane	ES2100	43	1.2	74	20	36	1.0	62	17	30	0.9	51	14
	ES2150	124	3.5	211	59	106	3.0	179	50	86	2.4	146	40
	ES2200	191	5.4	325	90	162	4.6	276	77	132	3.7	224	62
	ES2300	268	7.6	456	127	225	6.4	383	106	185	5.2	314	87
	ES2400	535	15.1	909	252	450	12.7	764	212	370	10.5	628	174
	ES2500	1062	30.1	1804	501	900	25.5	1530	425	734	20.8	1247	346
	ES2600	2113	59.8	3590	997	1800	51.0	3057	849	1461	41.4	2482	689

Refrigerated Dryer Installed in System		Oil Type											
		Band A Turbine, Additive Free				Band B Mineral, PAO, TMP, PE				Band C Diesters, Triesters, PAG			
Compressor	Model	cfm	m ³ /min	m ³ /hr	L/s	cfm	m ³ /min	m ³ /hr	L/s	cfm	m ³ /min	m ³ /hr	L/s
Rotary Screw, Vane	ES2100	33	0.9	55	15	27	0.8	46	13	22	0.6	38	10
	ES2150	93	2.6	158	44	79	2.2	134	37	64	1.8	109	30
	ES2200	143	4.1	243	67	122	3.4	207	57	99	2.8	168	47
	ES2300	201	5.7	341	95	169	4.8	286	79	138	3.9	235	65
	ES2400	400	11.3	680	189	337	9.5	572	159	277	7.8	470	130
	ES2500	795	22.5	1351	375	674	19.1	1145	318	549	15.6	934	259
	ES2600	1582	44.8	2687	756	1347	38.1	2288	635	1093	31.0	1858	516

No Refrigerated Dryer Installed in System		Oil Type											
		Band A Turbine, Additive Free				Band B Mineral, PAO, TMP, PE				Band C Diesters, Triesters, PAG			
Compressor	Model	cfm	m ³ /min	m ³ /hr	L/s	cfm	m ³ /min	m ³ /hr	L/s	cfm	m ³ /min	m ³ /hr	L/s
Rotary Screw, Vane	ES2100	16	0.5	28	8	14	0.4	23	6	11	0.3	19	5
	ES2150	47	1.3	80	22	40	1.1	68	19	33	0.9	55	15
	ES2200	73	2.1	123	34	62	1.7	105	29	50	1.4	85	24
	ES2300	102	2.9	173	48	85	2.4	145	40	70	2.0	119	33
	ES2400	203	5.7	345	96	171	4.8	290	80	140	4.0	238	66
	ES2500	403	11.4	684	190	341	9.7	580	161	278	7.9	473	131
	ES2600	801	22.7	1361	378	682	19.3	1159	322	554	15.7	941	261

Refrigerated Dryer Installed in System		Oil Type											
		Band A Turbine, Additive Free				Band B Mineral, PAO, TMP, PE				Band C Diesters, Triesters, PAG			
Compressor	Model	cfm	m ³ /min	m ³ /hr	L/s	cfm	m ³ /min	m ³ /hr	L/s	cfm	m ³ /min	m ³ /hr	L/s
Rotary Screw, Vane	ES2100	13	0.4	23	6	11	0.3	19	5	9	0.3	16	4
	ES2150	38	1.1	64	18	32	0.9	55	13	26	0.7	45	12
	ES2200	58	1.7	99	27	50	1.4	84	23	40	1.1	69	19
	ES2300	82	2.3	139	39	69	1.9	117	32	56	1.6	96	27
	ES2400	163	4.6	278	77	137	3.9	234	65	113	3.2	192	53
	ES2500	324	9.2	551	153	275	7.8	467	130	224	6.4	381	106
	ES2600	645	18.3	1097	305	550	15.6	934	259	446	12.6	758	210

Climate Condition 1

System Conditions

- Ambient Temperature at Compressor Inlet: 77°F (25°C)
- Relative Humidity: 85%
- Compressor Discharge Temperature: 95°F (35°C)
- Refrigerated Dryer Dewpoint if Fitted: 35°F (2°C)
- Min. System Temp. Without Refrigerated Dryer: 86°F (30°C)
- System Pressure: 102 psig (7 bar g)
- (For conditions other than those shown, e.g. higher ambient temperatures, please contact Parker.)

- For systems using 1 or 2 stage piston/reciprocating compressors multiply compressor flow by 1.4 and select a separator from screw compressor flow rates shown, ensuring due consideration is given to oil type. For 3 or 4 stage piston/reciprocating compressors, please contact Parker.

Climate Condition 2

System Conditions

- Ambient Temperature at Compressor Inlet: 95°F (35°C)
- Relative Humidity: 85%
- Compressor Discharge Temperature: 113°F (45°C)
- Refrigerated Dryer Dewpoint if Fitted: 35°F (2°C)
- Min. System Temp. Without Refrigerated Dryer: 104°F (40°C)
- System Pressure: 102 psig (7 bar g)
- (For conditions other than those shown, e.g. higher ambient temperatures, please contact Parker.)

- For systems using 1 or 2 stage piston/reciprocating compressors multiply compressor flow by 1.4 and select a separator from screw compressor flow rates shown, ensuring due consideration is given to oil type. For 3 or 4 stage piston/reciprocating compressors, please contact Parker.

Maintenance Kits

We are pleased to offer a complete range of competitor interchange oil/water separator maintenance kits.

Beko Condensate Systems

Code No	To Suit Separator Models
PDHR-OWB1	Alternative Maintenance Kit to suit Owamat 1
PDHR-OWB1	Alternative Maintenance Kit to suit Owamat 2
PDHR-OWB4	Alternative Maintenance Kit to suit Owamat 3
PDHR-OWB5	Alternative Maintenance Kit to suit Owamat 4
PDHR-OWB6	Alternative Maintenance Kit to suit Owamat 5
PDHR-OWB8	Alternative Maintenance Kit to suit Owamat 6

Ultrafilter

Code No	To Suit Separator Models
PDHR-OWU5	Alternative Carbon Bag Kit to suit Super Plus 5
PDHR-OWU10	Alternative Carbon Bag Kit to suit Super Plus 10
PDHR-OWU15	Alternative Carbon Bag Kit to suit Super Plus 15
PDHR-OWU30	Alternative Carbon Bag Kit to suit Super Plus 30
PDHR-OWU60	Alternative Carbon Bag Kit to suit Super Plus 60
PDHR-OWU120	Alternative Carbon Bag Kit to suit Super Plus 120
PDHR-OWU240	Alternative Carbon Bag Kit to suit Super Plus 240
PDHR-FSC5	Foam Service Kit to suit UFS 5
PDHR-FSC10	Foam Service Kit to suit UFS 10
PDHR-FSC15	Foam Service Kit to suit UFS 15
PDHR-FSC30	Foam Service Kit to suit UFS 30
PDHR-FSC60	Foam Service Kit to suit UFS 60

Wortman

Code No	To Suit Separator Models
PDHR-OWW1	Alternative Carbon Bag Kit to suit Drukomat 1
PDHR-OWW2	Alternative Carbon Bag Kit to suit Drukomat 2-15
PDHR-OWW6	Alternative Carbon Bag Kit to suit Drukomat 30
PDHR-OWW7	Alternative Carbon Bag Kit to suit Drukomat 60

Hankison

Code No	To Suit Separator Models
PDHR-OWW1	Alternative Maintenance Kit to suit HSMK-1
PDHR-OWW2	Alternative Maintenance Kit to suit HSMK-2
PDHR-OWW2z	Alternative Maintenance Kit to suit HSMK-3
PDHR-OWW2	Alternative Maintenance Kit to suit HSMK-4
PDHR-OWW5	Alternative Maintenance Kit to suit HSMK-5
PDHR-OWW6	Alternative Maintenance Kit to suit HSMK-6
PDHR-OWW7	Alternative Maintenance Kit to suit HSMK-7





MotivAir

Code No	To Suit Separator Models
PDHR-0WW1	Alternative Carbon Bag Kit to suit OSW01
PDHR-0WW2	Alternative Carbon Bag Kit to suit OSW02
PDHR-0WW2	Alternative Carbon Bag Kit to suit OSW03
PDHR-0WW2	Alternative Carbon Bag Kit to suit OSW04
PDHR-0WW5	Alternative Carbon Bag Kit to suit OSW05
PDHR-0WW6	Alternative Carbon Bag Kit to suit OSW06
PDHR-0WW7	Alternative Carbon Bag Kit to suit OSW07
PDHR-0WW8	Alternative Carbon Bag Kit to suit OSW08

ASP

Code No	To Suit Separator Models
PDHR-0WA15	Alternative Carbon Bag Kit to suit ASP-CE15
PDHR-0WA30	Alternative Carbon Bag Kit to suit ASP-CE30
PDHR-0WA60	Alternative Carbon Bag Kit to suit ASP-CE60
PDHR-0WA120	Alternative Carbon Bag Kit to suit ASP-CE120
PDHR-0WA180	Alternative Carbon Bag Kit to suit ASP-CE180
PDHR-0WA240	Alternative Carbon Bag Kit to suit ASP-CE240
PDHR-0WA20	Alternative Carbon Bag Kit to suit PS20/CE20
PDHR-0WA40	Alternative Carbon Bag Kit to suit PS40/CE40
PDHR-0WA90	Alternative Carbon Bag Kit to suit PS90/CE90

Kaeser

Code No	To Suit Separator Models
PDHR-0WU5	Alternative Maintenance Kit to suit MK-75
PDHR-0WU10	Alternative Maintenance Kit to suit MK-150
PDHR-0WU15	Alternative Maintenance Kit to suit MK-260
PDHR-0WU30	Alternative Maintenance Kit to suit MK-520
PDHR-0WU60	Alternative Maintenance Kit to suit MK-2060
PDHR-0WU120	Alternative Maintenance Kit to suit MK-2060D
PDHR-0WU240	Alternative Maintenance Kit to suit MK-2060Q

Quincy

Code No	To Suit Separator Models
PDHR-0WU5	Alternative Carbon Bag Kit to suit QLOW05
PDHR-0WU10	Alternative Carbon Bag Kit to suit QLOW0010
PDHR-0WU15	Alternative Carbon Bag Kit to suit QLOW0015
PDHR-0WU30	Alternative Carbon Bag Kit to suit QLOW0030
PDHR-0WU60	Alternative Carbon Bag Kit to suit QLOW0060
PDHR-0WU120	Alternative Carbon Bag Kit to suit QLOW120
PDHR-0WU240	Alternative Carbon Bag Kit to suit QLOW240

Worldwide Filtration Manufacturing Locations

North America

Compressed Air Treatment

Industrial Gas Filtration and Generation Division

Lancaster, NY
716 686 6400
www.parker.com/igfg

Haverhill, MA
978 858 0505
www.parker.com/igfg

Engine Filtration

Racor

Modesto, CA
209 521 7860
www.parker.com/racor

Holly Springs, MS
662 252 2656
www.parker.com/racor

Hydraulic Filtration

Hydraulic & Fuel Filtration

Metamora, OH
419 644 4311
www.parker.com/hydraulicfilter

Laval, QC Canada
450 629 9594
www.parkerfarr.com

Velcon
Colorado Springs, CO
719 531 5855
www.velcon.com

Process Filtration

domnick hunter Process Filtration SciLog

Oxnard, CA
805 604 3400
www.parker.com/processfiltration

Water Purification

Village Marine, Sea Recovery, Horizon Reverse Osmosis

Carson, CA
310 637 3400
www.parker.com/watermakers

Europe

Compressed Air Treatment

domnick hunter Filtration & Separation

Gateshead, England
+44 (0) 191 402 9000
www.parker.com/dhfn

Parker Gas Separations

Etten-Leur, Netherlands
+31 76 508 5300
www.parker.com/dhfn

Hiross Zander

Essen, Germany
+49 2054 9340
www.parker.com/hzfd

Padova, Italy
+39 049 9712 111
www.parker.com/hzfd

Engine Filtration & Water Purification

Racor

Dewsbury, England
+44 (0) 1924 487 000
www.parker.com/rfde

Racor Research & Development

Stuttgart, Germany
+49 (0)711 7071 290-10

Hydraulic Filtration

Hydraulic Filter

Arnhem, Holland
+31 26 3760376
www.parker.com/hfde

Urdala, Finland
+358 20 753 2500

Condition Monitoring Parker Kittiwake

West Sussex, England
+44 (0) 1903 731 470
www.kittiwake.com

Process Filtration

domnick hunter Process Filtration Parker Twin Filter BV

Birtley, England
+44 (0) 191 410 5121
www.parker.com/processfiltration

Asia Pacific

Australia

Castle Hill, Australia
+61 2 9634 7777
www.parker.com/australia

China

Shanghai, China
+86 21 5031 2525
www.parker.com/china

India

Chennai, India
+91 22 4391 0700
www.parker.com/india

Parker Fowler

Bangalore, India
+91 80 2783 6794
www.johnfowlerindia.com

Japan

Tokyo, Japan
+81 45 870 1522
www.parker.com/japan

Korea

Hwaseon-City
+82 31 359 0852
www.parker.com/korea

Singapore

Jurong Town, Singapore
+65 6887 6300
www.parker.com/singapore

Thailand

Bangkok, Thailand
+66 2186 7000
www.parker.com/thailand

Latin America

Parker Comercio Ltda.

Filtration Division
Sao Paulo, Brazil
+55 12 4009 3500
www.parker.com/br

Pan American Division

Miami, FL
305 470 8800
www.parker.com/panam

Africa

Aeroporto Kempton Park, South Africa
+27 11 9610700
www.parker.com/africa

© 2019 Parker Hannifin Corporation. Product names are trademarks or registered trademarks of their respective companies

BRO-PKR_ES-FO_012019



Parker Hannifin Corporation
Industrial Gas Filtration
and Generation Division
4087 Walden Avenue
Lancaster, NY 14086
phone 800 343 4048
www.parker.com/igfg



State of California ONLY
WARNING: Proposition 65
The products described herein can expose you to chemicals known to the State of California to cause cancer or reproductive harm.
For more information: www.P65Warnings.ca.gov