


Global ISO Offering

Industrial Pneumatic Linear Rod Actuators



ENGINEERING YOUR SUCCESS.

Parker Hannifin - Worldwide

The global leader in motion & control technologies



Parker Hannifin is one of the worlds leading suppliers of products and solutions in Motion and Control. Using innovative product development and an acquisition strategy to increase our range of pneumatic products and solutions, we now have one of the broadest product offerings available in the market.

Our range now extends from the power to the point at which air is used. This could be supplying power take off on a vehicle, moving a cylinder or gripper to milking cows. The design and manufacture of bespoke integrated solutions for air, gas and fluid control is one of four core specifications.

200
MANUFACTURING
FACILITIES

150
OFFICES

15,000
DISTRIBUTORS

54
COUNTRIES

500,000
CUSTOMERS

What is ISO (International Organisation for Standardisation)

ISO originated from the union of two Organisations – the ISO (International Federation of the National Standardising Associations) and the UNSCC (United Nations Standard Coordinating Committee).

In 1946 over 25 countries met at the Institute of Civil Engineers in London to create a new international Organisation, where the objective was to 'facilitate the international coordination and unification of industrial standards' from this the new Organisation ISO began operations in February 1947. The word ISO is derived from the Greek ISOS meaning 'equal'.

As the International Organisation for Standardization would translate differently across different languages it was decided that the short form name for the Organisation would be ISO.

Today the ISO has grown to a confederation of delegates representing over 150 countries and has published over 16,500 international standards. They meet on a regular basis to further develop new and existing management standards.

Benefits of Certification

Each standard supports its own benefits within every industry, however the common benefits across the certifications include: widened market potential, compliance to procurement tenders, improved efficiency and cost savings, higher level of customer service, and therefore satisfaction, and heightened staff moral and motivation.

By having a recognised management standard it tells your customers that you are serious about their needs.

ISO 6432 P1A/P1S Series



P1A / P1S Series Round Cylinders

The P1A / P1S Series are a complete range of ISO 6432 round cylinders developed to meet the highest requirements for value, quality and performance. The careful design in every detail provides first class function and service life properties. Suitable for a wide range of limited stroke lengths applications.

Benefits

Reliability and long service life are key qualities of any pneumatic cylinder. Therefore we have given P1A / P1S highest possible quality in every detail based on our 40 years of experience and extensive testing. Long service life with proven expertise for leading and proven tribology solutions and seal technology within Parker Pradifa. The compact dimension makes it possible to use the P1A / P1S cylinders in a broad range of applications. This is highly valuable in narrow spaces in machines or production lines.

Installation dimensions

Complies with the ISO 6432 for cylinder dimensions and for the mountings (from bore 32mm) for customer reassurance world-wide interchangeability.

Features

- Bores 10, 12, 16, 20, 25 mm (ISO 6432)
- Air ports M5 bores 12-16 mm, 1/8 BSPP (G threads) bores 20-25 mm
- Strokes from 5 up to 1000 mm
- Double or single acting
- Magnetic piston as standard
- Piston with elastic end of stroke cushioning as standard
- Piston rod in polished stainless steel as standard
- Male threads
- Scraper / piston rod seal in one
- Standard and high temperature
- Corrosion resistant design, end covers in anodised aluminium (P1A) or in stainless steel (P1S) barrel in stainless steel
- Without piston rod guidance
- Low weight construction
- Bracket for fixing sensors on the cylinder's body
- Flexible direct mountings, threads on each end face

ISO 15524 P1Q Series



P1Q Series Compact Cylinder

The P1Q Series is a complete range of ISO 15524 compact cylinders developed to meet the highest requirements for value, quality and performance. The careful design in every detail provides first class function and service life properties. The versatile high quality ISO compact cylinder range, P1Q cylinders are up to 50% shorter than ISO 15552 cylinders for the same stroke. Suitable for a wide range of limited stroke lengths applications.

Benefits

Reliability and long service life are key qualities of any pneumatic cylinder. Therefore we have given P1Q highest possible quality in every detail based on our 40 years of experience and extensive testing. Long service life with proven expertise for leading and proven tribology solutions and seal technology.

The compact axial dimension makes it possible to use the P1Q cylinders in a broad range of applications. This is highly valuable in narrow spaces in machines or production lines.

Installation dimensions

Complies with the ISO 15524 for cylinder dimensions for customer reassurance world-wide interchangeability.

Features

- Bores 12, 16, 20, 25, 32, 40, 50, 63, 80, 100 mm
- Air ports Metric bores 12 to 25 mm, BSPP (G threads) bores 32 to 100 mm
- Strokes from 5 up to 100 mm
- Double acting
- Magnetic or non magnetic piston
- Buffer cushioning both side as standard
- Stainless steel piston rod bores 12 to 32 mm, medium carbon steel bores 40 to 100 mm as standard
- Female threads as standard
- Standard temperature
- Corrosion resistant design, end covers and barrel in anodised aluminium
- Without piston rod guidance
- Low weight construction
- 2 sensors grooves per side face
- Flexible direct mountings, 4 through holes or 4 threads on each end face

ISO 21287 P1P Series



P1P Series Compact Cylinders

The P1P Series is a complete range of ISO 21287 compact cylinders developed to meet the highest requirements for value, quality and performance. The careful design in every detail provides first class function and service life properties. The versatile high quality ISO compact cylinder range, P1P cylinders are up to 50% shorter than ISO 15552 cylinders for the same stroke. Suitable for a wide range of limited stroke lengths applications.

Benefits

Reliability and long service life are key qualities of any pneumatic cylinder. Therefore we have given P1P highest possible quality in every detail based on our 40 years of experience and extensive testing. Long service life with proven expertise for leading and proven tribology solutions and seal technology within Parker Prädifa.

The compact axial dimension makes it possible to use the P1P cylinders in a broad range of applications. This is highly valuable in narrow spaces in machines or production lines.

Installation dimensions

Complies with the ISO 21287 for cylinder dimensions and with ISO 15552 for the mountings (from bore 32mm) for customer reassurance world-wide interchangeability.

Features

- Bores 20, 25, 32, 40, 50, 63, 80, 100 mm
- Air ports M5 bores 20 to 25 mm, BSPP (G threads) bores 32 to 100 mm
- Strokes from 5 up to 100 mm
- Double or single acting
- Magnetic piston as standard
- Piston with elastic end of stroke cushioning as standard
- Piston rod in polished stainless steel as standard
- Female or male threads
- Piston rod bearing in multilayer PTFE/ steel
- Wiper / piston rod seal in one
- Standard, low and high temperature
- Corrosion resistant design, end covers and barrel in anodised aluminium
- With or without piston rod guidance
- Low weight construction
- 1 or 2 sensors grooves per side face
- Flexible direct mountings, 4 through holes or 4 threads on each end face

ISO 15552 P1F Series



P1F Cylinders

The P1F Series is a complete range of ISO 15552 compact cylinders developed to meet the highest requirements for value, quality and performance. The careful design in every detail provides first class function and service life properties. The versatile high quality ISO cylinder range. Suitable for a wide range of applications.

Benefits

Reliability and long service life are key qualities of any pneumatic cylinder. Therefore we have given P1F highest possible quality in every detail based on our 40 years of experience and extensive testing. Long service life with proven expertise for leading and proven tribology solutions and seal technology within Parker Pradifa.

Installation dimensions

Complies with the ISO 15552 for cylinder dimensions and for the mountings for customer reassurance world-wide interchangeability.

Features

- Bores 32, 40, 50, 63, 80, 100, 125 mm
- Air ports 1/8, 1/4, 1/4, 3/8, 3/8, 1/2, 1/2, BSPP (G threads)
- Strokes from 5 up to 2.500 mm
- Double acting
- Magnetic piston as standard
- Aluminium and non magnetic piston as an option
- Piston rod in polished stainless steel as standard
- Female or male threads
- Piston rod bearing in multilayer PTFE/ steel
- Wiper / piston rod seal in one
- Standard, low and high temperature
- Metallic scraper as an option
- FKM or dry running scraper with stainless steel screws and anodised end caps as an option
- Corrosion resistant design, sandblast end covers and barrel in anodised aluminium
- Without piston rod guidance
- Low weight construction
- ATEX version as an option
- Rod locks as an option
- 2 sensors grooves on top face
- Flexible direct mountings, 4 threads on each end face

ISO 15552 P1F-T Series



P1F-T Series Tie-Rods Cylinders

The P1D-T Series is a complete range of ISO 15552 cylinders developed to meet the highest requirements for value, quality and performance. The careful design in every detail provides first class function and service life properties. Suitable for a wide range of applications.

Benefits

Reliability and long service life are key qualities of any pneumatic cylinder. Therefore we have given P1F highest possible quality in every detail based on our 40 years of experience and extensive testing. Long service life with proven expertise for leading and proven tribology solutions and seal technology within Parker Pradifa.

Installation dimensions

Complies with the ISO 15552 for cylinder dimensions and for the mountings for customer reassurance world-wide interchangeability.

Features

- Bores 160, 200, 250, 320 mm
- Air ports 1/2, 1/2, 1, 1, BSPP (G threads)
- Strokes from 5 up to 2300 mm
- Double acting
- Magnetic piston as standard
- Non magnetic piston as an option
- Piston rod in polished stainless steel as standard
- Male threads
- Piston rod bearing in multilayer PTFE/ steel
- Standard and high temperature
- Corrosion resistant design, painted end covers and barrel
Sin anodised aluminium
- Without piston rod guidance
- Low weight construction
- Bracket for fixing sensors on tie rods
- Flexible direct mountings, 4 threads on each end face

Parker Worldwide

Europe, Middle East, Africa

AE – United Arab Emirates, Dubai

Tel: +971 4 8127100
parker.me@parker.com

AT – Austria, Wiener Neustadt

Tel: +43 (0)2622 23501-0
parker.austria@parker.com

AT – Eastern Europe, Wiener Neustadt

Tel: +43 (0)2622 23501 900
parker.easteurope@parker.com

AZ – Azerbaijan, Baku

Tel: +994 50 2233 458
parker.azerbaijan@parker.com

BE/LU – Belgium, Nivelles

Tel: +32 (0)67 280 900
parker.belgium@parker.com

BG – Bulgaria, Sofia

Tel: +359 2 980 1344
parker.bulgaria@parker.com

BY – Belarus, Minsk

Tel: +48 (0)22 573 24 00
parker.poland@parker.com

CH – Switzerland, Etoy

Tel: +41 (0)21 821 87 00
parker.switzerland@parker.com

CZ – Czech Republic, Klecany

Tel: +420 284 083 111
parker.czechrepublic@parker.com

DE – Germany, Kaarst

Tel: +49 (0)2131 4016 0
parker.germany@parker.com

DK – Denmark, Ballerup

Tel: +45 43 56 04 00
parker.denmark@parker.com

ES – Spain, Madrid

Tel: +34 902 330 001
parker.spain@parker.com

FI – Finland, Vantaa

Tel: +358 (0)20 753 2500
parker.finland@parker.com

FR – France, Contamine s/Arve

Tel: +33 (0)4 50 25 80 25
parker.france@parker.com

GR – Greece, Athens

Tel: +30 210 933 6450
parker.greece@parker.com

HU – Hungary, Budaörs

Tel: +36 23 885 470
parker.hungary@parker.com

IE – Ireland, Dublin

Tel: +353 (0)1 466 6370
parker.ireland@parker.com

IL – Israel

Tel: +39 02 45 19 21
parker.israel@parker.com

IT – Italy, Corsico (MI)

Tel: +39 02 45 19 21
parker.italy@parker.com

KZ – Kazakhstan, Almaty

Tel: +7 7273 561 000
parker.easteurope@parker.com

NL – The Netherlands, Oldenzaal

Tel: +31 (0)541 585 000
parker.nl@parker.com

NO – Norway, Asker

Tel: +47 66 75 34 00
parker.norway@parker.com

PL – Poland, Warsaw

Tel: +48 (0)22 573 24 00
parker.poland@parker.com

PT – Portugal

Tel: +351 22 999 7360
parker.portugal@parker.com

RO – Romania, Bucharest

Tel: +40 21 252 1382
parker.romania@parker.com

RU – Russia, Moscow

Tel: +7 495 645-2156
parker.russia@parker.com

SE – Sweden, Spånga

Tel: +46 (0)8 59 79 50 00
parker.sweden@parker.com

SL – Slovenia, Novo Mesto

Tel: +386 7 337 6650
parker.slovenia@parker.com

TR – Turkey, Istanbul

Tel: +90 216 4997081
parker.turkey@parker.com

UA – Ukraine, Kiev

Tel: +48 (0)22 573 24 00
parker.poland@parker.com

UK – United Kingdom, Warwick

Tel: +44 (0)1926 317 878
parker.uk@parker.com

ZA – South Africa, Kempton Park

Tel: +27 (0)11 961 0700
parker.southafrica@parker.com

North America

CA – Canada, Milton, Ontario

Tel: +1 905 693 3000

US – USA, Cleveland

Tel: +1 216 896 3000

Asia Pacific

AU – Australia, Castle Hill

Tel: +61 (0)2-9634 7777

CN – China, Shanghai

Tel: +86 21 2899 5000

HK – Hong Kong

Tel: +852 2428 8008

IN – India, Mumbai

Tel: +91 22 6513 7081-85

JP – Japan, Tokyo

Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul

Tel: +82 2 559 0400

MY – Malaysia, Shah Alam

Tel: +60 3 7849 0800

NZ – New Zealand, Mt Wellington

Tel: +64 9 574 1744

SG – Singapore

Tel: +65 6887 6300

TH – Thailand, Bangkok

Tel: +662 186 7000

TW – Taiwan, Taipei

Tel: +886 2 2298 8987

South America

AR – Argentina, Buenos Aires

Tel: +54 3327 44 4129

BR – Brazil, Sao Jose dos Campos

Tel: +55 800 727 5374

CL – Chile, Santiago

Tel: +56 2 623 1216

MX – Mexico, Toluca

Tel: +52 72 2275 4200

European Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

