




# Treatment & Distribution of Industrial Fluids

Compressed Air - Vacuum - Inert Gas - Industrial Water and Oil



ENGINEERING YOUR SUCCESS.

# Products



## Coalescing and Activated Carbon Filters

Flow rate up to 31.000 m<sup>3</sup>/h. Operating pressure up to 350 bar  
Deliverables in accordance with the main international bodies (PED, ASME VIII div. 1 and 2, Ghost, China Stamp, LRofS, DNV, GL, ABS, etc.) including directives ISO12500 and ISO8573.1



## Refrigeration Dryers

- Flow up to 21 400 m<sup>3</sup>/h
- Operating pressure up to 40 bar
- Pressure dew point +3 °C
- Energy-saving system SMART SAVE




## Transair® System in Aluminium

Transair®: a unique, truly flexible and upgradeable aluminium pipe system  
Creating primary and secondary networks of the main industrial gases has never been quicker  
Compatible fluids: air, nitrogen, vacuum and argon, etc  
Diameters available: 16.5, 25, 40, 50, 63, 76, 100 and 168mm  
Tube colours: blue, grey and green  
Fittings: BSP and NPT



## Adsorption Dryers for Compressed Air

- Flow rate up to 14.500 m<sup>3</sup>/h. Operating pressure up to 350 bar  
Pressure dew point to -70°C. Designed for air and other compressed gases
- Patented vacuum regeneration system
- Compliant with the requirements of main international standards and bodies (PED, ASME VIII div. 1 and 2, Ghost, China Stamp, LRofS, DNV, GL, ABS, etc.)  
Also available are variants for ATEX and food beverage and pharma



## Membrane Dryers

- Designed for point of use applications where compact size is a determining factor.
- Flow rate of air up to 1.000 m<sup>3</sup>/h
- Operating pressure up to 10 bar
- Pressure dew point to -40°C
- Operates without electrical supply



## Breathing Air Systems

- Flow rate up to 850 m<sup>3</sup>/h
- Operating pressure up to 16 bar
- Compliant with ISO 12021 and European Pharmacopoeia standards



## Heat Exchangers with Air and Liquid Cooling Systems



- Flow rate up to 12.000 m<sup>3</sup>/h
- Designed for applications from 0 to 40 bar
- Available in stainless steel and other materials resistant to chemical agents
- Special ranges for biogas and natural gas
- Bespoke installations according to requirements

# From the Technical Room...

## One Solution for Each Contaminant

There are several different techniques for efficiently removing the contaminants found in compressed air and gases.


Parker develops the best solutions and equipment for optimum results, with associated energy savings and respect for the environment.





# ...to the Heart of Production

The Parker solution couples excellent purity of conveyed air and gases with high flow and lower operating costs



# Products

## Chillers for Industrial Cooling

- Refrigerating power up to 757 kW
- Special external and internal surface treatments for aggressive gases and environments are available
- Dedicated equipment for laser applications and special gases (biogas)
- Bespoke installations according to requirements



## Condensate Drains

- For compressed air lines up to 66.000 m3/h.
- Operating pressure up to 50 bar. Designed for corrosive gases and air
- Float, time delay and electronic level control versions



## Transair® System in Stainless Steel

Transair®: a flexible and upgradeable stainless steel pipe system for creating primary and secondary industrial water networks.  
Compatible fluids: industrial water, oils, etc  
Main application: cooling (moulds, tools, welding, etc.)  
Diameters available: 22, 28, 42, 60, 76 and 100 mm  
Fittings: BSP and NPT



## Water-Oil Condensate Separators

Available in 7 models for the treatment of condensates generated by compressed air for flow rates up to 3.600 m3/h



## Nitrogen Generators for Industrial and Laboratory Applications

- Pressure Swing Adsorption and Hollow Fibre Membrane technologies available to provide most convenient application fit.
- Flow rates from 500cc/min to 1000's m3/hour
- Multi-bank modular construction for larger high flow rate demand to ensure maximum flexibility
- Energy Saving Technology, (EST), ensures low energy consumption and reduced CO<sub>2</sub>
- Purities from 5% to 5 parts per million (ppm), maximum remaining oxygen content.
- Air inlet pressure range from 4 bar to 13 bar
- Nitrogen outlet pressure range from 1 bar to 11 bar
- Independent 3rd party testing to demonstrate compliance with European Pharmacopoeia.
- Food Grade Nitrogen E941 and FDA Article 21



## Nitrogen Membrane Generators

- To generate ultra-pure nitrogen from compressed air
- Flow rate of nitrogen produced up to 300 m3/h
- Modular assembly for larger nitrogen flow rates
- Degree of purity: from 95% to 99.5%
- Maximum pressure of outgoing nitrogen: 13 bar
- Reduced compressed air consumption per m3 of nitrogen produced
- Designed for point-of-use applications



## Added Value Services

- Contaminant analysis
- Particle counting
- Humidity testing
- Breathing air analysis
- Leak testing
- Service packages
- Factory trained technicians




# Transair® for Technical Rooms

Transair® has developed a range of **specific products for technical rooms** and the connection of industrial fluid treatment equipment.

This range has been designed to meet the **specific requirements of technical rooms**, such as **reduced space** and the need for equipment **maintenance operations**, while preserving the historic advantages of Transair®: speed and ease of installation, **flexibility, modularity, safety** and **performance**.

All these Transair® products are made of **aluminium** and meet the requirements of **ISO 8573: 2001 & 2010 Class 1.1.1**, guaranteeing **non-contamination** of the fluid by solid particles, water, humidity or oil.





# Focus on Compressed Air: the 4<sup>th</sup> Utility

Compressed air is a **safe and reliable power source** that is widely used throughout industry.

Known as the 4<sup>th</sup> utility, approximately **90%** of all companies use **compressed air** in some aspect of their operations.

Unlike gas, water and electricity which is supplied to site by a utility company to strict tolerances and quality specifications, **compressed air is generated on-site** by the end user.

The **quality** of the compressed air and the cost of producing this powerful utility is therefore the **responsibility of the user**.

The quality and reliability of compressed air distribution systems have always posed problems. Almost all concerns arise from **contaminants carried in the air**.

Typically there are at least **10 different contaminants in a traditional compressed air network**.

These may be present in the **atmospheric** air drawn into the compressor or can be created within the compressor itself. They are also often found in air receivers or **out-dated pipe systems** which may be **subject to corrosion**.

Contaminants, however, can be fully **removed or reduced** to acceptable levels when the **compressed air treatment** and the air **distribution system** are **managed safely and efficiently**.



Water supplied to industrial concerns is continually monitored by Local Authorities in order to check there are no contaminants present which could endanger the production cycle.



Utility providers must ensure that the gas and water supplied to industrial users meet stringent quality standards.




Compressed air is generated by users themselves who alone are responsible for its purity.

## CONTAMINATION: THE RISK POINTS IN THE SYSTEM

The ten main contaminants in a compressed air system come from four main sources:

- Source 1 – Ambient Air
- Source 2 – The Air Compressor
- Source 3 – The Air Receiver
- Source 4 – The Distribution Piping



# Parker Worldwide

## Europe, Middle East, Africa

**AE – United Arab Emirates,**  
Dubai

Tel: +971 4 8127100  
parker.me@parker.com

**AT – Austria,** Wiener Neustadt

Tel: +43 (0)2622 23501-0  
parker.austria@parker.com

**AT – Eastern Europe,** Wiener  
Neustadt

Tel: +43 (0)2622 23501 900  
parker.easteurope@parker.com

**AZ – Azerbaijan,** Baku

Tel: +994 50 2233 458  
parker.azerbaijan@parker.com

**BE/LU – Belgium,** Nivelles

Tel: +32 (0)67 280 900  
parker.belgium@parker.com

**BG – Bulgaria,** Sofia

Tel: +359 2 980 1344  
parker.bulgaria@parker.com

**BY – Belarus,** Minsk

Tel: +375 17 209 9399  
parker.belarus@parker.com

**CH – Switzerland,** Etoy

Tel: +41 (0)21 821 87 00  
parker.switzerland@parker.com

**CZ – Czech Republic,** Klecany

Tel: +420 284 083 111  
parker.czechrepublic@parker.com

**DE – Germany,** Kaarst

Tel: +49 (0)2131 4016 0  
parker.germany@parker.com

**DK – Denmark,** Ballerup

Tel: +45 43 56 04 00  
parker.denmark@parker.com

**ES – Spain,** Madrid

Tel: +34 902 330 001  
parker.spain@parker.com

**FI – Finland,** Vantaa

Tel: +358 (0)20 753 2500  
parker.finland@parker.com

**FR – France,** Contamine s/Arve

Tel: +33 (0)4 50 25 80 25  
parker.france@parker.com

**GR – Greece,** Athens

Tel: +30 210 933 6450  
parker.greece@parker.com

**HU – Hungary,** Budaörs

Tel: +36 23 885 470  
parker.hungary@parker.com

**IE – Ireland,** Dublin

Tel: +353 (0)1 466 6370  
parker.ireland@parker.com

**IT – Italy,** Corsico (MI)

Tel: +39 02 45 19 21  
parker.italy@parker.com

**KZ – Kazakhstan,** Almaty

Tel: +7 7273 561 000  
parker.easteurope@parker.com

**NL – The Netherlands,** Oldenzaal

Tel: +31 (0)541 585 000  
parker.nl@parker.com

**NO – Norway,** Asker

Tel: +47 66 75 34 00  
parker.norway@parker.com

**PL – Poland,** Warsaw

Tel: +48 (0)22 573 24 00  
parker.poland@parker.com

**PT – Portugal,** Leca da Palmeira

Tel: +351 22 999 7360  
parker.portugal@parker.com

**RO – Romania,** Bucharest

Tel: +40 21 252 1382  
parker.romania@parker.com

**RU – Russia,** Moscow

Tel: +7 495 645-2156  
parker.russia@parker.com

**SE – Sweden,** Spånga

Tel: +46 (0)8 59 79 50 00  
parker.sweden@parker.com

**SK – Slovakia,** Banská Bystrica

Tel: +421 484 162 252  
parker.slovakia@parker.com

**SL – Slovenia,** Novo Mesto

Tel: +386 7 337 6650  
parker.slovenia@parker.com

**TR – Turkey,** Istanbul

Tel: +90 216 4997081  
parker.turkey@parker.com

**UA – Ukraine,** Kiev

Tel: +380 44 494 2731  
parker.ukraine@parker.com

**UK – United Kingdom,** Warwick

Tel: +44 (0)1926 317 878  
parker.uk@parker.com

**ZA – South Africa,** Kempton Park

Tel: +27 (0)11 961 0700  
parker.southafrica@parker.com

## North America

**CA – Canada,** Milton, Ontario

Tel: +1 905 693 3000

**US – USA,** Cleveland

Tel: +1 216 896 3000

## Asia Pacific

**AU – Australia,** Castle Hill

Tel: +61 (0)2-9634 7777

**CN – China,** Shanghai

Tel: +86 21 2899 5000

**HK – Hong Kong**

Tel: +852 2428 8008

**IN – India,** Gurgaon

Tel: +91 124 459 0600  
legris.india@parker.com

**JP – Japan,** Tokyo

Tel: +81 (0)3 6408 3901

**KR – South Korea,** Seoul

Tel: +82 2 559 0400

**MY – Malaysia,** Shah Alam

Tel: +60 3 7849 0800

**NZ – New Zealand,** Mt Wellington

Tel: +64 9 574 1744

**SG – Singapore**

Tel: +65 6887 6300

**TH – Thailand,** Bangkok

Tel: +662 186 7000-99

**TW – Taiwan,** Taipei

Tel: +886 2 2298 8987

## South America

**AR – Argentina,** Buenos Aires

Tel: +54 3327 44 4129

**BR – Brazil,** Sao Jose dos Campos

Tel: +55 800 727 5374

**CL – Chile,** Santiago

Tel: +56 2 623 1216

**MX – Mexico,** Toluca

Tel: +52 72 2275 4200

European Product Information Centre

Free phone: 00 800 27 27 5374

(from AT, BE, CH, CZ, DE, DK, EE, ES, FI,  
FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU,  
SE, SK, UK, ZA)

## Low Pressure Connectors Europe

Transair Business Unit

Parc Alcyone - 1, rue André et Yvonne Meynier

35000 Rennes - France

Tél : +33 (0)2 99 25 55 00

[www.parkertransair.com](http://www.parkertransair.com)

