


## SWVE-R Banjo elbow

EO 24° cone end / Male BSPP thread



Series	D1	Type	T	D3	D4	D5	L1	L2	L3	L4	L5	L6	S1	S2	S3	Weight g/1 piece	Order code*	PN (bar) <sup>1)</sup>	
																		CF	A3C
LL <sup>2)</sup>	04	B	G 1/8A	3.0	5.0	15	15.5	11.5	10.0	6	21.5	21	14	14	10	29	<b>SWVE04LLRKDSOMD</b>	250	250
	06	B	G 1/8A	4.5	5.0	15	15.5	10.0	10.0	6	21.5	22	14	14	12	30	<b>SWVE06LLRKDSOMD</b>	250	250
LL <sup>2)</sup>	04	A	G 1/8A	3.0	5.0	14	15.5	11.5	10.0	6	21.0	21	14	14	10	28	<b>SWVE04LLROMD</b>	63	63
	06	A	G 1/8A	4.5	5.0	14	15.5	10.0	10.0	6	21.5	22	14	14	12	28	<b>SWVE06LLROMD</b>	63	63
	08	A	G 1/8A	6.0	5.0	14	16.5	11.0	10.0	6	21.0	23	14	14	14	30	<b>SWVE08LLROMD</b>	63	63
L <sup>3)</sup>	06	A	G 1/8A	4.0	5.0	14	17.5	10.5	10.0	6	21.0	25	14	14	14	31	<b>SWVE06LROMD</b>	160	160
	08	A	G 1/4A	6.0	6.5	18	20.0	13.0	13.0	9	27.0	28	19	19	17	65	<b>SWVE08LROMD</b>	160	160
	10	A	G 1/4A	8.0	6.5	18	21.0	14.0	13.0	9	27.0	29	19	19	19	66	<b>SWVE10LROMD</b>	160	160
	12	A	G 3/8A	10.0	8.5	22	22.5	15.5	15.0	9	32.0	30	22	22	22	102	<b>SWVE12LROMD</b>	100	100
	15	A	G 1/2A	12.0	11.0	26	26.0	19.0	18.0	11	37.5	34	27	27	27	171	<b>SWVE15LROMD</b>	100	100
	18	A	G 1/2A	15.0	12.0	26	28.0	20.5	21.5	11	44.0	37	30	27	32	249	<b>SWVE18LROMD</b>	100	100
S <sup>4)</sup>	06	A	G 1/4A	4.0	6.5	18	22.0	15.0	13.0	9	27.0	30	19	19	17	69	<b>SWVE06SROMD</b>	160	160
	08	A	G 1/4A	5.0	6.5	18	22.0	15.0	13.0	9	27.0	30	19	19	19	73	<b>SWVE08SROMD</b>	160	160
	10	A	G 3/8A	7.0	8.5	22	23.5	16.0	15.0	9	32.0	32	22	22	22	108	<b>SWVE10SROMD</b>	100	100
	12	A	G 3/8A	8.0	8.0	22	24.5	17.0	18.0	9	37.0	33	24	24	24	147	<b>SWVE12SROMD</b>	100	100
	14	A	G 1/2A	10.0	11.0	26	28.0	20.0	18.0	11	37.0	38	27	27	27	177	<b>SWVE14SROMD</b>	100	100
	16	A	G 1/2A	12.0	12.0	26	30.0	21.5	21.5	11	44.0	40	30	27	30	249	<b>SWVE16SROMD</b>	100	100
	20	A	G 3/4A	16.0	18.0	32	35.0	24.5	24.0	13	49.0	46	36	32	36	359	<b>SWVE20SROMD</b>	100	100

<sup>1)</sup> Pressure shown = item deliverable

<sup>2)</sup> LL = very light series; <sup>3)</sup> L = light series; <sup>4)</sup> S = heavy series

$$\frac{PN \text{ (bar)}}{10} = PN \text{ (MPa)}$$

Delivery without nut and ring. Information on ordering complete fittings or alternative sealing materials see page 17.

Order code suffixes			
Material	Suffix surface and material	Example	Standard sealing material (no additional suffix needed)
Steel, zinc plated, chrome <sup>6</sup> -free	CF	SWVE16SROMDCF	
Steel, zinc yellow plated	A3C	SWVE16SROMDA3C	
Steel, zinc plated, chrome <sup>6</sup> -free	CF	SWVE06LLRKDSOMDCF	NBR
Steel, zinc yellow plated	A3C	SWVE06LLRKDSOMDA3C	NBR

\*Please add the **suffixes** below according to the material/surface required.