

# **Compact Fluid Power Systems**

Catalog HY22-1131/US

aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding



ENGINEERING YOUR SUCCESS.



FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS AND/OR SYSTEMS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors provide product and/or system options for further investigation by users having technical expertise. It is important that you analyze all aspects of your application and review the information concerning the product or system in the current product catalog. Due to the variety of operating conditions and applications for these products or systems, the user, through its own analysis and testing, is solely responsible for making the final selection of the products and systems and assuring that all performance, safety and warning requirements of the application are met.

The products described herein, including without limitation, product features, specifications, designs, availability and pricing, are subject to change by Parker Hannifin Corporation and its subsidiaries at any time without notice.

#### Offer of Sale

The items described in this document are hereby offered for sale by Parker Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions stated in the "Offer of Sale".

© Copyright 2016 Parker Hannifin Corporation, All Rights Reserved



| INTRODUCTION   |
|--|
| EHA CATALOG<br>Electro-Hydraulic Actuators for high power density applications   |
| <b>108-165 SERIES POWER UNITS</b><br>AC and DC Motors up to 5.3 lpm (1.4 gpm), up to 241 bar (3500 psi)  |
| <b>550 SERIES POWER UNITS</b><br>AC Motors, up to 14.4 lpm (3.8 gpm), up to 207 bar (3000 psi) 17-26   |
| MINIATURE PISTON AND 3-PISTON CARTRIDGE PUMPS * See Notice Below<br>AC and DC Motors, up to .865 cc/rev (.01 in <sup>3</sup> /rev), up to 276 bar (4000 psi) |
| DC MOTORS<br>Reversing controls suggestions  |
| <b>750 SERIES HAND PUMPS * See Notice Below</b><br>5.9 cc/stroke (0.5 in <sup>3</sup> /stroke), up to 172 bar (2500 psi), built-in 4-way Valve               |
| 09 SERIES HYDRAULIC GEAR MOTORS OBSOLETE<br>1.48 cc/rev (.09 in <sup>3</sup> /rev), up to 345 bar (5000 psi), up to 25000 rpm                                |
| PRESSURE SWITCHES * See Notice Below<br>Up to 345 bar (5000 psi), Single or Duplex Models  |
| OFFER OF SALE  |

### NOTICE

The HPS Division no longer manufactures these products. Please contact QCC for sales and support of these products.

QCC, LLC 7315 W. Wilson Avenue Harwood Heights, IL 60706 Contact: Brian Angioletti, Sales Manager Phone: 708.887.6241 Email: angioletti@qccorp.com

## **Oildyne Division**

The Oildyne Division of Parker Hannifin Corporation has been manufacturing top quality compact hydraulic products since 1955. Anywhere in the world where there is a need for a compact fluid power system solution requiring flows up to 14.4 liters per minute (3.8 gallons per minute) and pressure to 276 bar (4000 psi), or integrated electro-hydraulic actuators, Parker Oildyne can provide the answer from concept to completion. Parker Oildyne is a company dedicated to providing solutions for today's high pressure, space saving, and power-dense hydraulic installations.

Parker Oildyne's current state-of-the-art manufacturing facility has been in operation since January 1999. An ISO9001 approach to delivering premium customer service is supported by a dedicated team of design, manufacturing and quality engineers using the latest technologies and equipment. Parker Oildyne pioneered the miniaturization of hydraulic components and offers this expertise to you.

Parker Oildyne products are used in a large range of diverse industries such as marine equipment, recreational vehicles, automotive, medical, material handling, construction equipment, turf care, industrial equipment and many more. Expand your hydraulic usage with compact fluid power systems from Parker Oildyne.

Note: Oildyne products are designed to industrial standards; they are not to be used in aircraft applications.





# **Compact EHA**

Electro-Hydraulic Actuators for high power density applications

aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding



ENGINEERING YOUR SUCCESS.

### Electro-Hydraulic Actuators Compact EHA

#### Easy to Install and Connect

Compact EHA is designed to make commissioning as simple as possible. The motor is connected to a suitable power supply and switching circuit, and the rod or base end is secured with a pivot pin. The unit is then actuated to align the opposite pivot pin connection, and the pin inserted to secure. And that's it - your Compact EHA is ready for use.



#### Maintenance

Because the Compact EHA is flushed, filled and sealed for life, there is virtually no maintenance required. This, in combination with the anodized housing, stainless steel rod and rugged seals and components, provides a longer service life with reduced warranty costs.

### **Complete Compact EHA Solutions**

In addition to custom actuators, our engineers are experienced in the design of complete actuation systems. Where your requirement includes cable harnesses, switchgear and power supplies, please contact us for further information.

For current Compact EHA literature, please call 1-800-CParker (1-800-272-7537) or e-mail to c-parker@ parker.com and ask for Catalog Number HY22-3101.

### **Specifications**

#### Actuator

| Туре                    | hyd  |
|-------------------------|------|
| Bore sizes              | 25.4 |
|                         | 36.  |
| Standard stroke lengths | 102  |
|                         | 203  |
| Piston rod diameters    | 14.2 |
|                         | 19.1 |
| Standard mounting       | 6.4  |
| pin diameters           | 12.7 |
| Motor                   |      |
| Motor types             | 12V  |
|                         | 12V  |
|                         | 24V  |
|                         | 24V  |
| Leads – length          | 1.5r |
| Leads – gauge           | 14 g |
|                         | 12 ( |
| Connector type          | ring |

Pump

Pump type Pump capacities

Iraulic, double-acting 4mm (1.0 in), 31.8mm (1.25 in), 5mm (1.44 in) 2mm (4 in), 152mm (6 in), 3mm (8 in) 2mm (.561 in), 15.9mm (.625 in), 1mm (.750 in) mm (.250 in), 9.5mm (.375 in), 7mm (.500 in)

/ DC, 245W (motor A) / DC, 560W (motor B) / DC, 245W (motor C) / DC, 560W (motor D) m (60 in) gauge (motors A & C) gauge (motors B & D) ring terminals, 6.6mm (.26 in) I/D

gear, reversible  $.100 \text{ gear} = .16 \text{ cc/rev} (.010 \text{ in}^3/\text{rev})$ .190 gear = .31cc/rev (.019 in<sup>3</sup>/rev) .250 gear = .41cc/rev (.025 in<sup>3</sup>/rev) .327 gear = .53cc/rev (.032 in<sup>3</sup>/rev) automatic transmission fluid (ATF)

Fluid medium

#### Circuit

Sealed hydraulic circuit with integrated pump, motor, actuator and reservoir, relief, thermal, check and back pressure valves.

#### **Certification and Testing**

| Vibration                |                                   |
|--------------------------|-----------------------------------|
| (minimum integrity test) | MIL-STD-810F                      |
| Sealing                  | IP65 and IP67                     |
| Salt spray               | 1000 hours per ASTM B117          |
| CE marked                | in conformity with Machinery      |
|                          | Directive 98/37/EC and 2007/42/EC |

For other application-specific approvals, please consult factory.

#### Performance

| Maximum force – extend  | 21.35kN (4800 lbf)    |
|-------------------------|-----------------------|
| Maximum force – retract | 16.00kN (3600 lbf)    |
| Maximum speed           | 84mm/sec (3.3 in/sec) |

#### General

Construction - body one-piece-piston rod Orientation universal Manual release option Operating temperature range Sound Level Weight

anodized cast aluminium, stainless steel retained, for emergency use only -34°C (-30°F) to +65°C (150°F) < 70 dBA under 5.5 kg (12 lbs)









# Oildyne 108/118 and 165/175 Series Hydraulic Power Units

Pressures to 241 bar (3500 psi) Flow to 5.3 lpm (1.4 gpm) aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding



ENGINEERING YOUR SUCCESS.

## **Typical applications**

#### Positioning

- Hydraulic door operators
- Conveyor belt tensioners
- Medical chairs, beds, and equipment

#### **Recreational Vehicles**

- Leveling
- Slideouts
- Tent Trailers

#### Clamping

- Tool fixtures and jigs
- Hydraulic brakes
- Crimping tools
- Arbor presses
- Truck restraints

#### Cycling

- Garbage compactors
- Valve operators
- Press controls
- Packing equipment
- Indexing tables

#### Lifting

- Handicap lifts
- Scissor lift tables
- Pallet movers
- Cab tilts
- Mobile sign lifts
- Boat lifts

Bi-directional, reversible units operate doubleacting cylinders and two-way motors.

New are the 118 and 175 Series codes. Instead of the standard threaded ports, these new versions provide a four-bolt, flat manifoldable surface to accept the solenoid manifold circuit or your custom manifold.

We'd like to work with you on your hydraulic applications. Our people know small hydraulics. We know how to design them, how to make them and how to apply them. Therefore, we can offer you a practical, economical solution to your fluid power problems.

Oildyne has pioneered top quality, compact hydraulic components since 1955. We can provide standard products or tailor high pressure, space saving solutions to your specific needs.

Note: Parker Oildyne products are not to be applied in aviation applications.



## 108 and 165 Series Self-contained Hydraulic Power Units

The Oildyne Division's compact 108/165 Series power units let you put the power where you need it. They're completely self-contained with an AC or DC motor, gear pump, reservoir, internal valving, load hold checks and relief valves.

The 108/165 Series models are designed for intermittent service and come in six standard pump sizes which produce flows of .16, .31. .41, .52, .82 and 1.06 cc/rev (.0098, .0187, .0246, .0321, .050 and .065 cubic inches/rev). Locking check valves are available in all models. Performance will vary with the type of fluid used. Several hydraulic circuits are available.

108/165 Series units are available with single- or bi-directional rotation. Single direction units are commonly used to charge accumulators, power one-direction hydraulic motors and cylinders, provide pilot flow to servo valves, pressurize lube systems and supply multifunction circuits using external valving.



#### **Standard Product Ordering Code** DN RV SETTING PRODUCT TYPE (Right Hand Port) 108 108 Power Unit 118 118 Power Unit In multiples of 100 psi 165 165 Power Unit Examples 175 175 Power Unit 04 = 400 psi12 = 1200 psi **MOTOR CODE - 108/118** 29 = 2900 psi AE 12 VDC Perm. Mag. If Single Direction circuit AM 12 VDC Ser. Wnd. use 00 BE 24 VDC Perm. Mag. 24 VDC Ser. Wnd. BI UP RV SETTING HA 115 VAC, 1 phase (Left Hand Port) HD 230 VAC, 1 phase 36 VDC Perm. Mag. In multiples of 100 psi IA Examples 36 VDC Ser. Wnd. IC 04 = 400 psi **MOTOR CODE - 165/175** 12 = 1200 psi AY 12 VDC Perm. Mag. 1 HP 29 = 2900 psi BY 24 VDC Perm. Mag. 1 HP PUMP TYPE MOUNTING S Standard V Vertical (motor up) Ċ Cold Temp Horizontal (ports up) н **PUMP SIZE 108/118** PORTS 10 .16 cc/rev (.010 in3/rev) 7/16-20 (SAE -4) (108 & 165 only) 1 19 .31 cc/rev (.019 in3/rev) 7/16-24 (Inv. Flare) (108 only) 2 25 .41 cc/rev (.025 in3/rev) 1/8 in Pipe (NPSF) (108 only) 3 32 1/8 in Pipe (BSPP) (108 & 165 only) .52 cc/rev (.032 in<sup>3</sup>/rev) 4 Note: for 118 or 175, use -1 for SAE mounting; **PUMP SIZE 165/175** use -4 for Metric mounting 32 .52 cc/rev (.032 in3/rev) 50 .82 cc/rev (.050 in3/rev) **CIRCUIT TYPE** 65 1.06 cc/rev (.065 in3/rev) NN Single direction WW Single dir. with check RESERVOIRS RR Reversible Vertical Usable CODE Horizontal Usable Reversible locking 11 21 in<sup>3</sup> 340 cc 410 cc 25 in<sup>3</sup> Α Reversible with Back Press. RB 600 cc 37 in<sup>3</sup> 640 cc 37 in<sup>3</sup> В I B Rev. lock, with Back Press. 410 cc 25 in<sup>3</sup> С N/A Each Solenoid Valve option below includes the WW circuit: 25 in<sup>3</sup> N/A 410 cc D Use 118 or 175 when coding solenoid valve circuit 95 in<sup>3</sup> 1500 cc F 1500 cc 92 in<sup>3</sup> Coils have dual leads: 18 ga, 457 mm (18") 750 cc 46 in<sup>3</sup> G 910 cc 55 in<sup>3</sup> 12 VDC, Normally Closed S1 1700 cc 104 in<sup>3</sup> Н 2400 cc 150 in<sup>3</sup> 24 VDC, Normally Closed S2 3700 cc 226 in<sup>3</sup> 4200 cc 1 254 in<sup>3</sup> S3 120 VAC, Normally Closed (108/118 only) 5300 cc 323 in<sup>3</sup> J 5600 cc 347 in<sup>3</sup> S4 240 VAC, Normally Closed (108/118 only) 950 cc 58 in<sup>3</sup> Р 58 in<sup>3</sup> 940 cc S5 12 VDC, Normally Open 118 in<sup>3</sup> Q 95 in<sup>3</sup> 1900 cc 1500 cc 24 VDC, Normally Open S6 4500 cc 277 in<sup>3</sup> R 3000 cc 185 in<sup>3</sup> **S**7 120 VAC, Normally Open (108/118 only) 3200 cc 201 in<sup>3</sup> S 2300 cc 141 in<sup>3</sup> <u>S8</u> 240 VAC, Normally Open (108/118 only) NOTES: C and D reservoirs are Vertical Mount only A, B and F reservoirs are available only for 108/118 Series Reservoir A with .32 pump cannot be horizontal mount

#### **ORDERING CODE INSTRUCTIONS**

Select the model code needed based on catalog information. All boxes above must be filled in before Oildyne can process the order. If the power unit is a single direction unit use '00' for the DN (Right Hand) relief valve box. For circuits LL and LB, the two relief valve settings should be within a 5:1 ratio.

#### **RELIEF VALVE TOLERANCES**

| Pressure Range Bar      | 14 to 34.4 | 35 to 68.9 | 70 to 137.9  | 138+     |
|-------------------------|------------|------------|--------------|----------|
| Pressure Range PSI      | 200 to 499 | 500 to 999 | 1000 to 1999 | 2000+    |
| Tolerance +/- (bar/psi) | 5.2/75     | 6.9/100    | 10.3/150     | 13.8/200 |

### **Hydraulic Fluid**

Acceptable fluids for 108/118/165/175 Series Power Units:

- Standard Automatic Transmission Fluid (ATF)
- Most mineral based hydraulic fluids

Viscosity range: 32-64 cSt (150-300 SSU) at 38°C (100°F).

#### **Temperature Range**

 Temperature Ranges for 108/118/165/175 Series:

 Operating:
 -7 to +60°C (+20 to +140°F)

 Storage:
 -7 to +60°C (+20 to +140°F)

 Please contact Parker Oildyne for usage outside of this range.

ALL DATA SUBJECT TO CHANGE WITHOUT NOTICE FOR POWER UNIT CONFIGURATIONS OTHER THAN THOSE SHOWN PLEASE CONSULT OILDYNE.





Performance data for reference only. Based on ATF at 21°C (70°F)





Performance data for reference only. Based on ATF at 21°C (70°F)





### 108/118 Series: AC Motors - HA/HD

### **108/118 Series HA Motors (115 VAC)** 1) For Single Direction only, and Reversible with UP port pressure:



### **115 VOLTAGE CONNECTION**

108/118 Series HD Motors (230 VAC)

1) For Single Direction only, and Reversible with UP port pressure:



For electrical controls suggestions, see page 36. To reverse rotation, interchange the Black and Red wires. Performance data for reference only. Based on ATF at 21°C (70°F)







## **Single Direction Circuits**



108/165 Series Single Direction NN Circuit



108/165 Series Single Direction WW Circuit



118 and 175 Series S1 - S4 Circuit (N.C. valve) S5-S8 Circuits use N.O. Valves

## Thermal Relief Valves – Why?

The thermal relief valve's (TRV) purpose is to allow a bleed off of built up pressure due to thermal expansion of the fluid or to act as a (very limited) shock load protection, should a cylinder in the system get bumped.

The thermal relief valve is included in circuits using a pilot operated check valve. The single direction units get one; the reversing units get two. It is located between the check valve and the 108 Series pump outlet port. It is a fixed relief valve with a pressure setting approximately 100-140 bar (1500-2000 psi) above the system relief valve pressure.



## **Reversible Circuits**



108/118 and 165/175 Series RR Circuit (Reversible)

**Note:** Back Pressure circuits (RB and LB) require the UP ports to be connected to the extend ports of cylinders.



108/118 and 165/175 Series RB Circuit (Reversible with Back Pressure)

### **Back Pressure Circuits –** Why?

The basic reversible circuit is essentially a closed loop. The oil returning from the system is fed back into the pump inlet. When a cylinder is being retracted more oil is being returned to the power unit than is leaving it due to the rod volume. This results in the DN side relief valve cracking open allowing the rod volume of oil to go back to the tank. The larger the rod volume the more open the relief valve will be. In many applications this is not a problem. However, if work is being done on the retract stroke, or if a pressure switch is used to signal the cylinder is fully retracted, the back pressure circuit is required. This circuit allows the rod volume of oil to return



108/118 and 165/175 Series LL Circuit (Reversible Locking)



108/118 and 165/175 Series LB Circuit (Reversible Locking with Back Pressure)

to the reservoir through a special shuttle spool, before it reaches the pump. Full relief valve pressure is then available to retract the cylinder, also preventing a pressure switch from tripping before the full retract position is achieved.

Recommended uses:

- In systems where work is being done on the retract stroke
- Where a pressure switch is used to signal the full retract position
- In systems requiring a faster retract than extend speed



### **Reservoir Dimensions**





Note: All dimensions in mm (inches).

(4.45)



# **108 Series shown with Series Wound motor and "A" reservoir**





Parker Hannifin HPS Division New Hope, MN 55428 USA







# Oildyne 550 Series Hydraulic Power Units

Pressures to 207 bar (3000 psi) Flow to 14.4 lpm (3.8 gpm) aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding



ENGINEERING YOUR SUCCESS.

## 550 Series Hydraulic Power Units

The 550 Series combines the features and benefits our customers and markets have requested in a durable and economical package. The integral motor, pump and reservoir are complemented with a full line of Parker D03/NG6 and cartridge valve options. Add a linear or rotary actuator and you have a complete hydraulic system solution for your application.

These high quality power units are ideal for industrial machine tool clamping circuits, dock levelers, food processing, hose crimping, scissor lift, presses, and a myriad of AC applications. Let them go to work for you.

Your local Parker sales representative will be pleased to provide further information.

## **Typical Applications**

- Machine tool clamping
- Dock levelers
- Man lifts
- Scissors lifts
- Wheelchair lifts
- Trash compactors
- Hose crimpers
- Boat lifts
- Presses
- Commercial ovens



### **Features**

- Numerous motors from .67 to 4 kW (.5 to 3 HP)
- 7 pump sizes flows from 1 to 14.4 lpm (.25 to 3.8 gpm)
- Externally adjustable relief valve
- Variety of reservoirs
- 207 bar (3000 psi) capability
- D03/NG6 pad or standard P and T ports
- Vertical and horizontal mounting







Performance data based on ATF @ 21°C (70°F)

|              | Nomin | al GPM |             |                             | Pressure      | Bar (PSI)     |               |               |
|--------------|-------|--------|-------------|-----------------------------|---------------|---------------|---------------|---------------|
| Pump<br>Size | @1725 | @3450  | 34<br>(500) | 69<br>(1000)                | 103<br>(1500) | 138<br>(2000) | 172<br>(2500) | 207<br>(3000) |
| 04           | 1⁄4   |        | .50 HP      | .50 HP                      | .50 HP        | .50 HP        | .50 HP        | .75 HP        |
| 04           |       | 1/2    | .50 HP      | .50 HP                      | .50 HP        | .75 HP        | 1.0 HP        | 1.5 HP        |
| 07           | 1⁄2   |        | .50 HP      | .50 HP                      | .50 HP        | .75 HP        | 1.0 HP        | 1.0 HP        |
| 07           |       | 1      | .50 HP      | .75 HP                      | 1.0 HP        | 1.5 HP        | 2.0 HP        | 2.0 HP        |
| 10           | 3⁄4   |        | .50 HP      | .50 HP                      | .75 HP        | 1.0 HP        | 1.5 HP        | 1.5 HP        |
| 10           |       | 1 ½    | .75 HP      | 1.0 HP                      | 1.5 HP        | 2.0 HP        | 3.0 HP        | 3.0 HP        |
| 14           | 1     |        | .50 HP      | .75 HP                      | 1.0 HP        | 1.5 HP        | 2.0 HP        | 2.0 HP        |
| 14           |       | 2      | 1.0 HP      | 1.0 HP 1.5 HP 2.0 HP 3.0 HP |               |               |               |               |
| 17           | 1 1⁄4 |        | .50 HP      | 1.0 HP                      | 1.5 HP        | 2.0 HP        | 2.0 HP        |               |
| 17           |       | 2 1/2  | 1.0 HP      | 2.0 HP                      | 3.0 HP        |               |               |               |
| 20           | 1 ½   |        | .50 HP      | 1.0 HP                      | 1.5 HP        | 2.0 HP        |               |               |
| 20           |       | 3      | 1.0 HP      | 2.0 HP                      | 3.0 HP        |               |               |               |
| 26           | 1.9   |        | .75 HP      | 1.5 HP                      | 2.0 HP        |               |               |               |
| 26           |       | 3.8    | 1.5 HP      | 3.0 HP                      |               |               |               |               |

#### Motor Horsepower Recommendations at Flow/Pressure

Note: Performance data is for reference only



## **Standard Product Ordering Code**





#### **Hydraulic Fluids:**

Standard Automatic Transmission Fluid (ATF) Most mineral based hydraulic fluids

Viscosity range: 32-64 cSt (150-300 SSU) at 38°C (100°F) Please contact Parker Oildyne to discuss any alternate fluids.

#### **Temperature Ranges:**

Operating: -7 to 60°C (+20 to 140°F) -10 to 60°C (+14 to 140°F)









"S1-S4, P1-P4" CIRCUITS



"S5-S8, P5-P8" CIRCUITS

















550 Series shown with 19 liter (5 gallon) steel reservoir and NG6/D03 valves



### NOTICE

HPS Division can no longer accept new purchase orders for Miniature Piston Pumps 5 Piston & Cartridge Design.

Please contact QCC for sales and support of these products.

QCC, LLC 7315 W. Wilson Avenue Harwood Heights, IL 60706 Contact: Brian Angioletti, Sales Manager Phone: 708.887.6241 Email: angioletti@qccorp.com



# Miniature Piston Pumps 5 Piston & Cartridge Design

Pressures to 276 bar (4000 psi) Displacements from .156 to .865cc/rev (.01 to .05 in³/rev)

ON PUMP

aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding



ENGINEERING YOUR SUCCESS.

# Miniature Piston Pumps: Pumping Efficiencies up to 90% Allow Effective Use of .156 to .865 cc/rev Piston Pumps at Pressures to 276 bar (4000 psi)

Breakthrough designs come and go, succeed and fail. The really good designs pass the test of time and continue to succeed. The Oildyne Division mini pump is one of these good designs.

Mini pumps handle hydraulic oil, brake fluid, ultra-low viscosity fluids and many nonwater based fluids with equal ease. Need greater versatility?

These fixed displacement axial piston pumps are efficient and powerful too. Tests run on 15.1 cSt (78 SSU) fluid at 38°C (100°F) at 207 bar (3000 psi) showed a 90% volumetric

efficiency. Capable of 276 bar (4000 psi) operation, mini pumps are available in nine displacements ranging from .156 to .865 cc/rev (.01 to .053 in<sup>3</sup>/rev).

Compact size, versatility, efficiency, power and speed are combined in a very competitive package in the Oildyne mini pumps. They're suitable for many applications requiring compact power including automotive, marine, medical and military uses.

#### **Mini Pump Features**

- .156 to .865 cc (.01 to .053 in<sup>3</sup>) displacement per revolution
- Designed for open circuit systems
- Fixed displacement Output flow is determined by motor drive speed.
- Operating temperature range: -40° to +149°C (-40° to 300°F)
- Inlet port on side or rear
- Will operate efficiently on extremely thin (5 cSt) fluid
- Tandem pumps, special configurations and bi-rotational pumps are available.

### Cartridge Piston Pumps: Compact Fluid Power Redefined by the Oildyne Division.

This cartridge piston pump raises the standard for compact fluid power! This three-piston cartridge style pump is an efficient, fixed displacement pump that provided high performance at a very economical price. Pressure ratings up to 276 bar (4000 psi), driven speeds up to 5000 RPM, and the ability to provide a variety of seal types make this the solution to your unique application. This uni-rotational pump is capable of pumping non-water based fluids ranging in viscosity from solvents to thick fluids.

The three-piston cartridge pump maintains the performance and flexibility of the Oildyne five-piston, standalone pump while reducing the overall package dimensions.

This ultra-compact cartridge piston pump, approximately

33 mm (1.3 in) in diameter and 51 mm (2 in) long, is designed to fit into your specially machined manifold allowing for a custom package that fits your space needs.

Three standard displacements are available all within the existing physical size. (The internal cam angle determines the displacement).

Contact Oildyne Division for a drawing showing the cavity details as well as the motor shaft and flange details needed for your motor to drive and mount this pump to your manifold.

#### **Cartridge Pump Features**

- .1 to .33 cc (.006 to .020 in<sup>3</sup>) displacement per revolution
- Designed for manifold mounting
- Fixed displacement Output flow is determined by motor drive speed.
- Operating temperature range: -40° to +149°C (-40° to 300°F)
- Will operate efficiently on extremely thin (5 cSt) fluid
- Counter clockwise rotation
   (from pump drive end)

See Page 34 for Cartridge Pump ordering code







V

Pump

Your Manifold Package



### Catalog HY22-1131/US Technical Specifications



### 5. For configurations not shown above please contact Oildyne

### **Miniature Piston Pump Basic Specifications**

| Model                                       | 156           | 206           | 259           | 311           | 346           | 417           | 519           | 692           | 865           |  |  |  |
|---|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|--|--|--|
| Displacement                                |               |               |               |               |               |               |               |               |               |  |  |  |
| In <sup>3</sup> per rev.                    | .0095         | .0126         | .0158         | .0190         | .0211         | .0255         | .0317         | .0422         | .0527         |  |  |  |
| cc /rev                                     | .156          | .206          | .259          | .311          | .346          | .417          | .519          | .692          | .865          |  |  |  |
| Max RPM @ rated pressure<br>W/O supercharge | 4400          | 4200          | 4000          | 3800          | 3800          | 3700          | 3700          | 3600          | 3500          |  |  |  |
| Operating Pressure (psi)                    |               |               |               |               |               |               |               |               |               |  |  |  |
| Continuous bar (psi)                        | 241<br>(3500) | 224<br>(3250) | 207<br>(3000) |  |  |  |
| Intermittent bar (psi)                      | 258<br>(3750) | 241<br>(3500) | 241<br>(3500) |  |  |  |
| Maximum bar (psi)                           | 276<br>(4000) | 258<br>(3750) | 241<br>(3500) |  |  |  |



Performance data shown are the average results based upon a series of laboratory tests of production units and are not necessarily representative of any one unit. Tests were run with 15.1 cSt (78 SSU) fluid. In accordance with our policy of continuing product development, we reserve the right to change specifications shown without notice.



Note: Performance data is for reference only.





Note: Performance data is for reference only.





AC Motor and Miniature Piston Pump Performance



NOTES:

The 115 VAC performance shown is at 60 Hz. At 230 VAC the current draw will be approximately  $\frac{1}{2}$  of that shown.

At 250 VAC the current draw will be approximately ½ of that shown. At 50 Hz, the flow will be about 5/6 of that shown and the current will be about 25% higher than the 60 Hz values. Performance data shown is for reference only.



Dimensions



### Standard 1/3 HP DC Permanent Magnet Motor with Pump



### Standard 1/3 HP AC Motor with Pump







**Tandem Miniature Piston Pump** 

**SEE NOTICE ON PAGE 27** 

Note: tandem pumps are not completely isolated from each other. Note: All dimensions in mm (inches)

С L 00 COMPONENT SHAFT/MOTOR С Cartridge Piston Pump 00 No motor or shaft ROTATION SEALS в CCW Buna N L (from shaft input end) ۷ Fluorocarbon Е EPR PUMP SIZE CODE DISP. 050 .17 cc/rev 075 .25 cc/rev





.33 cc/rev

100

CL100 (.33 cc/rev)

1.41

1.27

1.13

0.99

0.85

0.71 **y** 

0.56

0.42

0.28

0.14

0

220

CL075 (.25 cc/rev)

CL050 (.17 cc/rev)

(M-M)

orgu

Cartridge pump input torque

at 23°C on DOT 3 brake fluid



### **Cartridge Piston Pump Performance**

200

180

160

140

**Torque** (in-oz) 100 80 00

40

20

0

0 20 40 60 80

## **Specifications**

Displacements: .1 cc/rev. (.006 in<sup>3</sup>/rev.) to .33 cc/rev. (.020 in<sup>3</sup>/rev.)

Speeds: Up to 5000 rpm maximum

Pressures: 207 bar (3000 psi) maximum continuous 276 bar (4000 psi) maximum intermittent

Temperature Ranges: Up to 120°C (250°F)

Seals Available: Variety

Weight: .19 kg (.42 lbs)

Fluids Compatibility: Variety, not water-based

Specifications subject to change without notice. Performance data is for reference only. This cartridge piston pump continues Oildyne's tradition of producing innovative products which can be customized to specific industries. Please call us to discuss how this cartridge pump can be used in your unique application. **Detailed cavity and motor interface dimensions are available on request. Ask for Oildyne drawing 500059** 

100 120 140 160 180 200

Pressure (Bar)

## **Cartridge Pump Dimensions**

(with sample manifold requirements) All dimensions in **mm** (inches)



-- Parker

Catalog HY22-1131/US

### **Reversing Motors Controls Suggestions**

Suggested reversing electrical schematics

### Oildyne 108/118 and 165/175 Series Hydraulic Power Units



**NOTE:** If a Double Pole, Double Throw toggle switch with a current rating for your application is not available, refer to the "108/118 AE/BE/IA and 165/175 Motors" below for a possible reversing circuit using control relays.









**NOTE:** The UP port corresponds to the Left Hand Port Flow in these schematics. The DN port corresponds to the Right Hand Port Flow. 108/118/165/175 Series power unit castings are marked above the pressure ports UP and DN.





QCC, LLC 7315 W. Wilson Avenue Harwood Heights, IL 60706 Contact: Brian Angioletti, Sales Manager Phone: 708.887.6241 Email: angioletti@qccorp.com

# **750 Series Hand Pumps**

Pressures to 172 bar (2500 psi) Handle Force at 610 mm (24"): 1kg/6.9 bar (2.2 lbs/100 psi) Temperature Range: -34 to 100°C (-30 to 212°F) aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding



Catalog HY22-1131/US
Technical Information

Hand Pump with 2-Way Valve 750 Series Hand Pumps

### **Hand Pump Dimensions**



NOTE: All dimensions in **mm** (inches)

38.1

(1.5)





### Model 750-1 Hand Pump

- 8.2 cc/Stroke (.5 in<sup>3</sup>/Stroke)
- Suitable for use in Single Acting Cylinder circuits
- Metering release valve for controlled return of fluid
- Weight: .91 kg (2 lbs) pump only

Note: Specifications subject to change without notice.



## **Hand Pump Dimensions**



Note: Specifications subject to change without notice.





118/175 Series Single Direction with 2-way valve



Application example for 750-2 Hand Pump

750-2 Hand pump used with a reversible locking power unit





#### **Motor Data**

.....OBSOLETE PRODUCT......

Rotation - Bi Directional Displacement - 1.48 cc/rev (.09 cipr) Torque - Approximately 1.47 Nm/70 bar (13 in-lbs/1,000 psi) Starting Torque - Approximately 1.36 Nm/70 bar (12 in-lbs/1,000 psi) Static Slip - 541 cc/70 bar (33 CIPM/1,000 psi)

# 09 Series Hydraulic Gear Motor

Pressures to 276 bar (4000 psi) Speeds to 20,000 rpm Torque to 6.1 Nm (54 in-lbs) Concentric Center Drive Face or Flange Mounting Instantly Reversible Variety of Shaft Options Compact Size aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding



ENGINEERING YOUR SUCCESS.

#### Performance .....OBSOLETE PRODUCT...... **Shaft Options 09 Series Hydraulic Motor** #403 KEY 6.78-(60) Output Torque - N-m (in.-lbs.) **5.65** (50) 276 bar (4000 psi) **29,2** (1.15 **4.52** (40) STANDARD CARTRIDGE SHAFT 1/2 BLANK SHAFT (K) 207 bar (3000 psi) (M) **3.39** (30) 3/8 FLATS 138 bai (2000 psi) **2.26** (20) 69 bar (1000 psi) **1.13** (10) 29,2 (1.15) 0 3/8 - 24 CHUCK ADAPTER SHAFT 7/8 BLANK SHAFT 0 5000 10000 15000 20000 25000 (Q) (L) Speed - RPM Note: All dimensions in mm (inches). **Dimensions 5,56** (Ø.219) 4 HOLES ON 1.562 B.C. 5,56 (Ø.219) 8-32 UNF - 2B -3 HOLES 120° APART 7,1 (.28) 2,5 (.10) HOLES ON 1.562 B.C. 3X SHCS 8 - 32 X ¥.5 ON 1 562 B C (E) 31,68 - 31,75 (Ø1.247 - 1.250) (Ø 66,7 Ø2.63) **66,68** (Ø2.625) UNIVERSAL CARTRIDGE FOR - 3X SHCS 8 - 32 X ∓.5 RADIAL AND AXIAL LOADS FLANGE MOUNT FOR UNIVERSAL CARTRIDGE 2,3 (.09) 11.1 (STANDARD CARTRIDGE SHAFT (K) SHOWN) (.437) (C) (G) 23,8 FLANGE MOUNT FOR BASIC MOTOR APPLICATION 3,97-4,01 (.156-.158) (.937) (F) M5X0.8X ↓.51 3 HOLES 120° APART ON 1.700 B.C 6,5 (.26) 7,928 - 7,934 (Ø.3121 - .3124) \_ 2X SAE6 PORT 9/16 - 18 UNF - 2B **28,50 - 28,54** (Ø1.122 - 1.124) **50,2** (Ø1.98) 1/8 NPT **3,2** (.13) CASE DRAIN 75,8 (2.99) (D) STANDARD BASIC MOTOR TANG-DRIVE BASIC MOTOR DIMENSIONS NO RADIAL LOAD OR AXIAL LOAD (S) **Standard Product** (09)**Ordering Code** 09 S-G-C K-P AXIAL LOAD Basic Motor = Ø**Basic Motor** Cartridge = 9.1 kg 09 (20 lbs.) max Seals (Fluid) Porting $\begin{array}{l} \mathsf{A} \ - \ \widetilde{\mathsf{Auto}} \ \mathsf{Case} \ \mathsf{Drain} \\ \mathsf{S} \ - \ \mathsf{Case} \ \mathsf{Drain} \end{array}$ P — Oil RADIAL LOAD Single Rotation Only T — Other (Specify) Basic Motor = Ø(Specify Rotation Cartridge = 23 kg From Shaft End) Shaft (50 lbs.) max Mounting B - Basic Motor Shaft D - Face Mounting **Basic Motor** K - Cartridge Shaft Extension - Std. E - Face Mounting Cartridge Motor \_ L - Cartridge Shaft Extension - 3/8-24 F - Flange Mounting Basic Motor M - Cartridge Shaft Extension - 1/2" Blank — G - Flange Mounting Cartridge Motor Q - Cartridge Shaft Extension - 7/8" Blank

#### Cartridge -

- C Universal Cartridge
- N Basic Motor W/O Cartridge

Note: Specifications subject to change without notice. Performance data is for reference only.





NOTICE

HPS Division can no longer accept new purchase orders for pressure switches, subplates and related components. Please contact QCC for sales and support of these products.

QCC, LLC 7315 W. Wilson Avenue Harwood Heights, IL 60706 Contact: Brian Angioletti, Sales Manager Phone: 708.887.6241 Email: angioletti@qccorp.com

# **Pressure Switches for AC Power**

3.4-345 bar (50-5000 psi) Range

aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding



ENGINEERING YOUR SUCCESS.

## **Pressure Switch Features**

#### Versatile

Our designs allow the switches to be used in any mounting orientation. They can sense hydraulic fluid pressure or air/gas pressure. A simple spring change allows the same basic switch to be used through a wide range of pressure settings.

#### Durable

Heavy-duty electrical contacts are rated for 15 amps at 125, 250 or 460 VAC. Normally open and normally closed contacts are provided.

#### Reliable

Repeatability is accomplished through a combination of a PTFE seal and a hardened, nickel-plated steel piston. This use of low-friction materials and the design of the unique PTFE seal (or diaphragm\*) prevents the piston from sticking. Repeatability, sensitivity and reliability are excellent. Limited piston movement prevents inertial forces from damaging the piston stop.

## **Typical Applications**

Pressure switches sense when a pre-selected fluid pressure is reached or lost and make or break an electrical circuit. Their operation can stop or start a machine's cycle, actuate indicator lights or sequential operations. Properly installed, their operation is automatic and limited by your imagination and need.

#### Spring Range

Duplex models contain two separate switches which can be activated by one or two sensing ports depending on the subplate configuration. See dimensional data for options.

#### Environmentally Resistant

Environmentally resistant models are available on special order.

## **Subplates**

Subplates are available for in-line mounting of Oildyne pressure switches. This allows further flexibility in mounting to existing equipment. Ports in 1/8 NPT or 7/16-20 (SAE-4) straight thread are standard. The duplex switch has two types of subplates, one with a port for each side of the switch, the other with one port only, for both sides of the switch.





## **Dimensions**

# Single Pressure Switch



### **Duplex Pressure Switch**



Wiring



Note: All dimensions in mm (inches).

## Weight

Single Standard .3 kg (10 oz.)

Subplates (Single & Duplex)

### **Duplex**

Standard .4 kg (14 oz.)

## **Electrical Duty**

Single pole, double throw element, U.L. rated for 15 amps at 125, 250 or 460 VAC. Electrical leads are not furnished with the switch.

## **Recommended Oil**

Any clean hydraulic fluid. Standard Buna N seals supplied, optional fluorocarbon rubber seals also available.



### **Spring Selection Guide**

| Spring<br>Number | Spring<br>Range | Adjustment<br>Range | Repeatability<br>Plus or Minus | Differential<br>Range | Spring<br>Color |
|------------------|-----------------|---------------------|--------------------------------|-----------------------|-----------------|
| 1                | 50 - 100 psi    | 50 to 100 psi       | 2 psi                          | 50 to 90 psi          | Green           |
| 2                | 100 - 300 psi   | 75 to 300 psi       | 4 psi                          | 50 to 100 psi         | Black           |
| 3                | 300 - 500 psi   | 150 to 500 psi      | 5 psi                          | 50 to 125 psi         | Red             |
| 4                | 500 - 1000 psi  | 200 to 1000 psi     | 8 psi                          | 50 to 150 psi         | Blue            |
| 5                | 1000 - 2000 psi | 300 to 2000 psi     | 15 psi                         | 75 to 250 psi         | White           |
| 6                | 2000 - 3000 psi | 400 to 3000 psi     | 20 psi                         | 75 to 250 psi         | Yellow          |
| 7                | 3000 - 4000 psi | 500 to 4000 psi     | 25 psi                         | 125 to 350 psi        | Orange          |
| 8                | 4000 - 5000 psi | 500 to 5000 psi     | 50 psi                         | 150 to 450 psi        | Pink            |

Note: 100 psi = 6.9 bar.

### Differential

This is the pressure required to open and close the switch contacts. It is a constant value dependent on the characteristics of the switch. The differential will be in the range as shown on the above table. For minimum differential, select the lightest spring including the maximum setting desired.

## **Standard Product Ordering Code**





#### PARKER-HANNIFIN CORPORATION OFFER OF SALE

The goods, services or work (referred to as the "Products") offered by **Parker-Hannifin Corporation**, its subsidiaries, groups, divisions, and authorized distributors ("Seller") are offered for sale at prices indicated in the offer, or as may be established by Seller. The offer to sell the Products and acceptance of Seller's offer by any customer ("Buyer") is contingent upon, and will be governed by all of the terms and conditions contained in this Offer of Sale. Buyer's order for any Products specified in Buyer's purchase document or Seller's offer, proposal or quote ("Quote") attached to the purchase order, when communicated to Seller verbally, or in writing, shall constitute acceptance of this offer.

1. <u>Terms and Conditions</u>. Seller's willingness to offer Products for sale or accept an order for Products is subject to the terms and conditions contained in this Offer of Sale or any newer version of the same, published by Seller electronically at www.parker.com/saleterms/. Seller objects to any contrary or additional terms or conditions of Buyer's order or any other document or other communication issued by Buyer.

2. <u>Price: Payment</u>. Prices stated on Seller's Quote are valid for thirty (30) days, except as explicitly otherwise stated therein, and do not include any sales, use, or other taxes or duties unless specifically stated. Seller reserves the right to modify prices to adjust for any raw material price fluctuations. Unless otherwise specified by Seller, all prices are F.C.A. Seller's facility (INCOTERMS 2010). Payment is subject to credit approval and payment for all purchases is due thirty (30) days from the date of invoice (or such date as may be specified by Seller's Credit Department). Unpaid invoices beyond the specified payment date incur interest at the rate of 1.5% per month or the maximum allowable rate under applicable law.

3. <u>Shipment; Delivery; Title and Risk of Loss</u>. All delivery dates are approximate. Seller is not responsible for damages resulting from any delay. Regardless of the manner of shipment, delivery occurs and title and risk of loss or damage pass to Buyer, upon placement of the Products with the shipment carrier at Seller's facility. Unless otherwise stated, Seller may exercise its judgment in choosing the carrier and means of delivery. No deferment of shipment at Buyers' request beyond the respective dates indicated will be made except on terms that will indemnify, defend and hold Seller harmless against all loss and additional expense. Buyer shall be responsible for any additional shipping charges incurred by Seller due to Buyer's acts or omissions.

4. <u>Warranty</u>. Seller warrants that the Products sold hereunder shall be free from defects in material or workmanship for a period of twelve (12) months from the date of delivery or 2,000 hours of normal use, whichever occurs first. All prices are based upon the exclusive limited warranty stated above, and upon the following disclaimer: <u>DISCLAIMER OF WARRANTY</u>: THIS WARRANTY IS THE SOLE AND ENTIRE WARRANTY PERTAINING TO PRODUCTS PROVIDED. SELLER DISCLAIMS ALL OTHER WARRANTIES, EXPRESS AND IMPLIED, INCLUDING DESIGN, MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

5. <u>Claims</u>; <u>Commencement of Actions</u>. Buyer shall promptly inspect all Products upon receipt. No claims for shortages will be allowed unless reported to the Seller within ten (10) days of delivery. No other claims against Seller will be allowed unless asserted in writing within thirty (30) days after delivery. Buyer shall notify Seller of any alleged breach of warranty within thirty (30) days after the date the defect is or should have been discovered by Buyer. Any claim or action against Seller based upon breach of contract or any other theory, including tort, negligence, or otherwise must be commenced within twelve (12) months from the date of the alleged breach or other alleged event, without regard to the date of discovery.

6. LIMITATION OF LIABILITY. IN THE EVENT OF A BREACH OF WARRANTY, SELLER WILL, AT ITS OPTION, REPAIR OR REPLACE A DEFECTIVE PRODUCT, OR REFUND THE PURCHASE PRICE WITHIN A REASONABLE PERIOD OF TIME. IN NO EVENT IS SELLER LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF, OR AS THE RESULT OF, THE SALE, DELIVERY, NON-DELIVERY, SERVICING, USE OR LOSS OF USE OF THE PRODUCTS OR ANY PART THEREOF, OR FOR ANY CHARGES OR EXPENSES OF ANY NATURE INCURRED WITHOUT SELLER'S WRITTEN CONSENT, WHETHER BASED IN CONTRACT, TORT OR OTHER LEGAL THEORY. IN NO EVENT SHALL SELLER'S LIABILITY UNDER ANY CLAIM MADE BY BUYER EXCEED THE PURCHASE PRICE OF THE PRODUCTS.

7. <u>User Responsibility</u>. The user, through its own analysis and testing, is solely responsible for making the final selection of the system and Product and assuring that all performance, endurance, maintenance, safety and warning requirements of the application are met. The user must analyze all aspects of the application and follow applicable industry standards and Product information. If Seller provides Product or system options based upon data or specifications provided by the user, the user is responsible for determining that such data and specifications are suitable and sufficient for all applications and reasonably foreseeable uses of the Products or systems.

8. Loss to Buyer's Property. Any designs, tools, patterns, materials, drawings, confidential information or equipment furnished by Buyer or any other items which become Buyer's property, will be considered obsolete and may be destroyed by Seller after two (2) consecutive years have elapsed without Buyer ordering the items manufactured using such property. Seller shall not be responsible for any loss or damage to such property while it is in Seller's possession or control.

**9.** <u>Special Tooling</u>. A tooling charge may be imposed for any special tooling, including without limitation, dies, fixtures, molds and patterns, acquired to manufacture Products. Such special tooling shall be and remain Seller's property notwithstanding payment of any charges by Buyer. In no event will Buyer acquire any interest in apparatus belonging to Seller which is utilized in the manufacture of the Products, even if such apparatus has been specially converted or adapted for such manufacture and notwithstanding any charges paid by Buyer. Unless otherwise agreed, Seller has the right to alter, discard or otherwise dispose of any special tooling or other property in its sole discretion at any time.

10. <u>Buyer's Obligation; Rights of Seller</u>. To secure payment of all sums due or otherwise, Seller retains a security interest in all Products delivered to Buyer and this agreement is deemed to be a Security Agreement under the Uniform Commercial Code. Buyer authorizes Seller as its attorney to execute and file on Buyer's behalf all documents Seller deems necessary to perfect its security interest.

11. Improper Use and Indemnity. Buyer shall indemnify, defend, and hold Seller harmless from any losses, claims, liabilities, damages, lawsuits, judgments and costs (including attorney fees and defense costs), whether for personal injury, property damage, patent, trademark or copyright infringement or any other claim, brought by or incurred by Buyer, Buyer's employees, or any other person, arising out of: (a) improper selection, application, design, specification or other misuse of Products purchased by Buyer from Seller; (b) any act or omission, negligent or otherwise, of Buyer; (c) Seller's use of patterns, plans, drawings, or specifications furnished by Buyer to manufacture Products; or (d) Buyer's failure to comply with these terms and conditions. Seller shall not indemnify Buyer under any circumstance except as otherwise provided.

12. <u>Cancellations and Changes</u>. Buyer may not cancel or modify or cancel any order for any reason, except with Seller's written consent and upon terms that will indemnify, defend and hold Seller harmless against all direct, incidental and consequential loss or damage. Seller may change Product features, specifications, designs and availability.

13. <u>Limitation on Assignment</u>. Buyer may not assign its rights or obligations under this agreement without the prior written consent of Seller.

14. <u>Force Majeure</u>. Seller does not assume the risk and is not liable for delay or failure to perform any of Seller's obligations by reason of events or circumstances beyond its reasonable control (hereinafter "Events of Force Majeure"). Events of Force Majeure shall include without limitation: accidents, strikes or labor disputes, acts of any government or government agency, acts of nature, delays or failures in delivery from carriers or suppliers, shortages of materials, or any other cause beyond Seller's reasonable control.

15. <u>Waiver and Severability</u>. Failure to enforce any provision of this agreement will not invalidate that provision; nor will any such failure prejudice Seller's right to enforce that provision in the future. Invalidation of any provision of this agreement by legislation or other rule of law shall not invalidate any other provision herein. The remaining provisions of this agreement will remain in full force and effect.

16. <u>Termination</u>. Seller may terminate this agreement for any reason and at any time by giving Buyer thirty (30) days prior written notice. Seller may immediately terminate this agreement, in writing, if Buyer: (a) breaches any provision of this agreement (b) appoints a trustee, receiver or custodian for all or any part of Buyer's property (c) files a petition for relief in bankruptcy on its own behalf, or one if filed by a third party (d) makes an assignment for the benefit of creditors; or (e) dissolves its business or liquidates all or a majority of its assets.

17. <u>Governing Law</u>. This agreement and the sale and delivery of all Products are deemed to have taken place in, and shall be governed and construed in accordance with, the laws of the State of Ohio, as applicable to contracts executed and wholly performed therein and without regard to conflicts of laws principles. Buyer irrevocably agrees and consents to the exclusive jurisdiction and venue of the courts of Cuyahoga County, Ohio with respect to any dispute, controversy or claim arising out of or relating to this agreement.

18. <u>Indemnity for Infringement of Intellectual Property Rights</u>. Seller is not liable for infringement of any patents, trademarks, copyrights, trade dress, trade secrets or similar rights except as provided in this Section. Seller will defend and indemnify Buyer against allegations of infringement of U.S. patents, U.S. trademarks, copyrights, trade dress and trade secrets ("Intellectual Property Rights"). Seller will defend at its expense and will pay the cost of any settlement or damages awarded in an action brought against Buyer based on an allegation that a Product sold pursuant to this agreement infringes the Intellectual Property Rights of a third party. Seller's obligation to defend and indemnify Buyer is contingent on Buyer notifying Seller within ten (10) days after Buyer becomes aware of such allegations of infringement, and Seller having sole control over the defense of any allegations or actions including all negotiations for settlement or compromise. If a Product is subject to a claim that it infringes the Intellectual Property Rights of a third party, Seller may, at its sole expense and option, procure for Buyer the right to continue using the Product, replace or modify the Product so as to make it noninfringing, or offer to accept return of the Product and refund the purchase price less a reasonable allowance for depreciation. Notwithstanding the foregoing, Seller is not liable for claims of infringement based on information provided by Buyer, or directed to Products delivered hereunder for which the designs are specified in whole or part by Buyer, or infringements resulting from the modification, combination or use in a system of any Product sold hereunder. The foregoing provisions of this Section constitute Seller's sole and exclusive liability and Buyer's sole and exclusive remedy for infringement of Intellectual Property Rights

19. <u>Entire Agreement</u>. This agreement contains the entire agreement between the Buyer and Seller and constitutes the final, complete and exclusive expression of the terms of sale All prior or contemporaneous written or oral agreements or negotiations with respect to the subject matter are herein merged. The terms contained herein may not be modified unless in writing and signed by an authorized representative of Seller.

20. <u>Compliance with Laws</u>. Buyer agrees to comply with all applicable laws, regulations, and industry and professional standards of care, including those of the United Kingdom the United States of America, and the country or countries in which Buyer may operate; including without limitation the U. K. Bribery Act, the U.S. Foreign Corrupt Practices Act ("FCPA"), the U.S. Anti-Kickback Act ("Anti-Kickback Act") and the U.S. Food Drug and Cosmetic Act ("FDCA"),each as currently amended, and the rules and regulations promulgated by the U.S. Food and Drug Administration ("FDA"), and agrees to indemnify and hold harmless Seller from the consequences of any violation of such provisions by Buyer, its employees or agents. Buyer acknowledges that it is familiar with the provisions of the U.K. Bribery Act, the FDA, and the Anti-Kickback Act, and certifies that Buyer will adhere to the requirements thereof. In particular, Buyer represents and agrees that Buyer will not make any payment or give anything of value, directly or indirectly to any governmental official, any foreign political party or official thereof, any candidate for foreign political office, or any commercial entity or person, for the purpose of influencing such person to purchase Products or otherwise benefit the business of Seller.

| <br> |  |  |  |  |  |  |  |  |  |  |  |
|------|--|--|--|--|--|--|--|--|--|--|--|
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |
|      |  |  |  |  |  |  |  |  |  |  |  |





## **Parker's Motion & Control Technologies**

At Parker, we're guided by a relentless drive to help our customers become more productive and achieve higher levels of profitability by engineering the best systems for their requirements. It means looking at customer applications from many angles to find new ways to create value. Whatever the motion and control technology need, Parker has the experience, breadth of product and global reach to consistently deliver. No company knows more about motion and control technology than Parker. For further info call 1 800 C-Parker (1 800 272 7537)



#### Fluid & Gas Handling

Key Markets Aerial lift Agriculture Bulk chemical handling Construction machinery Food & beverage Fuel & gas delivery Industrial machinery Life sciences Marine Mining Mobile Ol & gas Renewable energy Transportation

#### Key Products

Check valves Connectors for low pressure fluid conveyance Deep sea umbilicals Diagnostic equipment Hose couplings Industrial hose Mooring systems & power cables PTFF hose & tubing Quick couplings Rubber & thermoplastic hose Tube fittings & adapters Tubeing & plastic fittings



#### Aerospace Key Markets

Aftermarket services Commercial transports Engines General & business aviation Helicopters Launch vehicles Military aircraft Missiles Power generation Regional transports Unmanned aerial vehicles

#### Key Products

Control systems & actuation products Engine systems & components Fluid conveyance systems & components Fluid metering, delivery & atomization devices Fuel systems & components Fluid tank inerting systems & components Thermal margagement Wheels & brakes



#### **Hydraulics**

Key Markets Aerial lift Agriculture Alternative energy Construction machinery Forestry Industrial machinery Machine tools Marine Material handling Mining Oil & gas Power generation Refuse vehicles Renewable energy Truck hydraulics Turf equipment

#### Key Products

Accumulators Cartridge valves Electrohydraulic actuators Human machine interfaces Hybrid drives Hydraulic cylinders Hydraulic systems Hydraulic systems Hydraulic systems Hydraulic valves & controls Hydraulic valves & controls Hydraulic valves & controls Prower take-offs Power units Rotary actuators Sensors





#### Climate Control Key Markets

Agriculture Air conditioning Construction Machinery Food & beverage Industrial machinery Life sciences Oil & gas Precision cooling Process Refrigeration Transportation

#### Key Products

Accumulators Advanced actuators CO<sub>2</sub> controls Electronic controllers Filter driers Hand shut-off valves Heat exchangers Hose & fittings Pressure regulating valves Refrigerant distributors Safety relief valves Solenoid valves Thermostatic expansion valves



#### Pneumatics Key Markets

Aerospace Conveyor & material handling Factory automation Life science & medical Machine tools Packaging machinery Transportation & automotive

#### Key Products

Air preparation Brass fittings & valves Manifolds Pneumatic accessories Pneumatic values & controls Quick disconnects Rotary actuators Rubber & thermoplastic hose & couplings Structural extrusions Thermoplastic tubing & fittings Vacuum generators, cups & sensors



#### Electromechanical

Key Markets Aerospace Factory automation Life science & medical Machine tools Packaging machinery Paper machinery Plastics machinery & converting Primary metals Semiconductor & electronics Textile Wire & cable

#### Key Products

AC/DC drives & systems Electric actuators, gantry robots & sides Electrohydrostatic actuation systems Electromechanical actuation systems Human machine interface Linear motors Stepper motors, servo motors, drives & controls Structural extrusions



#### **Process Control**

Key Markets Alternative fuels Biopharmaceuticals Chemical & refining Food & beverage Marine & shipbuilding Medical & dental Microelectronics Nuclear Power Offshore oil exploration Oil & gas Pharmaceuticals Power generation Pulp & paper Steel Water/wastewater

#### **Key Products**

Analytical Instruments Analytical sample conditioning products & system Chemical injection fittings & valves Fluoropolymer chemical delivery fittings, valves & pumps High purity gas delivery fittings, valves, regulators & digital flow controllers Industrial mass flow meters/ controllers Permanent no-weld tube fittings Precision industrial regulators & flow controllers Process control double block & bleeds Process control fittings, valves, regulators & manifold valves



#### Filtration

Key Markets Aerospace Food & beverage Industrial plant & equipment Life sciences Marine Mobile equipment Oil & gas Power generation & renewable energy Process Transportation Water Purification

#### Key Products

Analytical gas generators Compressed air filters & dryers Engine air, coolant, fuel & oil filtration systems Fluid condition monitoring systems Hydraulic & lubrication filters Hydrogen, nitrogen & zero air generators Instrumentation filters Membrane & fiber filters Microfiltration Sterlie air filtration Water desalination & purification filters & systems



#### Sealing & Shielding

Key Markets Aerospace Chemical processing Consumer Fluid power General industrial Information technology Life sciences Microelectronics Military Oll & gas Power generation Renewable energy Telecommunications Transportation

#### **Key Products**

Dynamic seals Elastomeric o-rings Electro-medical instrument design & assembly EMI shielding Extruded & precision-cut, fabricated elastomeric seals High temperature metal seals Homogeneous & inserted elastomeric shanes Medical device fabrication & assembly Metal & plastic retained composite seals Shielded optical windows Silicone tubing & extrusions Thermal management Vibration dampening



Parker Hannifin Corporation Hydraulic Pump and Power Systems Division Oildyne Business Unit 5520 Highway 169 North New Hope, MN 55428 USA Ph: 937-644-3915 Fax: 937-642-3738 www.parker.com/hps

Catalog HY22-1131/US 5M, 11/15/BG