► 156 Hose Products for the Aerospace Industry







FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS AND/OR SYSTEMS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

Before selecting or using any Parker hose or fittings or related accessories, it is important that you read and follow Parker Safety Guide for Selecting and Using Hoses, Fittings, and Related Accessories (Parker Publication No. 4400-B.1)

This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors, provide product and/or system options for further investigation by users having technical expertise. It is important that you analyze all aspects of your application and review the information concerning the product or system in the current product catalog. Due to the variety of operating conditions and applications for these products or systems, the user, through its own analysis and testing, is solely responsible for making the final selection of the products and systems and assuring that all performance, safety and warning requirements of the application are met.

The products described herein, including without limitation, product features, specifications, designs, availability and pricing, are subject to change by Parker Hannifin Corporation and its subsidiaries at any time without notice.

Offer of Sale

The items described in this document are hereby offered for sale by Parker Hannifin Corporation, its subsidiaries or its authorized distributors. This offer and its acceptance are governed by the provisions in the "Offer of Sale".

© 2006 Parker Hannifin Corporation



Table of Contents

How to Use This Catalog	2
Ordering Information for Standard Items	3-4
Stratoflex "Twist Angle" Information	4
Measurement of Flareless Hose Assemblies	4
156 Medium Pressure, Lightweight Engine Hose	5
156H Medium Pressure, Lightweight Fire Resistant Engine Hose	6
156K Medium Pressure hose with Polyester Cover	7
156 Hose Fittings (Field Attachable) 8-	-12
156 Flare Hose Assemblies (Field Attachable)	-16
156 Flareless Hose Assemblies (Field Attchable)17-	-20
156 Flange Hose Assemblies (Field Attachable)21-	-24
Abrasion / Firesleeve Data25-	-26
Safety Guide27-	-28
Offer of Sale	29



How to Use This Catalog

- If you know the type of part (fitting, hose assembly, etc.), see the Table of Contents on page 1.
- The Stratoflex part numbering system for Hose, Fittings and Hose Assemblies is defined on page 3.
- The Stratoflex Hose and Fitting information tables have international symbols as column heads. The symbols and their meaning are noted below.

SYMBOL	DEFINITION	SYMBOL	DEFINITION		
#	Part Number	Hg	Vacuum Rating		
0	Hose Inner Diameter	=	Crimp Fitting		
0	Hose Outer Diameter		Field Attachable Fitting		
	Working Pressure		Page Number		
*	Burst Pressure	<u>~~~~~</u>	Thread Size		
\sim	Minimum Bend Radius	\bigcirc	Hex Size		
lb	Weight	Ø	Diameter		



Ordering Information for Standard Items

1. HOSE ASSEMBLY: STRAIGHT TO STRAIGHT OR STRAIGHT TO SINGLE ELBOW EXAMPLE: 156001-8D-0185 Assembly Length in Inches. The last digit specifies Basic Hose Assembly Numbereighths of an inch / 3.175 mm. Size (1/2 inch / 12.7 mm O.D. See Material Note Below Tube Size) In 1/16 inch / 1.5975 mm Basic Hose Assembly part numbers may be modified to add a sleeve or coil by the insertion of a code letter between the basic hose number and the configuration number. Code letters and accessories are described on pages 26 & 27. 156F001-8D-0185 Basic Part Number with 2650 Firesleeve and 10781-SIZE CR Clamp (See page 26). 156H001-8D-0185 Basic Part Number with Integral Extruded Silicone Fire Cover. (Hose Part No. 156-SIZE H) 156K001-8D-0185 Basic Part Number with Braided Polyester Abrasion Cover. (Hose Part No. 156-SIZE K) 156060E0185D180 **DOUBLE ELBOW EXAMPLE:** Twist Angle (180° - See Page 4) Basic Hose Assembly Number See Material Note Below Size (1/2inch / 12.7 mm O.D. Assembly Length in Inches. Last digit specifies Tube Size) In 1/16" / 1.588 mm eighths of an inch / 3.175 mm. SIZE CODE FOR DOUBLE ELBOW HOSE ASSEMBLIES -12 DASH SIZE -3 -4 -5 -10 -16 -20 -24 -32 -6 -8 SF CODE LETTER С Ε F G Н J Κ Α В D L Е F SIZE CODE MS Н R **MATERIAL:** Unless otherwise noted, conforms to applicable specifications. C or CR - Non-Brazed/Welded Parts - SAE 30304 (AMS5639) D - Non-Brazed Parts - SAE 2024-T6 (AMS4112) Brazed/Welded Parts - SAE 30321 (AMS5570 or AMS5645) Brazed Parts - SAE 6061-T6 (AMS4117 or CL - Same as CR except lockwire holes in nut AMS4080) S - All parts SAE 1137 (AMS5024) or SAE 1010 (AMS5050) except socket SAE 2024-T6 (AMS4112) SL - Same as S except lockwire holes in nut LENGTH MEASUREMENT - Length is measured along hose centerline from end of nipple to end of nipple 2. HOSE FITTING - EXAMPLE: 678-8D Material Designation (See material note above) Basic Fitting Number — Size (1/2" / 12.7 mm O.D. Tube Size) in 1/16 inch / 1.588 mm 3. BULK HOSE, GUARDS & SLEEVES - EXAMPLE: 750 FT. **156-8** – Hose Size Quantity in Feet-Basic Hose Number (Bulk hose furnished in random lengths in accordance with the applicable hose specification.) 4. CUT HOSE, GUARDS & SLEEVES - EXAMPLE: 156-8-0185 Length, 18-5/8 inches / Basic Hose Number -473.075 mm



Hose Size -

Ordering Information for Standard Items

5. IDENTIFICATION BANDS: An example of Identification bands used when required for Hose Assemblies confirming TSO-C53a and C75 follows:

NOTE: For additional information on special materials or accessories not shown on page 3, contact Stratoflex.

NOTE: Unless otherwise noted, dimensions shown herein are nominal and are subject to change without notice. Contact Stratoflex Engineering for current data.

NOTE: Must be authorized by Parker Stratoflex to tag hose assemblies with TSO markings.

STRATOFLEX, FT.WORTH A 156001-8D-0185 SIZE 8 1-12-97 TSO-C53a, Type A

STRATOFLEX "TWIST ANGLE" INFORMATION

HOW TO MEASURE AND SPECIFY POSITIONING OF FITTINGS WHEN TWO ELBOW FITTINGS ARE REQUIRED ON A HOSE ASSEMBLY



MEASURING: When installations require hose assemblies with elbow fittings on both sides, hold the assembly so that the nearest fitting is pointing in the 6 o'clock position. Measure angle between fitting, counterclockwise. Both fittings pointing to 6 o'clock to be specified as zero degrees (0°)


SPECIFYING POSITION: Suffix the hose assembly part number with the number of degrees in the angle. (Example: 111511E0185D180; 180° Twist Angle.)

NOTE: Elbow Hose Fittings shown is this catalog are STRATOFLEX standard type designs. If your installation requires a fitting of a different angle or connection, either submit a print or call Stratoflex Engineering.

MEASUREMENT OF FLARELESS HOSE ASSEMBLIES

NAS 1760 Nipple end design is supplied by Stratoflex on flareless hose fittings. Flareless hose assembly length "L" is measured from END of nipple to END of nipple. To convert "END to END" to "GAGE POINT to GAGE POINT" measurement, subtract from "L" the appropriate "B or C" dimension shown in table below for each end fitting. The figures and table below give a comparison of NAS 1760 nipple end design and Stratoflex Radius Seal end design.

NOTE: ALL HOSE FITTINGS ARE MEASURED AT THE CENTERLINE FOR LENGTH AND DROP DIMENSIONS.





156 Medium Pressure Lightweight Engine Hose



SPECIFICATIONS:

Meets the dimensional requirements and meets or exceeds the functional requirements of MIL-H-83797 with an improved inner tube of HSP® for better high temperature resistance. See information bulletin IB-1030 for TSO approvals.

CONSTRUCTION:

Tube - Seamless HSP® elastomer.*

Reinforcement - One and one-half corrosion resistant steel wire braids.

APPLICATION:

Medium pressure service with most petroleum base oils, JP fuels, aviation gasoline, MIL-L-7808 and MIL-L-23699 lubricants, and many synthetic base fluids. Not affected by alcohols, coolants, and solvents common to the aerospace industry. Avgas has no adverse affect on the Stratoflex HSP innertube.

TEMPERATURE RANGE:

-65 to +300°F (-55 to +149°C)

NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size	Hose Size	0	0		**	Proof	*	5	lb/in g/mm
TT	O.D.		Nominal	Nominal	Fuel & Oil	Hydraulic	Pressure		* •	g/mm
156-3	.188	-3	.156	.376	1500	1500	3000	6000	1.75	.008
	4.775		3.962	9.550	103.42	103. 4 2	206.84	413.69	44.45	.143
156-4	.250	-4	.219	.440	1500	1500	3000	6000	2.00	.010
	6.350		5.563	11.176	103.42	103.42	206.84	413.69	50.80	.176
156-5	.312	-5	.281	.486	1500	1500	3000	6000	2.25	.012
	7.925		7.137	12.344	103.42	103.42	206.84	413.69	57.15	.214
156-6	.375	-6	.344	.549	1500	1500	3000	6000	2.50	.013
	9.525		8.738	13.945	103.42	103.42	206.84	413.69	63.50	.230
156-8	.500	-8	.438	.651	1250	1250	2500	5000	3.50	.017
	12.700		11.125	16.535	86.18	86.18	172.37	344.74	88.90	.307
156-10	.625	-10	.562	.797	1250	1250	2500	5000	4.00	.022
	15.875		14.275	20.244	86.18	86.18	172.37	344.74	101.60	.393
156-12	.750	-12	.688	.938	1250	950	2000	3750	4.50	.026
	19.050		17.475	23.825	86.18	65.50	137.90	258.55	114.30	.464
156-16	1.00	-16	.875	1.156	1000	625	1500	2500	5.50	.037
	25.400		22.225	29.362	68.95	43.09	103.42	172.37	139.70	.661
156-20	1.25	-20	1.125	1.437	800	-	1300	2000	8.00	.051
	31.750		28.575	36.500	55.16		89.63	137.90	203.20	.911
156-24	1.50	-24	1.375	1.703	400	-	800	1750	9.00	.069
	38.100		34.925	43.256	27.58		55.16	120.66	228.60	1.044
156-32	2.00	-32	1.773	2.101	350	-	700	1400	12.50	.085
	50.800		45.034	53.365	24.13		48.26	96.53	317.50	1.232

^{*} Originally Qualified Under Part Number 176

^{**} Exceeds Pressure Requirements of MIL-H-83797



156H Medium Pressure Lightweight Fire Resistant Engine Hose



SPECIFICATIONS:

Meets or exceeds the functional requirements of MIL-H-83797 with an improved inner tube of HSP[®] for better high temperature resistance. See information bulletin IB-1030 for TSO approvals.

CONSTRUCTION:

Tube - Seamless HSP® elastomer.

Reinforcement - One and one-half corrosion resistant steel wire braids.

Cover - Integral Fire Resistant Silicone.

APPLICATION:

Medium pressure service with most petroleum base oils, JP fuels, aviation gasoline, MIL-L-7808 and MIL-L-23699 lubricants, and many synthetic base fluids. Not affected by alcohols, coolants, and solvents common to the aerospace industry. Avgas has no adverse affect on the Stratoflex HSP innertube.

TEMPERATURE RANGE:

-65 to +300°F (-55 to +149°C)

NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size	Hose Size	0	0		<u> </u>	Proof	*	5	Ib/in
	O.D.		Nominal	Nominal	Fuel & Oil	Hydraulic	Pressure	7	- -	g/mm
156-3H	.188	-3	.156	.699	1500	1500	3000	6000	1.75	.0212
	4.775		3.962	17.755	103.42	103.42	206.84	413.69	44.45	.3785
156-4H	.250	-4	.219	.733	1500	1500	3000	6000	2.00	.0242
	6.350		5.563	18.618	103.42	103.42	206.84	413.69	50.80	.4256
156-5H	.312	-5	.281	.788	1500	1500	3000	6000	2.25	.0274
	7.925		7.137	20.020	103.42	103.42	206.84	413.69	57.15	.4893
156-6H	.375	-6	.344	.842	1500	1500	3000	6000	2.50	.0292
	9.525		8.738	21.387	103.42	103.42	206.84	413.69	63.50	.5215
156-8H	.500	-8	.438	.944	1250	1250	2500	5000	3.50	.0353
	12.700		11.125	23.978	86.18	86.18	172.37	344.74	88.90	.6303
156-10H	.625	-10	.562	1.103	1250	1250	2500	5000	4.00	.0447
	15.875		14.275	28.016	86.18	86.18	172.37	344.74	101.60	.7982
156-12H	.750	-12	.688	1.244	1250	950	2000	3750	4.50	.0524
	19.050		17.475	31.598	86.18	65.50	137.90	258.55	114.30	.9357
156-16H	1.00	-16	.875	1.438	1000	625	1500	2500	5.50	.0666
	25.400		22.225	36.525	68.95	43.09	103.42	172.37	139.70	1.189
156-20H	1.25	-20	1.125	1.719	800	-	1300	2000	8.00	.0872
	31.750		28.575	43.662	55.16		89.63	137.90	203.20	1.557

BENEFITS

- Envelope dimensions smaller than conventional "slip over" firesleeve
- No "wicking" as seen with "slip over" firesleeve
- No end dipping necessary
- Same small bend radii as 156 hose



156K Medium Pressure Hose with Polyester Cover



SPECIFICATIONS:

Meets or exceeds the functional requirements of MIL-H-83797 with an improved inner tube of HSP® for better high temperature resistance.

CONSTRUCTION:

Tube - Seamless HSP® elastomer.

Reinforcement - One and one-half corrosion resistant steel wire braids.

Cover - Blue Braided Polyester Abrasion Resistant.

APPLICATION:

Medium pressure service with most petroleum base oils, JP fuels, aviation gasoline, MIL-L-7808 and MIL-L-23699 lubricants, and many synthetic base fluids. Not affected by alcohols, coolants, and solvents common to the aerospace industry. Avgas has no adverse affect on the Stratoflex HSP innertube.

TEMPERATURE RANGE:

-65 to +300°F (-55 to +149°C)


NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size	Hose Size	0	0		<u> </u>	Proof	*	5	Ib/in
	O.D.		Nominal	Nominal	Fuel & Oil	Hydraulic	Pressure	7	* -	g/mm
156-3K	.188	-3	.156	.471	1500	1500	3000	6000	1.75	.0102
	4.775		3.962	11.963	103.42	103.42	206.84	413.69	44.45	.1822
156-4K	.250	-4	.219	.534	1500	1500	3000	6000	2.00	.0125
	6.350		5.563	13.564	103.42	103.42	206.84	413.69	50.80	.2232
156-5K	.312	-5	.281	.588	1500	1500	3000	6000	2.25	.0143
	7.925		7.137	14.732	103.42	103.42	206.84	413.69	57.15	.2554
156-6K	.375	-6	.344	.643	1500	1500	3000	6000	2.50	.0155
	9.525		8.738	16.332	103.42	103.42	206.84	413.69	63.50	.2768
156-8K	.500	-8	.438	.745	1250	1250	2500	5000	3.50	.0198
	12.700		11.125	18.923	86.18	86.18	172.37	344.74	88.90	.3536
156-10K	.625	-10	.562	.892	1250	1250	2500	5000	4.00	.0253
	15.875		14.275	22.657	86.18	86.18	172.37	344.74	101.60	.4518
156-12K	.750	-12	.688	1.033	1250	950	2000	3750	4.50	.0302
	19.050		17.475	26.238	86.18	65.50	137.90	258.55	114.30	.5393
156-16K	1.00	-16	.875	1.251	1000	625	1500	2500	5.50	.0418
	25.400		22.225	31.775	68.95	43.09	103.42	172.37	139.70	.7645
156-20K	1.25	-20	1.125	1.532	800	-	1300	2000	8.00	.0571
	31.750		28.575	38.913	55.16		89.63	137.90	203.20	1.1970
156-24K	1.50	-24	1.375	1.799	400	-	800	1750	9.00	.0765
	38.100		34.925	45.695	27.58		55.16	120.66	228.60	1.3661
156-32K	2.00	-32	1.773	2.197	350	-	700	1400	12.50	.0948
	50.800		45.034	55.804	24.13		48.26	96.53	317.50	1.6929



676 Straight Flared Fitting (Field Attachable)

37° Flare Swivel M83798/1 Mates with MS33656/AS4395 type connectors.



NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size O.D.	Hose Size	<u>~~~~~</u>	Nominal A	Cut Factor B	Nominal C	Nominal D	E	Nominal
676-3S	.188 4.775	-3	.375-24UNJF-3B	1.63 41.40	.74 18.80	.11 2.79	. 35 8.89	. 50 12.70	.038 17.237
676-4S	.250 6.350	-4	.4375-20UNJF-3B	1.65 41.91	. 74 18.80	.16 4.06	.35 8.89	.56 14.22	. 067 30.391
676-5S	.312 7.925	-5	.500-20UNJF-3B	1.70 <i>43.18</i>	.76 19.30	.22 5.59	. 38 9.65	.62 15.75	.083 37.648
676-6D	. 375 9.525	-6	.5625-18UNJF-3B	1.80 <i>45.7</i> 2	.84 21.34	.28 7.11	.39 9.91	.69 17.53	.050 22.680
676-8D	. 500 12.700	-8	.750-16UNJF-3B	2.02 51.31	.97 24.64	.38 9.65	.44 11.18	.88 22.35	.078 35.380
676-10D	. 625 15.875	-10	.875-14UNJF-3B	2.24 56.90	1.05 26.67	. 48 12.19	. 52 13.21	1.00 25.40	. 107 48.534
676-12D	. 750 19.050	-12	1.0625-12UNJ-3B	2.30 58.42	1.11 28.19	. 59 14.99	.58 14.73	1.25 31.75	. 173 78.471
676-16D	1.000 25.400	-16	1.3125-12UNJ-3B	2.84 72.14	1.34 34.04	. 79 20.07	.65 16.51	1.50 38.10	.275 124.738
676-20D	1.250 31.750	-20	1.625-12UNJ-3B	3.14 79.76	1.54 39.12	1.04 26.42	. 64 16.26	1.81 45.97	.339 153.768
676-24D	1.500 38.100	-24	1.875-12UNJ-3B	3.52 89.41	1.70 43.18	1.28 32.51	. 74 18.80	2.12 53.85	. 504 228.611
676-32D	2.000 50.800	-32	2.500-12UNJ-3B	4.11 104.39	2.04 51.82	1.68 <i>4</i> 2.67	.93 23.62	2.75 69.85	1.022 463.571

678 45° Elbow Flared Fitting (Field Attachable)

37° Flare Swivel M83798/1 Mates with MS33656/AS4395 type connectors.


NOTE: English measurements in BOLD; metric measurements in ITALICS.

OTE. Eng	TE. English measurements in <u>BOLD</u> , metric measurements in <u>MALICS</u> .										
44	Tube Size	Hose Size		Nominal	Cut Factor	Nominal	Nominal	$\langle \rangle$			
#	O.D.	0.20		A	В	С	D	E	Nominal		
678-3S	.188 4.775	-3	.375-24UNJF-3B	1.68 <i>4</i> 2.67	1.15 29.21	.11 2.79	.34 8.64	.50 12.70	.046 20.865		
678-4S	. 250 6.350	-4	.4375-20UNJF-3B	1.63 <i>41.40</i>	1.07 27.18	.16 4.06	. 35 8.89	.56 14.22	. 072 36.659		
678-5S	. 312 7.925	-5	.500-20UNJF-3B	1.70 43.18	1.14 28.96	.22 5.59	.41 10.41	.62 15.75	.094 42.638		
678-6D	. 375 9.525	-6	.5625-18UNJF-3B	1.80 45.72	1.22 30.99	. 28 7.11	.44 11.18	.69 17.53	. 053 24.040		
678-8D	. 500 12.700	-8	.750-16UNJF-3B	1.92 48.77	1.31 33.27	. 38 9.65	.46 11.68	.88 22.35	. 081 36.740		
678-10D	.625 15.875	-10	.875-14UNJF-3B	2.10 53.34	1.44 36.58	.48 12.19	.54 13.72	1.00 25.40	.114 51.709		
678-12D	.750 19.050	-12	1.0625-12UNJ-3B	2.33 59.18	1.72 <i>4</i> 3.69	.59 14.99	.62 15.75	1.25 31.75	.179 81.193		
678-16D	1.000 25.400	-16	1.3125-12UNJ-3B	2.88 73.15	2.03 51.56	.79 20.07	.66 16.76	1.50 38.10	.280 127.006		
678-20D	1.250 31.750	-20	1.625-12UNJ-3B	3.26 <i>82.80</i>	2.30 58.42	1.04 26. <i>4</i> 2	.77 19.56	1.81 <i>45.97</i>	.486 220.446		
678-24D	1.500 38.100	-24	1.875-12UNJ-3B	3.61 91.69	2.53 64.26	1.28 32.51	.87 22.10	2.12 53.85	.622 282.135		
678-32D	2.000 50.800	-32	2.500-12UNJ-3B	4.04 102.62	2.91 73.91	1.68 <i>4</i> 2.67	1.07 27.18	2.75 69.85	1.080 489.880		



680 90° Elbow Flared Fitting (Field Attachable)

37° Flare Swivel M83798/3 Mates with MS33656/AS4395 type connectors.



 $\angle_{\text{E-NUT HEX}}$


NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size O.D.	Hose Size	<u>~~~~~</u>	Nominal A	Cut Factor B	Nominal C	Nominal D	E	Nominal
680-3S	.188 4.775	-3	.375-24UNJF-3B	1.32 33.53	. 79 20.07	.11 2.79	.65 16.51	. 50 12.70	.048 21.772
680-4S	.250 6.350	-4	.4375-20UNJF-3B	1.50 38.10	. 94 23.88	.16 4.06	. 72 18.29	. 56 14.22	. 074 33.566
680-5S	.312 7.925	-5	.500-20UNJF-3B	1.54 39.12	.98 24.89	.22 5.59	.84 21.34	.62 15.75	.096 43.545
680-6D	.375 9.525	-6	.5625-18UNJF-3B	1.64 <i>41.66</i>	1.07 27.18	.28 7.11	.92 23.37	.69 17.53	.055 24.948
680-8D	. 500 12.700	-8	.750-16UNJF-3B	1.76 <i>44.70</i>	1.15 29.21	. 38 9.65	.94 23.88	.88 22.35	.086 39.009
680-10D	.625 15.875	-10	.875-14UNJF-3B	1.94 <i>4</i> 2.28	1.27 32.26	.48 12.19	1.12 28.45	1.00 25.40	. 121 <i>54</i> .885
680-12D	. 750 19.050	-12	1.0625-12UNJ-3B	2.20 55.88	1.59 <i>40.39</i>	.59 14.99	1.38 35.05	1.25 31.75	.197 89.358
680-16D	1.000 25.400	-16	1.3125-12UNJ-3B	2.79 70.87	1.93 <i>4</i> 9. <i>0</i> 2	. 79 20.07	1.50 38.10	1.50 38.10	.306 138.799
680-20D	1.250 31.750	-20	1.625-12UNJ-3B	3.19 <i>81.03</i>	2.23 56.64	1.04 26.42	1.78 <i>45.21</i>	1.81 <i>45.97</i>	. 510 231.332
680-24D	1.500 38.100	-24	1.875-12UNJ-3B	3.55 90.17	2.47 62.74	1.28 32.51	2.03 51.56	2.12 53.85	.668 302.000
680-32D	2.000 50.800	-32	2.500-12UNJ-3B	4.00 101.60	2.86 72.64	1.68 <i>4</i> 2.67	2.53 64.26	2.75 69.85	1.156 524.353

25634 Straight Flareless Fitting (Field Attachable)

Flareless Swivel NAS-1760, M83798/4 Mates with MS33514/AS4375 type connectors.








25636 45° Elbow Flareless Fitting (Field Attachable)

Flareless Swivel NAS-1760, M83798/5 Mates with MS33514/AS4375 type connectors.




NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size O.D.	Hose Size	<u>~~~~~</u>	Nominal A	Cut Factor B	Nominal C	Nominal D	E	Nominal
25636-4-4S	.250	-4	.4375-20UNJF-3B	1.83	1.26	.16	.54	.56	.074
	6.350			46.48	32.00	4.06	13.72	14.22	33.566
25636-6-6D	.375	-6	.5625-18UNJF-3B	2.00	1.42	.28	.65	.69	.054
	9.525			50.80	36.07	7.11	16.51	17.53	24.494
25636-8-8D	.500	-8	.750-16UNJF-3B	2.16	1.56	.37	.70	.88	.085
	12.700			54.86	39.62	9.40	17.78	22.35	38.555
25636-10-10D	.625	-10	.875-14UNJF-3B	2.38	1.71	.48	.81	1.00	.120
	15.875			60.45	43.43	12.19	20.57	25.40	54.431
25636-12-12D	.750	-12	1.0625-12UNJ-3B	2.61	1.90	.59	.91	1.25	.195
	19.050			66.29	48.26	14.99	23.11	31.75	88.450
25636-16-16D	1.000	-16	1.3125-12UNJ-3B	3.19	2.34	.79	.97	1.50	.292
	25.400			81.03	59.44	20.07	24.64	38.10	132.449
25636-20-20D	1.250	-20	1.625-12UNJ-3B	3.60	2.64	1.04	1.11	1.81	.517
	31.750			91.44	67.06	26.42	28.19	45.97	234.507

25638 90° Elbow Flareless Fitting (Field Attachable)

Flareless Swivel NAS-1760, M83798/6 Mates with MS33514/AS4375 type connectors.




NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size O.D.	Hose Size	<u>^</u>	Nominal A	Cut Factor B	Nominal C	Nominal D	E	Nominal
25638-4-4S	.250	-4	.4375-20UNJF-3B	1.50	.94	.16	.98	.56	.076
	6.350			38.10	23.88	4.06	24.89	14.22	34.473
25638-6-6D	.375	-6	.5625-18UNJF-3B	1.64	1.07	.28	1.21	.69	.056
	9.525			41.66	27.18	7.11	30.73	17.53	25.401
25638-8-8D	.500	-8	.750-16UNJF-3B	1.76	1.15	.38	1.28	.88	.088
	12.700			44.70	29.21	9.65	32.51	22.35	39.916
25638-10-10D	.625	-10	.875-14UNJF-3B	1.94	1.27	.48	1.51	1.00	.127
	15.875			49.28	32.26	12.19	38.35	25.40	57.606
25638-12-12D	.750	-12	1.0625-12UNJ-3B	2.20	1.59	.59	1.78	1.25	.204
	19.050			55.88	40.39	14.99	45.21	31.75	93.440
25638-16-16D	1.000	-16	1.3125-12UNJ-3B	2.79	1.93	.79	1.94	1.50	.311
	25.400			70.87	49.02	20.07	49.28	38.10	141.067
25638-20-20D	1.250	-20	1.625-12UNJ-3B	3.19	2.23	1.04	2.26	1.81	.545
	31.750			81.03	56.64	26. <i>4</i> 2	57.40	45.97	247.208



681 Straight Flange Fitting (Field Attachable)

Swivel Flange (MS20756) M83798/7




NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size O.D.	Hose Size	Nominal A	Cut Factor B	Nominal C	Nominal
681-12D	.75	-12	1.85	1.25	.59	.157
	19.05		46.99	31.75	14.99	71.214
681-16D	1.00	-16	2.32	1.46	.79	.239
	25.40		58.93	37.08	20.07	108.409
681-20D	1.25	-20	2.63	1.67	1.04	.345
	31.75		66.80	42.42	26.42	156.489
681-24D	1.50	-24	2.68	1.60	1.28	.432
	38.10		68.07	40.64	32.51	195.952

683 45° Flange Fitting (Field Attachable)

Swivel Flange (MS20756) M83798/8



NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size O.D.	Hose Size	Nominal A	Cut Factor B	Nominal C	Nominal D	Nominal
683-12D	.75	-12	2.17	1.57	.59	.47	.160
	19.05		55.12	39.88	14.99	11.94	72.575
683-16D	1.00	-16	2.72	1.87	.79	.50	.237
	25.40		69.09	47.50	20.07	12.70	107.501
683-20D	1.25	-20	3.06	2.11	1.04	.57	.362
	31.75		77.72	53.59	26.42	14.48	164.200
683-24D	1.50	-24	3.37	2.29	1.28	.62	.454
	38.10		85.60	58.17	32.51	15.75	205.931



685 90° Elbow Flange Fitting (Field Attachable)


B

Swivel Flange (MS20756) M83798/9


NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Tube Size O.D.	Hose Size	Nominal A	Cut Factor B	Nominal C	Nominal D	Nominal
685-12D	.75	-12	2.20	1.59	.59	1.16	.170
	19.05		55.88	40.39	14.99	29.46	77.111
685-16D	1.00	-16	2.79	1.93	.79	1.28	.256
	25.40		58.17	49.02	20.07	32.51	116.120
685-20D	1.25	-20	3.19	2.23	1.04	1.50	.393
	31.75		81.03	56.64	26.42	38.10	178.262
685-24D	1.50	-24	3.55	2.47	1.28	1.69	.485
	38.10		90.17	62.74	32.51	42.93	219.992






EXAMPLE OF PART NUMBER



Hose Assemblies with FLARE fittings meet the requirements of MIL-H-83796 and applicable M83796 slash sheets. Fittings mate with MS33656/AS4395 type connectors. Assembly length measured from END of nipple to END of nipple.

Assemblies with Flare Fittings




NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	A	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156001-3S-L	156-3	676-3S	676-3S	L-1.48	1.75	.163
				L-37.59	44.45	73.936
156001-4S-L	156-4	676-4S	676-4S	L-1.48	2.00	.243
				L-37.59	50.80	110.223
156001-5S-L	156-5	676-5S	676-5S	L-1.52	2.25	.292
				L-38.61	57.15	132.449
156001-6D-L	156-6	676-6D	676-6D	L-1.68	2.50	.233
				L-42.67	63.50	105.687
156001-8D-L	156-8	676-8D	676-8D	L-1.94	3.50	.324
				L-49.28	88.90	146.964
156001-10D-L	156-10	676-10D	676-10D	L-2.10	4.00	.428
				L-53.34	101.60	194.138
156001-12D-L	156-12	676-12D	676-12D	L-2.22	4.50	.599
				L-56.39	114.30	271.702
156001-16D-L	156-16	676-16D	676-16D	L-2.68	5.50	.890
				L-68.07	139.70	403.697
156001-20D-L	156-20	676-20D	676-20D	L-3.08	8.00	1.129
				L-78.23	203.20	512.106
156001-24D-L	156-24	676-24D	676-24D	L-3.40	9.00	1.600
				L-86.36	228.60	725.748
156001-32D-L	156-32	676-32D	676-32D	L-4.08	12.50	2.720
				L-103.63	317.50	1233.771

M83796/1 Style A



Assemblies with Flare Fittings




Straight-To-45° Elbow

NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	2	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156003-3S-L	156-3	676-3S	678-3S	L-1.89 <i>L-48.01</i>	1.75 <i>44.4</i> 5	. 170 77.111
156003-4S-L	156-4	676-4S	678-4S	L-1.81 <i>L-45.97</i>	2.00 50.80	.245 111.130
156003-5S-L	156-5	676-5S	678-5S	L-1.90 <i>L-4</i> 8.26	2.25 57.15	.298 135.171
156003-6D-L	156-6	676-6D	678-6D	L-2.06 <i>L-53.32</i>	2.50 63.50	. 231 104.780
156003-8D-L	156-8	676-8D	678-8D	L-2.28 <i>L-57.91</i>	3.50 88.90	. 321 145.603
156003-10D-L	156-10	676-10D	678-10D	L-2.49 <i>L-63.25</i>	4.00 101.60	.426 193.230
156003-12D-L	156-12	676-12D	678-12D	L-2.83 <i>L-71.88</i>	4.50 114.30	.590 267.620
156003-16D-L	156-16	676-16D	678-16D	L-3.37 <i>L-85.60</i>	5.50 139.70	.870 394.625
156003-20D-L	156-20	676-20D	678-20D	L-3.84 <i>L-97.54</i>	8.00 203.20	1.238 561.547
156003-24D-L	156-24	676-24D	678-24D	L-4.23 <i>L-107.44</i>	9.00 228.60	1.661 753.417
156003-32D-L	156-32	676-32D	678-32D	L-4.95 <i>L-127.7</i> 3	12.50 317.50	2.704 1226.514

M83796/1 Style C



Straight-To-90° Elbow


NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	<i>₹</i>	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156005-3S-L	156-3	676-3S	680-3S	L-1.53 <i>L-38.86</i>	1.75 44.45	. 173 78.471
156005-4S-L	156-4	676-4S	680-4S	L-1.68 L-42.67	2.00 50.80	.248 112.941
156005-5S-L	156-5	676-5S	680-5S	L-1.74 <i>L-44.20</i>	2.25 57.15	. 302 136.985
156005-6D-L	156-6	676-6D	680-6D	L-1.91 <i>L-48.51</i>	2.50 63.50	.235 106.594
156005-8D-L	156-8	676-8D	680-8D	L-2.12 <i>L-53.85</i>	3.50 88.90	.329 149.232
156005-10D-L	156-10	676-10D	680-10D	L-2.32 <i>L-5</i> 9.93	4.00 101.60	.437 198.220
156005-12D-L	156-12	676-12D	680-12D	L-2.70 <i>L-68.58</i>	4.50 114.30	.612 277.599
156005-16D-L	156-16	676-16D	680-16D	L-3.27 <i>L-</i> 83.06	5.50 139.70	.900 408.233
156005-20D-L	156-20	676-20D	680-20D	L-3.77 <i>L-95.76</i>	8.00 203.20	1.265 573.794
156005-24D-L	156-24	676-24D	680-24D	L-4.17 <i>L-105.92</i>	9.00 228.60	1.711 776.097
156005-32D-L	156-32	676-32D	680-32D	L-4.90 <i>L-124.4</i> 6	12.50 317.50	2.784 1262.801

M83796/1 Style E




EXAMPLE OF PART NUMBER



Assembly length measured from END of nipple to END of nipple.

Assemblies with Double Elbow Flare Fittings



NOTE: English measurements in **BOLD**; metric measurements in <u>ITALICS</u>.


#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	£	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156060A(L)S*	156-3	678-3S	678-3S	L-2.30	1.75	.177
				L-58.42	44.45	80.286
156060B(L)S*	156-4	678-4S	678-4S	L-2.14	2.00	.247
				L-54.36	50.80	112.037
156060C(L)S*	156-5	678-5S	678-5S	L-2.28	2.25	.305
				L-57.91	57.15	138.346
156060D(L)D*	156-6	678-6D	678-6D	L-2.44	2.50	.229
				L-61.98	63.50	103.873
156060E(L)D*	156-8	678-8D	678-8D	L-2.62	3.50	.319
				L-66.55	88.90	114.696
156060F(L)D*	156-10	678-10D	678-10D	L-2.88	4.00	.425
				L-73.15	101.60	192.777
156060G(L)D*	156-12	678-12D	678-12D	L-3.44	4.50	.580
				L-87.38	114.30	263.084
156060H(L)D*	156-16	678-16D	678-16D	L-4.06	5.50	.850
				L-103.12	139.70	385.554
156060J(L)D*	156-20	678-20D	678-20D	L-4.60	8.00	1.346
				L-116.84	203.20	610.535
156060K(L)D*	156-24	678-24D	678-24D	L-5.06	9.00	1.721
				L-128.52	228.60	780.633
156060L(L)D*	156-32	678-32D	678-32D	L-5.82	12.50	2.688
				L-147.83	317.50	1219.356

M83796/1 Style G

^{*} See "Twist Angle" Measurement on Page 4



Assemblies with Double Elbow Flare Fittings




45° Elbow-To-90° Elbow

NOTE: English measurements in <u>BOLD</u>; metric measurements in <u>ITALICS</u>.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	2	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156062A(L)S*	156-3	678-3S	680-3S	L-1.94 <i>L-49.28</i>	1.75 <i>44.4</i> 5	.179 81.193
156062B(L)S*	156-4	678-4S	680-4S	L-2.01 <i>L-51.05</i>	2.00 50.80	. 250 113.398
156062C(L)S*	156-5	678-5S	680-5S	L-2.12 <i>L-53.85</i>	2.25 57.15	.309 140.160
156062D(L)D*	156-6	678-6D	680-6D	L-2.29 <i>L-58.17</i>	2.50 63.50	.233 105.69
156062E(L)D*	156-8	678-8D	680-8D	L-2.46 <i>L-62.48</i>	3.50 88.90	.326 147.871
156062F(L)D*	156-10	678-10D	680-10D	L-2.71 L-68.83	4.00 101.60	.436 197.766
156062G(L)D*	156-12	678-12D	680-12D	L-3.31 L-84.07	4.50 114.30	. 601 272.609
156062H(L)D*	156-16	678-16D	680-16D	L-3.96 L-100.58	5.50 139.70	. 879 398.708
156062J(L)D*	156-20	678-20D	680-20D	L-4.53 L-115.06	8.00 203.20	1.374 623.236
156062K(L)D*	156-24	678-24D	680-24D	L-5.00 L-127.00	9.00 228.60	1.772 809.766
156062L(L)D*	156-32	678-32D	680-32D	L-5.77 <i>L-146.56</i>	12.50 317.50	2.768 1255.544

^{*} See "Twist Angle" Measurement on Page 4

M83796/1 Style J



metric measurements in ITALICS.

90° Elbow-To-90° Elbow

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	A	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156115A(L)S*	156-3	680-3S	680-3S	L-1.58 <i>L-40.13</i>	1.75 44.45	. 182 82.555
156115B(L)S*	156-4	680-4S	680-4S	L-1.88 <i>L-47.75</i>	2.00 50.80	.253 114.759
156115C(L)S*	156-5	680-5S	680-5S	L-1.96 <i>L-49.78</i>	2.25 57.15	. 312 141.521
156115D(L)D*	156-6	680-6D	680-6D	L-2.14 <i>L-54.36</i>	2.50 63.50	.237 107.501
156115E(L)D*	156-8	680-8D	680-8D	L-2.30 <i>L-58.42</i>	3.50 88.90	. 334 151.450
156115F(L)D*	156-10	680-10D	680-10D	L-2.54 <i>L-64.52</i>	4.00 101.60	. 446 202.302
156115G(L)D*	156-12	680-12D	680-12D	L-3.18 <i>L-80.77</i>	4.50 114.30	.622 282.135
156115H(L)D*	156-16	680-16D	680-16D	L-3.86 <i>L-98.04</i>	5.50 139.70	.909 <i>412.316</i>
156115J(L)D*	156-20	680-20D	680-20D	L-4.46 <i>L-113.28</i>	8.00 203.20	1.402 635.937
156115K(L)D*	156-24	680-24D	680-24D	L-4.94 <i>L-125.4</i> 8	9.00 228.60	1.822 826.445
156115I (L)D*	156-32	680-32D	680-32D	L-5.72	12.50	2.848


^{*} See "Twist Angle" Measurement on Page 4

M83796/1 Style L




1291.831

L-145.29 317.50




EXAMPLE OF PART NUMBER



Hose Assemblies with FLARELESS fittings meet the requirements of MIL-H-83796 and applicable M83796 slash sheets. Fittings mate with MS33514/AS4375 type connectors. Assembly length measured from END of nipple to END of nipple. See "MEASUREMENT OF FLARELESS HOSE ASSEMBLIES" to convert to/from GAGE POINT to GAGE POINT assembly length.

Assemblies with Flareless Fittings



Straight-To-Straight


NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	2	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156141-4S-L	156-4	25634-4-4S	25634-4-4S	L-1.92	2.00	.237
				L-48.77	50.80	107.501
156141-6D-L	156-6	25634-6-6D	25634-6-6D	L-2.18	2.50	.231
				L-55.37	63.50	104.780
156141-8D-L	156-8	25634-8-8D	25634-8-8D	L-2.48	3.50	.315
				L-62.99	88.90	142.882
156141-10D-L	156-10	25634-10-10D	25634-10-10D	L-2.68	4.00	.421
				L-68.07	101.60	190.962
156141-12D-L	156-12	25634-12-12D	25634-12-12D	L-3.00	4.50	.609
				L-76.20	114.30	276.238
156141-16D-L	156-16	25634-16-16D	25634-16-16D	L-3.60	5.50	.871
				L-91.44	139.70	395.079
156141-20D-L	156-20	25634-20-20D	25634-20-20D	L-4.06	8.00	1.422
				L-103.12	203.20	645.008

M83796/3 Style A




Assemblies with Flareless Fittings



Straight-To-45° Elbow

		<u>/////</u> /				
#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	\mathcal{A}_{\star}	12 in. <i>(304.8 mm)</i> Ass'y Weight Ib. <i>(g)</i>
156143-4S-L	156-4	25634-4-4S	25636-4-4S	L-2.22 <i>L-56.39</i>	2.00 50.80	.242 109.770
156143-6D-L	156-6	25634-6-6D	25636-6-6D	L-2.51 <i>L-63.75</i>	2.50 63.50	.228 103.419
156143-8D-L	156-8	25634-8-8D	25636-8-8D	L-2.80 <i>L-71.12</i>	3.50 88.90	.317 143.889
156143-10D-L	156-10	25634-10-10D	25636-10-10D	L-3.05 <i>L-77.47</i>	4.00 101.60	.423 191.870
156143-12D-L	156-12	25634-12-12D	25636-12-12D	L-3.40 <i>L-86.36</i>	4.50 114.30	.606 274.877
156143-16D-L	156-16	25634-16-16D	25636-16-16D	L-4.14 <i>L-105.16</i>	5.50 139.70	.861 390.543
156143-20D-L	156-20	25634-20-20D	25636-20-20D	L-4.67 <i>L-118.62</i>	8.00 203.20	1.398 634.122

M83796/3 Style C




Straight-To-90° Elbow

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	A	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156145-4S-L	156-4	25634-4-4S	25638-4-4S	L-1.90	2.00	.247
				L-48.26	50.80	112.037
156145-6D-L	156-6	25634-6-6D	25638-6-6D	L-2.16	2.50	.235
				L-54.86	63.50	106.594
156145-8D-L	156-8	25634-8-8D	25638-8-8D	L-2.39	3.50	.326
				L-60.71	88.90	147.871
156145-10D-L	156-10	25634-10-10D	25638-10-10D	L-2.61	4.00	.440
				L-66.29	101.60	199.581
156145-12D-L	156-12	25634-12-12D	25638-12-12D	L-3.09	4.50	.623
				L-78.49	114.30	282.588
156145-16D-L	156-16	25634-16-16D	25638-16-16D	L-3.73	5.50	.895
				L-94.74	139.70	405.965
156145-20D-L	156-20	25634-20-20D	25638-20-20D	L-4.26	8.00	1.447
				L-108.20	203.20	656.348

M83796/3 Style E




EXAMPLE OF PART NUMBER



Assembly length measured from END of nipple to END of nipple. See "MEASUREMENT OF FLARELESS HOSE ASSEMBLIES" to convert to GAGE POINT to GAGE POINT assembly length.

Assemblies with Double Elbow Flareless Fittings



NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.


#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	R.	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156190B(L)S*	156-4	25636-4-4S	25636-4-4S	L-2.52	2.00	.247
				L-64.01	50.80	107.501
156190D(L)D*	156-6	25636-6-6D	25636-6-6D	L-2.84	2.50	.226
				L-72.14	63.50	102.512
156190E(L)D*	156-8	25636-8-8D	25636-8-8D	L-3.12	3.50	.318
				L-79.25	88.90	144.242
156190F(L)D*	156-10	25636-10-10D	25636-10-10D	L-3.42	4.00	.425
				L-86.87	101.60	192.777
156190G(L)D*	156-12	25636-12-12D	25636-12-12D	L-3.80	4.50	.602
				L-96.52	114.30	273.063
156190H(L)D*	156-16	25636-16-16D	25636-16-16D	L-4.68	5.50	.851
				L-118.87	139.70	386.007
156190J(L)D*	156-20	25636-20-20D	25636-20-20D	L-5.28	8.00	1.374
				L-134.11	203.20	623.236

M83796/3 Style G

^{*} See "Twist Angle" Measurement on Page 4



Assemblies with Double Elbow Flareless Fittings




45° Elbow-To-90° Elbow

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	A.	12 in. <i>(304.8 mm)</i> Ass'y Weight Ib. <i>(g)</i>
156192B(L)S*	156-4	25636-4-4S	25638-4-4S	L-2.20	2.00	.252
156192D(L)D*	156-6	25636-6-6D	25638-6-6D	L-55.88 L-2.49	50.80 2.50	114.305 . 233
130132B(E)B	130 0	23030 0 00	25050 0 00	L-63.25	63.50	105.687
156192E(L)D*	156-8	25636-8-8D	25638-8-8D	L-2.71	3.50	.328
156192F(L)D*	156-10	25636-10-10D	25638-10-10D	<i>L-68.83</i> L-2.98	88.90 4.00	148.778 . 442
				L-75.69	101.60	200.488
156192G(L)D*	156-12	25636-12-12D	25638-12-12D	L-3.49 <i>L-88.65</i>	4.50 114.30	. 619 280.774
156192H(L)D*	156-16	25636-16-16D	25638-16-16D	L-4.27	5.50	.885
				L-108.46	139.70	401.429
156192J(L)D*	156-20	25636-20-20D	25638-20-20D	L-4.87	8.00	1.423
				L-123.44	203.20	645.462

M83796/3 Style J

metric measurements in ITALICS.

^{*} See "Twist Angle" Measurement on Page 4




90° Elbow-To-90° Elbow

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	2	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156235B(L)S*	156-4	25638-4-4S	25638-4-4S	L-1.88 <i>L-47.75</i>	2.00 50.80	.257 116.573
156235D(L)D*	156-6	25638-6-6D	25638-6-6D	L-2.14 <i>L-54.36</i>	2.50 63.50	.239 108.409
156235E(L)D*	156-8	25638-8-8D	25638-8-8D	L-2.30 <i>L-58.42</i>	3.50 88.90	. 338 153.314
156235F(L)D*	156-10	25638-10-10D	25638-10-10D	L-2.54 <i>L-64.52</i>	4.00 101.60	.458 207.745
156235G(L)D*	156-12	25638-12-12D	25638-12-12D	L-3.18 <i>L-80.77</i>	4.50 114.30	.636 288.485
156235H(L)D*	156-16	25638-16-16D	25638-16-16D	L-3.86 <i>L-98.04</i>	5.50 139.70	.919 <i>416.851</i>
156235J(L)D*	156-20	25638-20-20D	25638-20-20D	L-4.46 <i>L-113.28</i>	8.00 203.20	1.472 667.688


M83796/3 Style L

^{*} See "Twist Angle" Measurement on Page 4






EXAMPLE OF PART NUMBER



Hose Assemblies with MS20756 FLANGE fittings meet the requirements of MIL-H-83796 and applicable M83796 slash sheets.

Assemblies with MS20756 Flange Fittings



Straight-To-Straight


NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	A	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156430-12D-L	156-12	681-12D	681-12D	L-2.50	4.50	.560
				L-63.50	114.30	254.012
156430-16D-L	156-16	681-16D	681-16D	L-2.92	5.50	.809
				L-74.17	139.00	336.956
156430-20D-L	156-20	681-20D	681-20D	L-3.34	8.00	1.128
				L-84.84	203.20	511.652
156430-24D-L	156-24	681-24D	681-24D	L-3.20	9.00	1.469
				L-81.28	228.60	666.327

M83796/9 Style A



Assemblies with MS20756 Flange Fittings




Straight-To-45° Elbow

NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	A	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156432-12D-L	156-12	681-12D	683-12D	L-2.82	4.50	.555
				L-71.63	114.30	251.744
156432-16D-L	156-16	681-16D	683-16D	L-3.33	5.50	.792
				L-84.58	139.00	359.245
156432-20D-L	156-20	681-20D	683-20D	L-3.78	8.00	1.123
				L-96.01	203.20	509.384
156432-24D-L	156-24	681-24D	683-24D	L-3.89	9.00	1.444
				L-98.81	228.60	654.987

M83796/9 Style C



Straight-To-90° Elbow


NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	£	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156434-12D-L	156-12	681-12D	685-12D	L-2.84	4.50	.567
				L-72.14	114.30	257.187
156434-16D-L	156-16	681-16D	685-16D	L-3.39	5.50	.809
				L-86.11	139.00	366.956
156434-20D-L	156-20	681-20D	685-20D	L-3.90	8.00	1.148
				L-99.06	203.20	520.724
156434-24D-L	156-24	681-24D	685-24D	L-4.07	9.00	1.463
				L-103.38	228.60	519.953


M83796/9 Style E



EXAMPLE OF PART NUMBER



Assemblies with Double Elbow Flange Fittings



45° Elbow-to-45°-Elbow

NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.


#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	2	12 in. (304.8 mm) Ass'y Weight Ib. (g)
156445G(L)D*	156-12	683-12D	683-12D	L-3.14	4.50	.549
				L-79.76	114.30	249.022
156445H(L)D*	156-16	683-16D	683-16D	L-3.74	5.50	.775
				L-95.00	139.00	351.534
156445J(L)D*	156-20	683-20D	683-20D	L-4.22	8.00	1.118
				L-107.19	203.20	507.116
156445K(L)D*	156-24	683-24D	683-24D	L-4.58	9.00	1.418
				L-116.33	228.60	517.912

M83796/9 Style G



^{*} See "Twist Angle" Measurement on Page 4

Assemblies with Double Elbow Flange Fittings




45° Elbow-To-90° Elbow

NOTE: English measurements in **BOLD**; metric measurements in <u>ITALICS</u>.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	2	12 in. <i>(304.8 mm)</i> Ass'y Weight Ib. <i>(g)</i>
156447G(L)D*	156-12	683-12D	685-12D	L3.16	4.50	.559
				L-80.26	114.30	253.558
156447H(L)D*	156-16	683-16D	685-16D	L-3.80	5.50	.792
				L-96.52	139.00	359.245
156447J(L)D*	156-20	683-20D	685-20D	L-4.34	8.00	1.143
				L-110.24	203.20	518.456
156447K(L)D*	156-24	683-24D	685-24D	L-4.76	9.00	1.437
				L-120.90	228.60	651.812

M83796/9 Style J

^{*} See "Twist Angle" Measurement on Page 4



90° Elbow-To-90° Elbow

NOTE: English measurements in **BOLD**; metric measurements in *ITALICS*.

#	Hose	Left Hand Hose Fitting	Right Hand Hose Fitting	H Cut-Factor	A	12 in. <i>(304.8 mm)</i> Ass'y Weight Ib. <i>(g)</i>
156456G(L)D*	156-12	685-12D	685-12D	L-3.18	4.50	.568
				L-80.77	114.30	257.641
156456H(L)D*	156-16	685-16D	685-16D	L-3.86	5.50	.809
				L-98.04	139.00	366.956
156456J(L)D*	156-20	685-20D	685-20D	L-4.46	8.00	1.168
				L-113.28	203.20	529.796
156456K(L)D*	156-24	685-24D	685-24D	L-4.94	9.00	1.456
				L-125.48	228.60	660.431

M83796/9 Style L



^{*} See "Twist Angle" Measurement on Page 4

Coil and Sleeve Accessories

FIRE SLEEVED TYPE HOSE ASSEMBLIES



2650 FIRESLEEVE CODE F Red Silicone Fiberglass -65° to 450°F (-54° to 232°C) AS-1072 5027 end dip for 2650 firesleeve to prevent wicking.

NOTE: Temperature rating is for Firesleeve only. Request P-104-29 for assembly instructions.

INTERNALLY SUPPORTED TYPE HOSE ASSEMBLIES



2646 INTERNAL SUPPORT COIL CODE B Corrosion Resistant Steel SAE 30302/AMS5688

Request P-104-41 for assembly instructions.

TUBULAR ABRASION SLEEVES



2606 CODE V TRANSLUCENT VINYL -90° to 158°F (-68° to 70°C) MIL-I-7444 TYPE I CLASS I



2637-SIZE B CODE T BLACK TFE -65° to 450°F (-54° to 232°C) AS1291

HEAT SHRINK ABRASION SLEEVES



2629 CODE M BLACK POLYOLEFIN -67° to 275°F (-55° to 135°C) As1073 and MIL-I-23053/5



2642 CODE Z TRANSPARENT FEP TFE -88° to 392°F (-67° to 200°C) MIL-I-23053/11

FIRE SLEEVE CLAMP

Fire Sleeve Clamp Versus Hose Assembly Size



	10781							
Hose	-4-13CR	-4-22CR	-4-32CR	-4-48CR				
111		-3/-8	-10/-16	-20/-32				
112		-4/-8	-10/-12	-16				
124	-3/-4/-5	-6/-12	-16Z/-20Z	-24Z				
156	-3	-4/-10	-12/-16	-20/-32				
170		-4/-10	-12/-16					
171		-4/-10	-12					
193	-2/-3	-4/-10						

SPIRAL WRAP ABRASION SLEEVES



2661-SIZE NB CODE X BLACK NYLON -65° to 300°F (-54° to 149°C) AS1294



2681 CODE U BLACK TFE -65° to 450°F (-54° to 232°C) AS1293



HOS	se or Sleeve						Hose S	ize						
Code	Туре	Part					nts in BOL LICS / g po				INDERLIN	IED BOLD	<u>l</u> .	
Code	Туре	No.	-3	-4	-5	-6	-8	-10	-12	-16	-20	-24	-32	
None	Hose only.	156	.0083	.0104	.507 12.88 .0120 (.214)	.0129		.0216	.0259	30.14	.0506	44.07 .0688	54.3 8	
Н	Hose with integral extruded red silicone fire cover is designed to meet the fire resistance requirements of AS1055, TSO-C53a and TSO-C75 as applicable.	156- SIZE H	.0212	.0242	.810 20.57 .0274 (.489)	.0292		28.60 .0447	.0524	37.31 .0666	1.750 44.45 .0872 (1.56)			
K	Hose with braided polyester abrasion cover, blue.	156- SIZE K	.0102	.0125	.0143	.0155	.762 19.35 .0198 (.353)	.0253	.0302	32.44 .0418	1.558 39.57 .0571 (1.02)	46.36 .0765	56.6 7	
F	2650 Red silicone-fiberglass FIRE SLEEVE enables hose assemblies to meet the fire test requirements of AS1055, TSO-C53a and TSO-C75 as applicable.	2650- SIZE	.0108	.0117	.0133	.0167	27.69	35.05 .0275	38.10 .0292	.0367	49.53 .0317	55.63 .0367	69.60	
М	Shrink abrasion sleeve (black), per AS1073 and MIL-I-23053/5. Polyolefin. Temperature limit -67°F to 275°F.	2629- SIZE	.0008	.0015	.577 14.66 .0015 (.027)	.0021		.0036	26.75 .0036	.0056	39.62 .0047	47.02 .0092		
т	Tubular abrasion sleeve (black), per AS1291B. TFE. Temperature limit -65°F to 450°F.	2637- SIZE B	.0028	.0031	.635 16.13 .0038 (.068)	.0041								
٧	Tubular abrasion sleeve (translucent), Per MIL-I-7444 Type I Class 1. Vinyl. Temperature limit	2606- SIZE	.0016	.0018	.0021	.0028		.0050	28.35 .0058	31.88 .0070	41.96 .0112		2.480 62.99 .0235 (.420	
X	Spiral abrasion sleeve (black), per AS1294. Nylon. Temperature limit -121°F to 300°F.	2661- SIZE NB	.0008	.0021	.577 14.66 .0021 (.038)	.0021		.0032	26.04 .0059	1.251 31.78 .0078 (.139)	38.91 .0097	45.69 .0102	2.205 56.01 .0128 (.229	
Z	Shrink abrasion sleeve (transparent) Per MIL-I-23053/11. FEP. Temperature limit -88°F to 392°F.	2642- SIZE	.0012	.0016	.0026	.0029	.730 18.54 .0047 (.084)	.0068	26.39 .0095	.0107	39.27 . 0109	46.05 .0140		

Coils and Sleeves Size(s) Reference Only

Letter Code	В	F	M	Т	U	V	Х	Z
Hose Part No.	Internal Support Coil	** Silicone Fiberglass Firesleeve	Polyolefin Shrink Sleeve	TFE Abrasion Sleeve	TFE Spiral Wrap	Vinyl Abrasion Sleeve	Nylon Spiral Wrap	FEP Shrink Sleeve
156-3*		2650-7	2629-16	2637-13B	2681-7	2606-6	2661-8NB	2642-11
156-4		2650-8	2629-28	2637-15B	2681-11	2606-7	2661-16NB	2642-12
156-5		2650-9	2629-28	2637-18B	2681-11	2606-8	2661-16NB	2642-14
156-6		2650-10	2629-32	2637-19B	2681-11	2606-9	2661-16NB	2642-16
156-8	2646-13CR	2650-12	2629-32	2637-22B	2681-11	2606-10	2661-24NB	2642-20
156-10	2646-17CR	2650-16	2629-48		2681-11	2606-14	2661-24NB	2642-24
156-12	2646-21CR	2650-18	2629-48		2681-15	2606-16	2661-32NB	2642-28
156-16	2646-27CR	2650-22	2629-64		2681-15	2606-18	2661-40NB	2642-32
156-20	2646-35CR	2650-26	2629-74		2681-15	2606-24	2661-48NB	2642-41
156-24	2646-43CR	2650-30	2629-96		2681-15	2606-28	2661-56NB	2642-48
156-32	2646-56CR	2650-38			2681-15	2606-36	2661-64NB	

^{*176-}X same as 156-X.



^{**}Size(s) per HS2650 only for TSO, AS1055 compliance.

^{***}Not recommended.

Safety Guide

106-SG

Parker Safety Guide for Selecting and Using Hose, Tubing, Fittings and Related Accessories



DANGER: Failure or improper selection or improper use of hose, fittings, or related accessories can cause death, personal injury and property damage. Possible consequences of failure or improper selection or improper use of hose, fittings, or related accessories include but are not limited to:

- Explosion or burning of the conveyed fluid.
- Contact with conveyed fluids, hot, cold, toxic and injurious.
- Dangerously whipping hose.
- Loss of control system.

- High velocity fluid discharge.
- Fittings thrown off at high speed.
- · Injection by high-pressure fluid discharge.

Before selecting or using any Parker Hose or Fittings or related accessories, it is important that you read and follow the instructions below.

1.0 GENERAL INSTRUCTIONS

- Scope: This safety guide provides instructions for selecting and using (including assembling, installing, and maintaining) hose (including all rubber and/or PTFE products commonly called "hose" or "tubing"), fittings (including all products commonly called "fittings" or "couplings") for attachment to hose), and related accessories (including crimping and swaging machines and tooling). This safety guide is a supplement to and is to be used with, the specific Parker publications for the specific hose, fittings and related accessories that are being considered for use.
- 1.2 Fail-Safe: Hose and hose assemblies can and do fail without warning for many reasons. Design all systems and equipment in a fail-safe mode, so that failure of the hose or hose assembly will not endanger
- persons or property.

 1.3 Distribution: Provide a copy of this safety guide to each person that is responsible for selecting or using hose and fitting products. Do not select or use hose and fittings without thoroughly reading and understanding this safety guide as well as the specific Parker
- publications for the products considered or selected.

 1.4 User Responsibility: Due to the wide variety of operating conditions and uses for hose and fittings, Parker and its distributors do not represent or warrant that any particular hose or fitting is suitable for any specific end use system. Most Parker Stratoflex Products Division products are qualified to Military or Industry Standards. This safety guide does not analyze all technical parameters that must be considered in selecting a product. The user, through its own analysis and testing, is solely responsible for:

 • Making the final selection of the hose and fitting.

 • Assuring that the user's requirements are met and that the use

 - presents no health or safety hazards.
 - Providing all appropriate health and safety warnings on the
- equipment on which the hose and fittings are used.

 1.5 Additional Questions: Call the appropriate Parker technical service department if you have any questions or require any additional information. See the Parker publication for the product being considered or used, for telephone numbers of the appropriate technical service department.

 2.0 HOSE AND FITTING SELECTION INSTRUCTIONS

2.1 Electrical Conductivity: Certain applications require that a hose be nonconductive to prevent electrical current flow or maintain electrical isolation. Other applications require the hose to be sufficiently resolution. Offer applications require the nose to be sufficiently conductive to drain off static electricity; this is typical of rubber hose and of all aerospace fuel, oil and hydraulic PTFE hose. Extreme care must be exercised when selecting hose and fittings for these or any other applications in which electrical conductivity or non-conductivity is a factor

For applications that require hose to be electrically nonconductive, only special nonconductive hose can be used. The manufacturer of the equipment in which the nonconductive hose is to be used must be consulted to be certain that the hose and fittings that are selected are proper for the application. Do not use any Parker hose or fitting for any such application requiring nonconductive hose unless (i) the application is expressly approved in the Parker technical publication for the product, (ii) the manufacturer of the equipment on which the hose is to be used specifically approves the particular Parker hose and fitting for such use.

The electrical conductivity or non-conductivity of hose and fittings is dependent upon many factors and may be susceptible to change. These factors include but are not limited to the various materials, including fitting finish, used to make the hose and the fittings, how the fittings contact the hose, age and amount of deterioration of damage or other changes and other factors. Aluminum fitting finish effects

"conductivity"; anodize is non-conductive, while alodine is conductive.

2.2 Pressure: Hose selection must be made so that the published maximum recommended working pressure of the hose is equal to or greater than the maximum system pressure. Surge pressures in the system higher than the published maximum recommended working pressure would cause failure or shorten hose life. Do not confuse burst pressure or other pressure values with working pressure and do not use burst pressure or other pressure values for this purpose.

- Hose assemblies are "proof pressure" tested (normally 2 x working rated pressure) to confirm proper fabrication of the assembly. Gaseous test, including air-under-water, shall be at rated working pressure only and see 4.7 caution below. Care must be exercised to prevent water, or other fluid contaminants from unnecessarily
- contacting reinforcement, etc.

 2.3 Suction: Hoses used for suction applications must be selected to insure that the hose will withstand the vacuum and pressure of the system. Improperly selected hose may collapse in suction application.
- **2.4 Temperature:** Be certain that fluid and ambient temperatures, both steady and transient, do not exceed the limitations of the hose. Temperatures below and above the recommended limit can degrade hose to a point where a failure may occur and release fluid. Care must be taken when routing hose near hot objects (e.g. manifolds) to properly insulate and protect the hose. Fire sleeve is not intended
- 2.5 Fluid Compatibility: Hose selection must assure compatibility of the hose tube, cover, reinforcement, and fittings with the fluid media used. Actual service life can only be determined by the end user by
- history or testing under all extreme conditions and other analysis.

 2.6 Permeation: Permeation (that is, seepage through the hose) may occur from inside the hose to outside when hose is used with gases, occur from inside the nose to outside when nose is used with gase liquid and gas fuels, and refrigerants (including but not limited to such materials as helium, fuel oil, natural gas, or refrigerant). This permeation may result in high concentrations of vapors, which are potentially flammable, explosive, or toxic, and in loss of fluid. Dangerous explosions, fires, and other hazards can result when using the wrong hose for such applications. The system desiner such take into account the foot that this permettiant take into account the foot that this permettiant takes of the control of must take into account the fact that this permeation will take place and must not use hose if this permeation could be hazardous. The system designer must take into account all legal, government, insurance, or any other special regulations, which govern the use of fuels and refrigerants. Never use a hose even though the fluid compatibility is acceptable without considering the potential hazardous effects that can result from permeation through the hose assembly.
- assembly.

 Gaseous permeation, particularly through a PTFE hose, occurs primarily if the gas is "stored" at pressure in the hose. Most standards limit the amount of permissible permeation.

 Size: Transmission of power by means of pressurized fluid varies with pressure and rate of flow. The size of the components must be adequate to keep pressure losses to a minimum, and avoid damage due to beat geoperation or expecsive fluid velocity. due to heat generation or excessive fluid velocity.
- 2.8 Routing: Attention must be given to optimum routing to minimize inherent problems (kinking or flow restriction due to hose collapse). See SAE AIR1569 for further information.
- Environment: Care must be taken to insure that the hose and fittings are either compatible with or protected from the environment (that is, surrounding conditions) to which they are exposed. Environmental conditions including but not limited to ultraviolet radiation, sunlight, heat, ozone, moisture, water, salt water, chemicals and air pollutants can cause degradation and premature failure.
- 2.10 Mechanical Loads: External forces can significantly reduce hose life or cause failure. Mechanical loads, which must be considered, include excessive flexing, twist, kinking, tensile or side loads, bend radius, and vibration. Use of swivel type fittings or adapters may be required to insure no twist is put into the hose. Unusual applications may require special testing prior to hose selection.

 2.11 Physical Damage: Care must be taken to protect hose from wear,
- snagging and cutting, which can cause premature hose failure. See SAE ARP1658 for Visual Guide.
 2.12 Proper End Fitting: See instructions 3.2 through 3.5 below. Testing to industry standards such as MIL-A-5070, AS1339, J517, etc must
- substantiate these recommendations.
- 2.13 Length: When establishing a proper hose length, motion absorption, hose length changes due to pressure, and hose and machine tolerances must be considered.



- 2.14 Specifications and Standards: When selecting hose and fittings, government, industry, and Parker specifications and recommendations must be reviewed and followed as applicable.
- 2.15 Hose Cleanliness: Hose components may vary in cleanliness levels.

 Care must be taken to insure that the assembly selected has an adequate level of cleanliness and compatibility for the application. See SAE AS611 for PTFE hose assembly cleanliness levels.
- 2.16 Fire Resistant Fluids: Some fire resistant fluids require the same hose as petroleum oil. Some life resistant fluids require the same hose as petroleum oil. Some use a special hose, while a few fluids will not work with any hose at all. See instructions 2.5 and 1.5. The wrong hose may fail after a very short service. In addition, all liquids but pure water may burn fiercely under certain conditions, and even pure water leakage may be hazardous.
- 2.17 Radiant Heat: Hose can be heated to destruction without contact by such nearby items as hot manifolds or molten metal. The same heat source may then initiate a fire. This can occur despite the presence of cool air around the hose
- 2.18 Welding or Brazing: When using a torch or arc-welder in close proximity to hydraulic lines, the hydraulic lines should be removed or shielded with appropriate fire resistant materials. Flame or weld spatter could burn through the hose and possibly ignite escaping fluid resulting in a catastrophic failure. Heating of plated parts, including hose fittings and adapters, above 450° F (232° C) such as during welding, brazing, or soldering may emit deadly gases.

 2.19 Atomic Radiation: Atomic radiation affects all materials used in hose
- assemblies. Since The long-term effects may be unknown, do not
- expose hose assemblies to atomic radiation.
 HOSE AND FITTING ASSEMBLY AND INSTALLATION INSTRUCTIONS
- 3.1 Pre-Installation and Periodic Inspection: Prior to installation, a careful examination of the hose assembly must be performed. All components must be checked for correct style, size, part number, components must be checked for correct style, size, part number, length, and minimum bend radius. In addition, the hose must be examined for cleanliness, broken wires, cuts, kinks, obstructions, blisters, cover looseness, or any other visible defects. Do not use any hose that has any of these conditions. See SAE ARP1658 for illustrations of damage conditions.

 3.2 Hose and Fitting Assembly: Do not assemble a Parker fitting on a parker hose that is not expected.
- Parker hose that is not specifically listed by Parker for that fitting on a Parker hose that is not specifically listed by Parker for that fitting unless authorized in writing by the Engineering/Technical Manager or Chief Engineer of the appropriate Parker division. Do not assemble a Parker fitting on another manufacturers hose or a Parker hose to another manufacturers fitting unless: (i) the Engineering/Technical Manager or Chief Engineer of the appropriate Parker division approves the assembly in writing, (ii) the user verifies the assembly and the application through analysis and testing or (iii) fabricating MILSPEC assemblies in accordance with proper instructions. See instruction 1.4 above.
 - The Parker published instructions must be followed for assembling the fitting on the hose. These instructions are provided in the Parker fitting catalog for the specific Parker industrial fitting being used; most MILSPEC and Aerospace fitting to hose fabrication is closely controlled to authorized facilities.
- 3.3 Related Accessories: Do not crimp or swage any Parker hose or fittings with anything but the proper listed Parker swage or crimp machine and dies and in accordance with Parker published instructions. Do not crimp or swage another manufacturers hose fitting with a Parker
- crimp or swage die unless authorized in writing by the chief engineer of the appropriate Parker division.

 3.4 Parts: Do not use any Parker hose fitting part (including but not limited to socket, shell, nipple, or insert) except with the correct Parker mating parts. in accordance with Parker published instructions, unless authorized in writing by the Engineering/Technical Manager or Chief Engineer of the appropriate Parker division. <u>Do not use hose or fitting components from Parker Stratoflex Division with any hose or fitting the Components from Parker Stratoflex Division with any hose or fitting</u>
- components from Parker Stratollex Division with any nose or litting components from any other Parker Division without this specific authorization. SPD and HPD fitting components shall not be mixed.

 3.5 Reusable/Permanent: Do not reuse any reusable fitting product that blew off or pulled off a hose. Do not reuse any fitting component that is cracked or deformed beyond new part tolerance. Do not reuse hose. Do not reuse a Parker permanent (that is, crimped or swaged) hose fitting or any part thereof.
- fitting or any part thereof.

 3.6 Minimum Bend Radius: Installation of a hose at less than the minimum listed bend radius may significantly reduce the hose life and cause premature failure. Particular attention must be given to preclude sharp bending at the hose/fitting juncture. If any Stratoflex Products Division hose has been bent to any radius less than its minimum bending (miner expertise) from programment and incompany attention of the product of the programment of the programm radius (minor exceptions from proper authority) or has been kinked during installation, do not use such hose. Such hose is damaged and cannot be used and should be discarded.

 3.7 Twist Angle and Orientation: Hose installations must be such that
- relative motion of machine components does not produce twisting. No twist in the hose is permitted during installation or use. See SAE AIR1569 for additional information.
- 3.8 Securement: In many applications, it may be necessary to restrain, protect, or guide the hose to protect it from damage by unnecessary flexing, pressure surges, and contact with other mechanical components. Care must be taken to insure such restraints do not ntroduce additional stress or wear points.
- 3.9 Proper Connection of Ports: Proper physical installation of the hose requires a correctly installed port connection insuring that no twist or torque is transferred to the hose confirm proper fabrication of the assembly. Gaseous test, including air-under-water, shall be at rated

- working pressure only and see 4.7 caution below. Care must be exercised to prevent water, or other fluid contaminants from unnecessarily contacting reinforcement, etc.
- 3.10 External Damage: Proper installation is not complete without insuring that tensile loads, side loads, kinking, flattening, potential abrasion, thread damage, or damage to sealing surfaces are corrected or
- eliminated. See instruction 2.10.

 3.11 System Checkout: All air entrapment must be eliminated (see 4.7) and the system pressurized to the maximum systems pressure and checked for proper function and freedom from leaks. Personnel must stay out of potential hazardous areas while testing and using
- 3.12 Routing: Hose should be routed in such a manner so if a failure does occur, oil or fuel mist will not come into contact with hot surfaces, open
- flame, or sparks, and the chance of personal injury is minimized.

 4.0 HOSE AND FITTING INSPECTION INSTRUCTIONS

 4.1 Even with proper selection and installation, hose life may be significantly reduced without a continuing inspection program. The frequency of inspection should be determined by the system designer or end user taking into account the severity of the application and risk potential. An inspection program must be established and followed by the user and, at minimum, must include instructions 4.2 through 4.7 listed below.
- 4.2 Visual Inspection Hose/Fitting: Any of the following conditions require immediate shut down and replacement of the hose assembly: (See also ARP1658 for illustrations.)
 - Fitting slippage on hose,
 - Damaged, cut or abraded cover (any reinforcement exposed);
 Hard, stiff, heat cracked, or charred hose;

 - Cracked, damaged, or badly corroded hose or fittings;

 - Leaks at fitting or in hose;
 Kinked, crushed, flattened or twisted hose; and
 Blistered, soft, degraded, or loose cover.
 System malfunction including but not limited to, over-pressurization or pressure spikes.
- 4.3 Visual Inspection All Other: The following items must be tightened, repaired or replaced as required:
 - Leaking port conditions;
- Remove excess dirt buildup;
 Clamps, guards, shields; and
 System fluid level, fluid type and any air entrapment.

 4.4 Functional Test: Operate the system at maximum operating pressure and check for possible malfunctions and freedom from leaks Personnel must avoid potential hazardous areas while testing and using the system
- 4.5 Replacement Intervals: Specific replacement intervals must be considered based on previous service life, government or industry recommendations, or when failures could result in unacceptable downtime, damage. or injury risk. See instructions 1.2 and 4.2 above.
 4.6 Inspecting a Pressurized System: Hydraulic power is accomplished
- by utilizing high-pressure fluids to do work. Hoses, fittings, and hose assemblies all contribute to doing work by transmitting fluids at high pressures. Fluids under pressure can be dangerous and potentially lethal and, therefore, extreme caution must be exercised when working with fluids under pressure and handling the hoses transporting the fluids. From time to time, hose assemblies will fail. Usually those failures are the result of some form of misapplication, abuse, or simply wear. When hoses fail, generally the high-pressure fluids inside escape in some sort of stream which may or may not be visible to the user. Under no circumstances should the user attempt to locate the leak by "feeling" with their hands or any other part of their body. High-pressure fluids can and will penetrate the skin and cause severe tissue damage and possibly loss of limb. Even seemingly minor hydraulic fluid injection injuries must be treated by a physician with knowledge of the tissue damaging properties of hydraulic fluid.

If a hose failure occurs, immediately shut down the equipment and leave the area until pressure has been completely released from the nose assembly. Simply shutting down the hydraulic pump may or may not eliminate the pressure in the hose assembly. Many times check valves, etc., are employed in a system and can cause pressure to remain in a hose assembly even when pumps or equipment are not operating. Tirry holes in the hose, commonly known as pinholes, can eject small, dangerously powerful but hard to see streams of hydraulic fluid. It may take several minutes or even hours for the pressure to be relieved so that the hose assembly may be examined safely.

Once the pressure has been reduced to zero. the hose assembly may be taken off the equipment and examined. It must always be replaced if a failure has occurred. Never attempt to patch or repair a hose assembly that has failed. Consult the nearest Parker distributor or the appropriate Parker division for hose assembly replacement information.

Never touch or examine a failed hose assembly unless it is obvious that the hose no longer contains fluid under pressure. The highpressure fluid is extremely dangerous and can cause serious and

potentially fatal injury.

4.7 Gases: Special care should be taken when working with gaseous systems. Gases are compressible, thus increase the danger of overpressure, particularly during test. Sudden escape of gases can cause blindness if the escaping gases contact the eye and can cause freezing or other severe injuries if it contacts any other portion of the body.



Offer of Sale

The items described in this document are hereby offered for sale at prices to be established by Parker Hannifin Corporation, its subsidiaries and its authorized distributors. This offer and its acceptance by any customer ("Buyer") shall be governed by all of the following Terms and Conditions. Buyer's order for any item described in its document, when communicated to Parker Hannifin Corporation, its subsidiary or an authorized distributor ("Seller") verbally or in writing, shall constitute acceptance of this offer.

- 1. Terms and Conditions of Sale: All descriptions, quotations, proposals, offers, acknowledgments, acceptances and sales of Seller's products are subject to and shall be governed exclusively by the terms and conditions stated herein. Buyer's acceptance of any offer to sell is limited to these terms and conditions. Any terms or conditions in addition to, or inconsistent with those stated herein, proposed by Buyer in any acceptance of an offer by Seller, are hereby objected to No such additional, different or inconsistent terms and conditions shall become part of the contract between Buyer and Seller unless expressly accepted in writing by Seller. Seller's acceptance of any offer to purchase by Buyer is expressly conditional upon Buyer's assent to all the terms and conditions stated herein, including any terms in addition to, or inconsistent with those contained in Buyer's offer. Acceptance of Seller's products shall in all events constitute such assent.
- 2. Payment: Payment shall be made by Buyer net 30 days from the date of delivery of the items purchased hereunder. Any claims by Buyer for omissions or shortages in a shipment shall be waived unless Seller receives notice thereof within 30 days after Buyer's receipt of the shipment.
- 3. Delivery: Unless otherwise provided on the face hereof, delivery shall be made F.O.B. Seller's plant. Regardless of the method of delivery, however, risk of loss shall pass to Buyer upon Seller's delivery to a carrier. Any delivery dates shown are approximate only and Seller shall have no liability for any delays in delivery.
- 4. Warranty: Seller warrants that the items sold hereunder shall be free from defects in material or workmanship for a period of 365 days from the date of shipment to Buyer, or 2,00.0 hours of use, whichever expires first. THIS WARRANTY COMPRISES THE SOLE AND ENTIRE WAR. RANTY PERTAINING TO ITEMS PROVIDED HEREUNDER. SELLER MAKES NO OTHER WARRANTY, GLARANTEE, OR REPRESENTATION OF ANY KIND WHATSOEVER. ALL OTHER WARRANTIES, INCLUDING BUT NOT LIMITED TO, MERCHANTIBILITY AND FITNESS FOR PURPOSE, WHETHER EXPRESS, IMPLIED, OR ARIS. ING BY OPERATION OF LAW, TRADE USAGE, OR COURSE OF DEAL ING ARE HEREBY DISCLAIMED. NOTWITHSTANDING THE FOREGOING, THERE ARE NO WARRAN. TIES WHATSOEVER ON ITEMS BUILT OR ACQUIRED WHOLLY OR PARTIALLY, TO BUYER'S DESIGNS OR SPECIFICATIONS.
- 5. Limitation Of Remedy: SELLER'S LIABILITY ARISING FROM OR IN ANYWAY CONNECTED WITH THE ITEMS SOLD OR THIS CONTRACT SHALL BE LIMITED EXCLUSIVELYTO REPAIR OR REPLACEMENT OF THE ITEMS SOLD OR REFUND OF THE PURCHASE PRICE PAID BY BUYER, AT SELLER'S SOLE OPTION. IN NO EVENT SHALL SELLER BE LIABLE FOR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES OF ANY KIND OR NATURE WHATSOEVER, INCLUDING BUT NOT LIMITED TO LOST PROFITS ARISING FROM OR IN ANY WAY CONNECTED WITH THIS AGREEMENT OR ITEMS SOLD HEREUNDER, WHETHER ALLEGED TO ARISE FROM BREACH OF CONTRACT, EXPRESS OR IMPLIED WARRANTY, OR IN TORT, INCLUDING WITHOUT LIMITATION, NEGLIGENCE, FAILURE TO WARN OR STRICT LIABILITY.
- 6. Changes, Reschedules and Cancellations: Buyer may request to modify the designs or specifications for the items sold hereunder as well as the quantities and delivery dates thereof, or may request to cancel all or part of this order, however, no such requested modification or cancellation shall become part of the contract between Buyer and Seller unless accepted by Seller in a written amendment to this Agreement. Acceptance of any such requested modification or cancellation shall be at Seller's discretion, and shall be upon such terms and conditions as Seller may require.
- 7. Special Tooling: A tooling charge may be imposed for any special tooling, including without limitation, dies, fixtures, molds and patterns, acquired to manufacture items sold pursuant to this contract. Such special tooling shall be and remain Seller's property notwithstanding payment of any charges by Buyer. In no event will Buyer acquire any interest in apparatus belonging to Seller which is utilized in the manufacture of the items sold hereunder, even if such apparatus has been specially converted or adapted for such manufacture and notwithstanding any charges paid by Buyer. Unless otherwise agreed, Seller shall have the right to alter, discard or otherwise dispose of any special tooling or other property in its sole discretion at any time.
- 8. Buyer's Property: Any designs, tools, patterns, materials, drawings, confidential information or equipment furnished by Buyer or any other items which become Buyer's property, may be considered obsolete and may be destroyed by Seller after two (2) consecutive years have elapsed without Buyer placing an order for the items which are manufactured using such property. Seller shall not be responsible for any loss or damage to such property while it is in Seller's possession or control.
- 9. Taxes: Unless otherwise indicated on the face hereof, all prices and charges are exclusive of excise, sales, use, property, occupational or like taxes which may be imposed by any taxing authority upon the manufacture, sale or delivery of the items sold hereunder. If any such taxes must be paid by Seller or if Seller is liable for the collection of such tax, the amount thereof shall be in addition to the amounts for the items sold. Buyer agrees to pay all such taxes or to reimburse Seller therefore upon receipt of its invoice. If Buyer claims exemption from any sales, use or other tax imposed by any taxing authority, Buyer shall save Seller harmless from and against any such tax, together with any interest or penalties thereon which may be assessed if the items are held to be taxable.
- 10. Indemnity For Infringement of Intellectual Property Rights: Seller shall have no liability for infringement of any patents, trademarks, copyrights, trade dress, trade secrets or similar rights except as provided in this Part 10. Seller will defend and indemnify Buyer against allegations of infringement of U.S. patents, U.S. trademarks, copyrights, trade dress and trade secrets (hereinafter 'Intellectual Property Rights'). Seller will defend at its expense and will pay the cost of any settlement or damages awarded in an action brought against Buyer based on an allegation that an item sold pursuant to this contract infringes the Intellectual Property Rights of a third party. Seller's obligation to defend and indemnify Buyer is contingent on Buyer notifying Seller within ten (10) days after Buyer becomes aware of such allegations of infringement, and Seller having sole control over the defense of any allegations or actions including all negotiations for settlement or compromise. If an item sold hereunder is subject to a claim that it infringes the Intellectual Property Rights of a third party, Seller may, at its sole expense and option, procure for Buyer the right to continue using said item, replace or modify said item so as to make it noninfringing, or offer to accept return of said item and return the purchase price less a reasonable allowance for depreciation. Notwithstanding the foregoing, Seller shall have no liability for claims of infringement based on information provided by Buyer, or directed to items delivered hereunder for which the designs are specified in whole or part by Buyer, or infringements resulting from the modification, combination or use in a system of any item sold hereunder. The foregoing provisions of this Part 10 shall constitute Seller's sole and exclusive liability and Buyer's sole and exclusive remedy for infringement of Intellectual Property Rights.

If a claim is based on information provided by Buyer or if the design for an item delivered hereunder is specified in whole or in part by Buyer, Buyer shall defend and indemnify Seller for all costs, expenses or judgments resulting from any claim that such item infringes any patent, trademark, copyright, trade dress, trade secret or any similar right.

- 11. Force Majeure: Seller does not assume the risk of and shall not be liable for delay or failure to perform any of Seller's obligations by reason of circumstances beyond the reasonable control of Seller (hereinafter 'events of Force Majeure]. Events of Force Majeure shall include without limitation, accidents, acts of God, strikes or labor disputes, acts, laws, rules or regulations of any government or government agency, fires, floods, delays or failures in delivery of carriers or suppliers, shortages of materials and any other cause beyond Seller's control.
- 12. Entire Agreement/Governing Law: The terms and conditions set forth herein, together with any amendments, modifications and any different terms or conditions expressly accepted by Seller in writing, shall constitute the entire Agreement concerning the items sold, and there are no oral or other representations or agreements which pertain thereto. This Agreement shall be governed in all respects by the law of the State of Ohio. No actions arising out of the sale of the items sold hereunder or this Agreement may be brought by either party more than two (2) years after the cause of action accrues.



NOTES:



NOTES:



NOTES:



Markets:

- Agriculture
- Aviation/Aerospace
- Food & Beverage
- Industrial Machinery
- In-Plant Automotive
- ► Machine Tool
- Marine
- Life Sciences/ Pharmaceutical Processing
- Mobile
- ► Oil & Gas
- Packaging
- Power Generation
 & Energy
- ▶ Process
- Pulp & Paper
- Refrigeration Heating
 & Air Concitioning
- Semiconductor
- Telecommunications/ Information Technology
- Transportation

Product Information

Parker's products are vital to virtually everything that moves or requires control, including the manufacture and processing of raw materials, durable goods, infrastructure development and all forms of transport. Customer's seeking product information, distributor locations, or repair services will receive prompt attention by calling the Parker Information Center using our toll free numbers.

United States: 1-800-C-Parker (1-800-272-7537) www.parker.com

In Europe: 00800-C-PARKER-H (00800-2727-5374) from AU,BE,CH,DE,EI,FR,UK only. For other countries call +44 1442 358429 Email: epic@parker.com Fax. +44 1442 458112 www.parker.com/eu

About Parker Hannifin Corporation

Throughout the world. Parker is serving more than 400,000 customers to improve productivity and reliability in thousands of industries. Parker motion and control systems are in operation on satellites orbiting the Earth, in machine tools and mobile equipment, on oil rigs and refineries, in hospitals and aboratories, in fact, wherever there is a need for motion and control, you ill find Parker components and system solutions hard at work. For more information, visit Parker's web site at www.parker.com.




Control systems and components for aerospace and related high-technology markets



Rigid and flexible connectors and associated products for pneumatic and fluid systems



Hydraulic components and systems for industrial and mobile machinery



Pneumatic and electromechanical components and systems for automation Climate & Industrial Controls

System-control and fluid handling components and systems for refrigeration, air conditioning and industrial equipment

Instrumentation



Industrial and commercial sealing devices and related products

Filtration



Commercial filtration, separation and clarification products

High-quality critical flow components for process instrumentation, ultra-highpurity, medical and analytical applications



Stratoflex Products Division Parker Hannifin Corporation 220 Roberts Cut-Off Road Fort Worth, Texas 76114 U.S.A. Phone: (817) 738-6543 Fax: (817) 738-9920

Stratoflex Products Division, Couplings Business Unit Parker Hannifin Corporation 3800 Calle Tecate Camarillo, CA 93012 U.S.A. Phone: (805) 484-8533 Fax: (805) 987-8958

Stratoflex Products Division Jacksonville Business Unit 2725 W. 5th Street Jacksonville, Florida 32254 U.S.A. Phone: (904) 389-3400 Fax: (904) 384-5874

Website: www.parker.com/stratoflex

