

Fusor® 123 Seam Sealer Family

Seal and Tool Large Interior and Exterior Seams



Fusor® 123 seam sealer family consists of two-component, urethane-based sealers used for duplicating factory appearance on truck beds, tooled door skins, floor pans and core support seams. We have a range of work times available in fast and slow.

These sealers are used in applications which require a non-sag and heavy-bodied cosmetic seam sealer. Fusor 123 can be applied directly to bare metal or primed surfaces.

Features & Benefits:

- **Range of Work Times** – Plenty of time to tool sealer in the summer months with humid climates and winter with colder temperatures
- **Seal & Bond** – Scuffed, primed, E-coated and painted surfaces
- **VOC-Free** – Work safer with this family of seam sealers that contain no volatile organic compounds
- **Weld-Through** – Can be welded to duplicate OEM weld-through sealers
- **Non-Sag & Heavy-Bodied** – Urethane formula holds bead pattern on horizontal surfaces, allowing for a better finish

Product Information:

Part #	Non-Sag Seam Sealer	Cartridge Size	UPC #	OEM Approvals
123	Fast	210 mL	Cartridge: 808498100413 Case: 10808498100410	Honda, Acura
123SL	Slow	210 mL	Cartridge: 808498101793 Case: 10808498101790	Honda, Acura
126	Fast	50 mL	Cartridge: 808498100376 Case: 10808498100373	Honda, Acura



Contact Information:

Parker Lord
Engineered Materials Group
 111 LORD Drive
 Cary, NC 27511-7923
 USA

phone +1 877 Ask Lord (275-5673)

www.Parker.com/APS