


SOFT-SHIELD® 5000

Low Closure Force, Conductive Fabric Jacket
Over Foam Core EMI Gaskets



Customer Value

Proposition:

Parker Chomerics SOFT-SHIELD® 5000 Series gaskets offer a low cost and high performance EMI gasketing solution for commercial electronic systems. This product has been obsoleted as of 2019 and has been replaced with SOFT-SHIELD 3500. **Cross referenced part numbers can be found on the last page of this document.**


The high reliability conductive fabric over foam core construction provides a cost effective alternative to beryllium copper or stainless steel fingerstock EMI gaskets. Applications for these conductive fabric over urethane foam core gaskets include; commercial electronic enclosures, medical electronics and general industrial applications. The variety of available cross-section profiles allow for very low closure forces, thus offering a minimization of the number of necessary fasteners for easy, user friendly installation, without an effect to shielding effectiveness. Cut-to-length strips of gasket are self terminating thereby enhancing the reliability of the application. The urethane foam core has excellent compressibility making the gasket material especially attractive for thin-walled plastic enclosures. Gaskets are offered standard with a UL 94 V-0 flammability rating.

Contact Information:

Parker Hannifin Corporation
Chomerics Division
77 Dragon Court
Woburn, MA 01801

phone 781 935 4850
fax 781 933 4318
chomailbox@parker.com

www.parker.com/chomerics



Product Features:

- Low closure force required for optimum performance.
- Provides shielding effectiveness over 90 dB from 10 MHz to 10 GHz.
- Silver nickel-plated, woven, ripstop nylon jacket over highly compressible urethane foam core.
- Supplied standard with a pressure sensitive acrylic based adhesive (PSA)
- Self terminating jacket – no loose fibers or sharp edges when gasket is cut.
- No degradation of shielding effectiveness after 10,000 deflection cycles.
- Supplied in standard 8 foot lengths in multiple cross section styles including rectangular, square, D-shape, C-fold, astragal, P-shape, triangular, and knife-edge with rigid inserts. Custom profiles are also possible.
- Available as kiss-cut parts on polyester film release liner for “peel and stick applications.”
- Available as individual pre-cut pieces .
- Single-piece “picture frame” gaskets can also be fabricated from continuous lengths, incorporating integral pre-cut notches.
- UL 94V-0 rated.
- RoHS & REACH compliant

SOFT-SHIELD® 5000 - Available Profiles

Contact Chomerics for any other special requirements and an updated profile list.

ORDERING INFORMATION

Referring to Tables 1-9 to order SOFT-SHIELD 5000 Series gasketing.






Table 1

RECTANGULAR STRIPS inches (mm)		
Profile Number	Height	Width
74039	0.020 (0.50)	0.157 (4.00)
74020	0.039 (1.00)	0.157 (4.00)
74003	0.039 (1.00)	0.197 (5.00)
74038	0.039 (1.00)	0.275 (7.00)
74004	0.039 (1.00)	0.394 (10.00)
74035	0.059 (1.50)	0.157 (4.00)
74040	0.062 (1.60)	0.200 (5.00)
74034	0.071 (1.80)	0.551 (14.00)
74002	0.079 (2.00)	0.157 (4.00)
74005	0.079 (2.00)	0.275 (7.00)
74066	0.079 (2.00)	0.355 (9.00)


74005, 74021



74003, 74004, 74020, 74035



74038



NOTE: Dimensions shown do not include PSA thickness (0.005 inch typically).
All SOFT-SHIELD 5000 Series profiles are supplied in UL 94V-0 rated versions.

SOFT-SHIELD® 5000 - Available Profiles






Table 1 continued

RECTANGULAR STRIPS inches (mm)		
Profile Number	Height	Width
74025	0.079 (2.00)	0.394 (10.00)
74049	0.079 (2.00)	0.827 (21.00)
74099	0.090 (2.30)	0.157 (4.00)
74102	0.098 (2.50)	0.870 (22.00)
74048	0.118 (3.00)	0.157 (4.00)
74023	0.125 (3.18)	0.250 (6.35)
74000	0.125 (3.18)	0.375 (9.53)
74012	0.125 (3.18)	0.500 (12.70)
74001	0.125 (3.18)	0.800 (20.32)
74015	0.130 (3.30)	0.190 (4.83)
74054	0.200 (5.00)	0.300 (7.60)
74016	0.250 (6.35)	0.375 (9.53)
74014	0.250 (6.35)	0.500 (12.70)
74021	0.375 (9.53)	0.500 (12.70)


74002, 74023




74000, 74015, 74025



74012, 74001



74014, 74016



NOTE: Dimensions shown do not include PSA thickness (0.005 inch typically).
All SOFT-SHIELD 5000 Series profiles are supplied in UL 94V-0 rated versions.

SOFT-SHIELD® 5000 - Available Profiles




Table 2

SQUARE STRIPS inches (mm)		
Profile Number	Height	Width
74018	0.118 (3.00)	0.118 (3.00)
74017	0.200 (5.00)	0.200 (5.00)
74022	0.236 (6.00)	0.236 (6.00)
74118	0.250 (6.35)	0.250 (6.35)
74024	0.375 (9.53)	0.375 (9.53)
74028	0.500 (12.70)	0.500 (12.70)






Table 3

D-STRIPS inches (mm)		
Profile Number	Height	Width
74037	0.060 (1.52)	0.150 (3.80)
74081	0.070 (1.78)	0.250 (6.35)
74019	0.090 (2.30)	0.090 (2.30)
74031	0.090 (2.30)	0.150 (3.80)
74053	0.100 (2.54)	0.250 (6.35)
74052	0.108 (2.74)	0.150 (3.80)
74055	0.110 (2.79)	0.225 (5.72)
74074	0.110 (2.79)	0.380 (9.65)
74013	0.120 (3.05)	0.150 (3.80)


74024, 74022, 74018




74017, 74028



74037



74019, 74031



NOTE: Dimensions shown do not include PSA thickness (0.005 inch typically).
All SOFT-SHIELD 5000 Series profiles are supplied in UL 94V-0 rated versions.

SOFT-SHIELD® 5000 - Available Profiles




Table 3 continued

D-STRIPS inches (mm)		
Profile Number	Height	Width
74036	0.120 (3.05)	0.250 (6.35)
74006	0.140 (3.56)	0.250 (6.35)
74058	0.140 (3.57)	0.380 (9.65)
74056	0.155 (3.94)	0.250 (6.35)
74041	0.157 (4.00)	0.150 (3.80)
74030	0.157 (4.00)	0.236 (6.00)
74033	0.180 (4.57)	0.400 (10.16)
74011	0.250 (6.35)	0.375 (9.53)
74029	0.375 (9.53)	0.500 (12.70)




Table 4

C-FOLD STRIPS inches (mm)		
Profile Number	Height	Width
74057	0.250 (6.35)	0.280 (7.11)
74008	0.385 (9.78)	0.420 (10.67)
74027	0.465 (11.81)	0.420 (10.67)






Table 5

ASTRAGEL STRIPS inches (mm)		
Profile Number	Height	Width
74010	0.675 (17.14)	0.580 (14.73)


74006, 74029, 74033, 74036




74011, 74013, 74030



74008, 74027



74010



NOTE: Dimensions shown do not include PSA thickness (0.005 inch typically).
All SOFT-SHIELD 5000 Series profiles are supplied in UL 94V-0 rated versions.

SOFT-SHIELD® 5000 - Available Profiles




Table 6

P-STRIPS inches (mm)			
Profile	Profile Number	Height	Width
P Shape	74009	0.130 (3.30)	0.520 (13.20)




Table 7

TRIANGULAR STRIPS inches (mm)			
Profile	Profile Number	Height	Width
Triangle Shape	74063	0.118 (3.00)	0.150 (3.81)
Triangle Shape	74042	0.782 (19.86)	0.882 (22.40)







Table 8

KNIFE-EDGE STRIPS inches (mm)			
Profile	Profile Number	Height	Width
Knife Shape	74007	0.106 (2.69)	0.445 (11.30)

Table 9

OTHER SOFT-SHIELD 5000 PROFILES inches (mm)			
Profile	Profile Number	Height	Width
Stealth Shape	74059	0.080 (2.03)	0.675 (17.15)
Stealth Shape	74101	0.100 (2.54)	0.393 (9.98)
Stealth Shape	74095	0.120 (3.05)	0.400 (10.16)
Stealth Shape	74084	0.134 (3.40)	0.625 (15.88)
Clip Shape	74045	0.200 (5.08)	0.156 (3.96)
Clip Shape	74077	0.240 (6.10)	0.296 (7.52)
Tall D Shape	74032	0.126 (3.20)	0.090 (2.29)



NOTE: Dimensions shown do not include PSA thickness (0.005 inch typically).
All SOFT-SHIELD 5000 Series profiles are supplied in UL 94V-0 rated versions.

SOFT-SHIELD® 5000 - Product Information


Table 10

Typical Properties		
Property	Test Method	SOFT-SHIELD 5000
Shielding Effectiveness	CHO-TM-TP08	See Figure 1
Compression-Deflection	ASTM C165 (modified)	See Graphs per Profile
Compression Set, % @ 25% Deflection	ASTM D3574 (modified)	<15%
Electrical Conductivity	CEPS-0002	0.1 ohm/sq., max
Adhesive Peel Strength	ASTM D1000 (90° Bend)	4 lb/inch (0.7 N/mm), min
Pressure-Sensitive Adhesive	-	Non-Conductive Adhesive
Operating Temperature Range	-	-40 to +70°C

Table 11

Dimensional Tolerances	
Cross Section inches (mm)	inches (mm)
Up to 0.040 (1.02)	±0.010 (0.25)
Above 0.040 (1.02)	±0.020 (0.51)
Cut Length inches (cm)	inches (mm)
up to 5.00 (up to 12.7)	±0.030 (0.76)
5.01 to 10.00 (12.7 to 25.4)	±0.060 (1.52)
10.01 to 15.00 (25.4 to 38.1)	±0.070 (1.78)
15.01 to 20.00 (38.1 to 50.8)	±0.080 (2.03)
20.01 to 30.00 (50.8 to 76.2)	±0.100 (2.54)
30.01 to 48.00 (76.2 to 121.92)	±0.200 (5.08)
48.01 to 95.00 (121.92 to 241.3)	±0.250 (6.35)
over 95.00 (over 241.3)	±0.500 (12.7)
Die-Cut inches (mm)	inches (mm)
up to 10.00 (up to 254)	±0.020 (0.51)
10.01 to 20.00 (25.4 to 508)	±0.030 (0.76)
20.01 to 30.00 (508.3 to 762)	±0.040 (1.02)
over 30.00 (over 762)	±0.060 (1.52)

Figure 1 Shielding Effectiveness



ORDERING PROCEDURE

Referring to Tables 1-9, use the part numbering scheme shown here to order SOFT-SHIELD 5000 Series gasketing.

82 —
SOFT-SHIELD® 5000 Family

ABC —
A:
 1. Silver nickel-plated nylon rip-stop fabric
B:
 2. Pressure Sensitive Acrylic Adhesive (PSA)
C:
 2. UL 94V-0 rating

XXXXX —
Profile Number

YYYYY —
Standard length of strip is 96 in.
Example: 09600 = 96"
Cut to length options available

SOFT-SHIELD® 5000 - Cross Reference to SOFT-SHIELD 3500

Cross From SOFT-SHIELD 5000	Cross To SOFT-SHIELD 3500	Cross From SOFT-SHIELD 5000	Cross To SOFT-SHIELD 3500
82-122-74000-09600	77-12-3148-09600	82-122-74031-09600	77-12-3648-09600
82-122-74001-09600	77-12-3470-09600	82-122-74032-09600	77-12-3602-09600
82-122-74002-09600	77-12-3104-09600	82-122-74033-09600	77-12-3785-09600
82-122-74003-09600	77-12-3217-09600	82-122-74034-09600	77-12-3533-09600
82-122-74004-09600	77-12-3233-09600	82-122-74035-09600	77-12-3370-09600
82-122-74005-09600	77-12-3133-09600	82-122-74036-09600	77-12-3651-09600
82-122-74006-09600	77-12-3650-09600	82-122-74037-09600	77-12-3607-09600
82-122-74007-09600	77-12-3837-09600	82-122-74038-09600	77-12-3224-09600
82-122-74008-09600	77-12-3806-09600	82-122-74039-09600	77-12-3268-09600
82-122-74009-09600	77-12-3816-09600	82-122-74040-09600	77-12-3219-09600
82-122-74010-09600	77-12-3807-09600	82-122-74041-09600	77-12-3666-09600
82-122-74011-09600	77-12-3626-09600	82-122-74048-09600	77-12-3106-09600
82-122-74012-09600	77-12-3173-09600	82-122-74049-09600	77-12-9288-09600
82-122-74013-09600	77-12-3608-09600	82-122-74052-09600	77-12-3608-09600
82-122-74014-09600	77-12-3174-09600	82-122-74053-09600	77-12-3671-09600
82-122-74015-09600	77-12-3298-09600	82-122-74054-09600	77-12-3311-09600
82-122-74016-09600	77-12-3149-09600	82-122-74055-09600	77-12-3669-09600
82-122-74017-09600	77-12-3113-09600	82-122-74056-09600	77-12-3693-09600
82-122-74018-09600	77-12-3102-09600	82-122-74057-09600	77-12-3872-09600
82-122-74019-09600	77-12-3601-09600	82-122-74058-09600	77-12-3667-09600
82-122-74020-09600	77-12-3214-09600	82-122-74059-09600	77-12-3845-09600
82-122-74021-09600	77-12-3175-09600	82-122-74066-09600	77-12-3143-09600
82-122-74022-09600	77-12-3126-09600	82-122-74074-09600	77-12-3672-09600
82-122-74023-09600	77-12-3128-09600	82-122-74081-09600	77-12-3765-09600
82-122-74024-09600	77-12-3150-09600	82-122-74084-09600	77-12-3850-09600
82-122-74025-09600	77-12-3151-09600	82-122-74095-09600	77-12-3890-09600
82-122-74027-09600	77-12-3830-09600	82-122-74099-09600	77-12-3498-09600
82-122-74028-09600	77-12-3176-09600	82-122-74101-09600	77-12-3823-09600
82-122-74029-09600	77-12-3643-09600	82-122-74118-09600	77-12-3270-09600
82-122-74030-09600	77-12-3649-09600	82-122-90057-09600	77-12-3914-09600

www.parker.com/chomerics

CHOMERICS and SOFT-SHIELD are registered trademarks of Parker Hannifin Corporation. © 2020

TB 1076 EN June 2020



ENGINEERING YOUR SUCCESS.