


Quick Ship DustHog® SFC Cartridge Collector

Perfect for welding, laser and plasma cutting, grinding, buffing, sanding, smelting, bulk powder handling, and more!

Easy to order and faster delivery to your facility, the flagship of industrial dust collection. Parker DustHog® SFC Quick Ship includes our three most popular models: SFC 8-2, SFC 12-3, and the SFC 16-4.

We will ship directly to your location within 20 days of a confirmed purchase order. All three models will be available for non-combustible or combustible dust (Kst <200) applications, including industry best Protura® filtration media, and each model will include standard features and accessories.

Simplicity and speed to meet your immediate need including new part numbers that incorporate all components required for a complete dust collection solution.



Clean Air. It's What We Do.®

We dramatically increased cartridge life by designing the SFC with optimized cabinets that broadened the space between cartridges and sidewalls to ensure lower velocities and reduced cartridge abrasion.



ENGINEERING YOUR SUCCESS.

Quick Ship DustHog® SFC Cartridge Collector

Air to Cloth, CFM

SFC Model	Number of Filters	Protura Filter Area, sq. ft.	2: 1	4: 1	Approx Shipping Weight, lbs.*
8-2	8	2,040	4,000	8,000	1,932
12-3	12	3,060	6,000	12,000	2,420
16-4	16	4,080	8,000	16,000	4,080

*Shipping weight is approximate and is only the SFC collector; it does not include a blower, 55-gal drum, or any accessories.

What is included in the Quick Ship part number?

- The collector you select, any of the three SFC models 8-2 / 12-3 / 16-4
- Protura FR nanofiber filters
- 45-degree hopper and leg set
- 55-gallon dust drum with drum lid and latch kit
- Electronic filter cleaning controls
- Variable-frequency drive for 460V/3P/60H input power¹
- Sprinkler coupler²
- Top mounted SFDD blower³, HP; 7.5 / 10 / 20 / 30
- Top and front blank-off panels for customer-supplied inlet collar
- Left-side clean chamber access panel
- Quoting and pricing will be available through eQUIP

For combustible dust models:

- Left side mounted explosion membrane for combustible dust applications

What can you order as separate accessories?

- Inlet collar
- Airflow control
- Blower silencer
- Non-return valve

Get 25% or more pulse cleaning power than the competition with our proprietary pulse cleaning technology, greater air capacity, and quick and easy maintenance.

Unlike competitors, the SFC uses external filter tracks to support the filters instead of internal filter “yokes” that interfere with cleaning, obstruct airflow, and add costly static pressure. The track system also serves as a static dissipative - filter grounding system that provides a path from the filter cage to the endcaps to the filter track to the chassis ground. The optimized nozzle and venturi filter cleaning system design allows unobstructed airflow and increased cleaning power with less energy, lower pressure drop, and longer cartridge life.

Contact your local distributor today or visit us online to find a specialist at dusthog.com.

¹Indoor/Inside installation only

²Customer is responsible for sprinkler head, installation, and any related sprinkler system components.

³Top-mounted blower housing support included where applicable.

