

Gold Cup Hydrostatic Pumps and Motors for Open and Closed Circuits

Naval Applications




Trusted by Navies Worldwide for the Most Demanding Applications

The tried and true design incorporates features such as, integral servo and replenishing pump, hot oil shuttle, and a unique servo control system; all of which combine to provide a rugged self-contained package that can withstand the harshest of conditions and continue to perform with trouble-free long life.

Certification and Approvals:

- Mil-P-17869
- Mil-S-901-C Grade A
- ABS Type Certification



Contact Information:

Parker Hannifin Corporation
Hydraulic Pump and Power Systems
14249 Industrial Parkway
Marysville, OH 43040 USA


phone 937 644 3915
fax 937 642 3738
hps.support@support.parker.com

www.parker.com/hps



Product Features:

- Rugged military fielded design
- Precise control accuracy
- Service and repair friendly
- Complete packaged functions
- Balanced components for extended life
- Ideal for tensioning applications





ENGINEERING YOUR SUCCESS

Gold Cup Sets the Standard for Dependability and Performance

Since Gold Cup's inception nearly 50 years ago, these first generation pumps and motors are still in use.

Gold Cup's naval applications include:

- Steering / Stabilizer
- Anchor Windlass
- Active Heave Compensated (AHC) Cranes
- Replenishment at Sea (RAS) System
- Gun Turret
- Hatch Doors
- Deck Edge Elevators
- Aircraft Handling Systems



SCHEDULE AN ENGINEERING CONSULTATION

Talk to a Parker Expert to find out how GOLD CUP can help you on your next application.

Email: pumptechsupport@parker.com